

LOC E	DIST B	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			C	ECR-05-017969	09JAN06	JMS	FWK

NOTES:

- 1

PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 2

100 TRAY PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 3

Ag PLATING
- 4

ELECTRICAL CHARACTERISTICS

FREQUENCY RANGE:DC - 11 GHz

NOMINAL IMPEDANCE:50 Ohm

INSULATION RESISTANCE:5000 MOhm

WORKING VOLTAGE:500 Volts RMS at Sea Level

DIELECTRIC WITHSTAND VOLTAGE:1500 Volts RMS Max

CONTACT RESISTANCE:

CENTRE CONTACT:1.50 mOhm Max

OUTER CONTACT:1.00 mOhm Max




INSERTION LOSS db:0.20 Max
- 5

MECHANICAL CHARATERISTICS


DURABILITY:500 Cycles Min
- 6

ENVIRONMENTAL CHARACTERISTICS

OPERATING TEMPERATURE:-65 to +165 DegC



		1	1	BRASS	FLANGE	4
		1	1	PTFE	INSULATION	3
		1	1	BRASS	CONTACT	2
		1	1	BRASS	BODY	1
		6--0	1--0	MATERIAL	DESCRIPTION	ITEM
QUANTITY PER ASSY				PARTS LIST		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	J.SANDWELL		09JAN06		tyco Electronics Tyco Electronics Corporation Bideford EX39 4HE		
DIMENSIONS:		CHK	S.PARLOW		09JAN06		NAME		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD		09JAN06		TNC PANEL SOCKET 50 OHM		
	0 PLC		± -				-		
	1 PLC		± -				-		
	2 PLC		± -				-		
	3 PLC		± -				-		
4 PLC		± -							
ANGLES		± -							
MATERIAL	FINISH		WEIGHT		-		SIZE		
SEE TABLE	-						CAGE CODE		
								DRAWING NO	
								RESTRICTED TO	
								-	
								A3 00779 C-1337472	
								SCALE	
								NTS	
								SHEET	
								1 OF 1	
								REV	
								C	
								CUSTOMER DRAWING	