

### THYRISTOR/ DIODE and THYRISTOR/ THYRISTOR

### ADD-A-pak™ GEN V Power Modules

#### Features

- High Voltage
- Industrial Standard Package
- Thick copper baseplate
- UL E78996 approved
- 3500V<sub>RMS</sub> isolating voltage
- TOTALLY LEAD-FREE

#### Benefits

- Up to 1600V
- Full compatible TO-240AA
- High Surge capability
- Easy Mounting on heatsink
- Al<sub>2</sub>O<sub>3</sub> DBC insulator
- Heatsink grounded

105 A

#### Mechanical Description

The Generation V of Add-A-pak module combine the excellent thermal performance obtained by the usage of Direct Bonded Copper substrate with superior mechanical ruggedness, thanks to the insertion of a solid Copper baseplate at the bottom side of the device. The Cu baseplate allow an easier mounting on the majority of heatsink with increased tolerance of surface roughness and improve thermal spread.

The Generation V of AAP module is manufactured without hard mold, eliminating in this way any possible direct stress on the leads.

The electrical terminals are secured against axial pull-out: they are fixed to the module housing via a click-stop feature already tested and proved as reliable on other IR modules.

#### Electrical Description

These modules are intended for general purpose high voltage applications such as high voltage regulated power supplies, lighting circuits, temperature and motor speed control circuits, UPS and battery charger.

#### Major Ratings and Characteristics

| Parameters                           | Values      | Units              |
|--------------------------------------|-------------|--------------------|
| $I_{T(AV)}$ or $I_{F(AV)}$<br>@ 85°C | 105         | A                  |
| $I_{O(RMS)}$ (*)                     | 235         | A                  |
| $I_{TSM}$ @ 50Hz                     | 1785        |                    |
| $I_{FSM}$ @ 60Hz                     | 1870        |                    |
| $I^2t$ @ 50Hz                        | 15.91       | KA <sup>2</sup> s  |
| @ 60Hz                               | 14.52       |                    |
| $I^2\sqrt{t}$                        | 159.1       | KA <sup>2</sup> /s |
| $V_{RRM}$ range                      | 400 to 1600 | V                  |
| $T_{STG}$                            | -40 to 150  | °C                 |
| $T_J$                                | -40 to 130  |                    |

(\*) As AC switch.



# IRK.105..P Series

Bulletin I27215 01/07


International  
IOR Rectifier

## ELECTRICAL SPECIFICATIONS

### Voltage Ratings

| Type number | Voltage Code | $V_{RRM}$ , maximum repetitive peak reverse voltage<br>V | $V_{RSM}$ , maximum non-repetitive peak reverse voltage<br>V | $V_{DRM}$ , max. repetitive peak off-state voltage, gate open circuit<br>V | $I_{RRM}$<br>$I_{DRM}$<br>130°C<br>mA |
|-------------|--------------|----------------------------------------------------------|--------------------------------------------------------------|----------------------------------------------------------------------------|---------------------------------------|
| IRK.105     | 04           | 400                                                      | 500                                                          | 400                                                                        | 20                                    |
|             | 06           | 600                                                      | 700                                                          | 600                                                                        |                                       |
|             | 08           | 800                                                      | 900                                                          | 800                                                                        |                                       |
|             | 10           | 1000                                                     | 1100                                                         | 1000                                                                       |                                       |
|             | 12           | 1200                                                     | 1300                                                         | 1200                                                                       |                                       |
|             | 14           | 1400                                                     | 1500                                                         | 1400                                                                       |                                       |
|             | 16           | 1600                                                     | 1700                                                         | 1600                                                                       |                                       |

### On-state Conduction

| Parameters                                                                                                  | IRK.105 | Units                        | Conditions                                                                                                                                                      |
|-------------------------------------------------------------------------------------------------------------|---------|------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------|
| $I_{T(AV)}$ Max. average on-state current (Thyristors)<br>$I_{F(AV)}$ Max. average forward current (Diodes) | 105     | A                            | 180° conduction, half sine wave,<br>$T_C = 85^\circ\text{C}$                                                                                                    |
| $I_{O(RMS)}$ Max. continuous RMS on-state current.<br>As AC switch                                          | 235     |                              |                                                                              |
| $I_{TSM}$ Max. peak, one cycle<br>or non-repetitive on-state                                                | 1785    |                              | $t = 10\text{ms}$ No voltage                                                                                                                                    |
| $I_{FSM}$ or forward current                                                                                | 1870    |                              | $t = 8.3\text{ms}$ reapplied                                                                                                                                    |
|                                                                                                             | 1500    |                              | $t = 10\text{ms}$ 100% $V_{RRM}$                                                                                                                                |
|                                                                                                             | 1570    |                              | $t = 8.3\text{ms}$ reapplied                                                                                                                                    |
|                                                                                                             | 2000    |                              | $T_J = 25^\circ\text{C}$ ,<br>$t = 10\text{ms}$ no voltage reapplied                                                                                            |
|                                                                                                             | 2100    |                              | $t = 8.3\text{ms}$                                                                                                                                              |
| $I^2t$ Max. $I^2t$ for fusing                                                                               | 15.91   | $\text{KA}^2\text{s}$        | $t = 10\text{ms}$ No voltage                                                                                                                                    |
|                                                                                                             | 14.52   |                              | $t = 8.3\text{ms}$ reapplied                                                                                                                                    |
|                                                                                                             | 11.25   |                              | $t = 10\text{ms}$ 100% $V_{RRM}$                                                                                                                                |
|                                                                                                             | 10.27   |                              | $t = 8.3\text{ms}$ reapplied                                                                                                                                    |
|                                                                                                             | 20.00   |                              | $T_J = 25^\circ\text{C}$ ,<br>$t = 10\text{ms}$ no voltage reapplied                                                                                            |
|                                                                                                             | 18.30   |                              | $t = 8.3\text{ms}$                                                                                                                                              |
| $I^2\sqrt{t}$ Max. $I^2\sqrt{t}$ for fusing (1)                                                             | 159.1   | $\text{KA}^2\sqrt{\text{s}}$ | $t = 0.1$ to $10\text{ms}$ , no voltage reappl. $T_J = T_J \text{ max}$                                                                                         |
| $V_{T(TO)}$ Max. value of threshold voltage (2)                                                             | 0.80    | V                            | Low level (3)                                                                                                                                                   |
|                                                                                                             | 0.85    |                              | High level (4)                                                                                                                                                  |
| $r_t$ Max. value of on-state slope resistance (2)                                                           | 2.37    | $\text{m}\Omega$             | Low level (3)                                                                                                                                                   |
|                                                                                                             | 2.25    |                              | High level (4)                                                                                                                                                  |
| $V_{TM}$ Max. peak on-state or<br>$V_{FM}$ forward voltage                                                  | 1.64    | V                            | $I_{TM} = \pi \times I_{T(AV)}$<br>$I_{FM} = \pi \times I_{F(AV)}$<br>$T_J = 25^\circ\text{C}$                                                                  |
| $di/dt$ Max. non-repetitive rate of rise of turned on current                                               | 150     | $\text{A}/\mu\text{s}$       | $T_J = 25^\circ\text{C}$ , from $0.67 V_{DRM}$ ,<br>$I_{TM} = \pi \times I_{T(AV)}$ , $I_g = 500\text{mA}$ ,<br>$t_r < 0.5 \mu\text{s}$ , $t_p > 6 \mu\text{s}$ |
| $I_H$ Max. holding current                                                                                  | 250     | mA                           | $T_J = 25^\circ\text{C}$ , anode supply = 6V,<br>resistive load, gate open circuit                                                                              |
| $I_L$ Max. latching current                                                                                 | 400     |                              | $T_J = 25^\circ\text{C}$ , anode supply = 6V, resistive load                                                                                                    |

(1)  $I^2t$  for time  $t_x = I^2\sqrt{t} \times \sqrt{t_x}$

(2) Average power =  $V_{T(TO)} \times I_{T(AV)} + r_t \times (I_{T(RMS)})^2$

(3)  $16.7\% \times p \times I_{AV} < I < p \times I_{AV}$

(4)  $I > p \times I_{AV}$

### Triggering

| Parameters                                       | IRK.105 | Units | Conditions                                             |
|--------------------------------------------------|---------|-------|--------------------------------------------------------|
| $P_{GM}$ Max. peak gate power                    | 12      | W     |                                                        |
| $P_{G(AV)}$ Max. average gate power              | 3       |       |                                                        |
| $I_{GM}$ Max. peak gate current                  | 3       | A     |                                                        |
| $-V_{GM}$ Max. peak negative gate voltage        | 10      | V     | Anode supply = 6V<br>resistive load                    |
| $V_{GT}$ Max. gate voltage required to trigger   | 4.0     |       |                                                        |
|                                                  | 2.5     |       |                                                        |
|                                                  | 1.7     |       |                                                        |
| $I_{GT}$ Max. gate current required to trigger   | 270     | mA    | Anode supply = 6V<br>resistive load                    |
|                                                  | 150     |       |                                                        |
|                                                  | 80      |       |                                                        |
| $V_{GD}$ Max. gate voltage that will not trigger | 0.25    | V     | $T_J = 125^\circ\text{C}$ ,<br>rated $V_{DRM}$ applied |
| $I_{GD}$ Max. gate current that will not trigger | 6       | mA    | $T_J = 125^\circ\text{C}$ ,<br>rated $V_{DRM}$ applied |

### Blocking

| Parameters                                                                         | IRK.105                      | Units            | Conditions                                                                  |
|------------------------------------------------------------------------------------|------------------------------|------------------|-----------------------------------------------------------------------------|
| $I_{RRM}$ Max. peak reverse and off-state leakage current at $V_{RRM}$ , $V_{DRM}$ | 20                           | mA               | $T_J = 130^\circ\text{C}$ , gate open circuit                               |
| $V_{INS}$ RMS isolation voltage                                                    | 2500 (1 min)<br>3500 (1 sec) | V                | 50 Hz, circuit to base, all terminals shorted                               |
| $dv/dt$ Max. critical rate of rise of off-state voltage (5)                        | 500                          | V/ $\mu\text{s}$ | $T_J = 130^\circ\text{C}$ , linear to $0.67 V_{DRM}$ ,<br>gate open circuit |

(5) Available with  $dv/dt = 1000\text{V/ms}$ , to complete code add S90 i.e. IRKT105/16AS90.

### Thermal and Mechanical Specifications

| Parameters                                                    | IRK.105     | Units            | Conditions                                                                                                                              |
|---------------------------------------------------------------|-------------|------------------|-----------------------------------------------------------------------------------------------------------------------------------------|
| $T_J$ Junction operating temperature range                    | - 40 to 130 | $^\circ\text{C}$ |                                                                                                                                         |
| $T_{stg}$ Storage temp. range                                 | - 40 to 150 |                  |                                                                                                                                         |
| $R_{thJC}$ Max. internal thermal resistance, junction to case | 0.135       | K/W              | Per module, DC operation                                                                                                                |
| $R_{thCS}$ Typical thermal resistance case to heatsink        | 0.1         |                  | Mounting surface flat, smooth and greased                                                                                               |
| $T$ Mounting torque $\pm 10\%$<br>to heatsink<br>busbar       | 5           | Nm               | A mounting compound is recommended and the torque should be rechecked after a period of 3 hours to allow for the spread of the compound |
|                                                               | 3           |                  |                                                                                                                                         |
| wt Approximate weight                                         | 110 (4)     | gr (oz)          |                                                                                                                                         |
| Case style                                                    | TO-240AA    |                  | JEDEC                                                                                                                                   |

### $\Delta R$ Conduction (per Junction)

(The following table shows the increment of thermal resistance  $R_{thJC}$  when devices operate at different conduction angles than DC)

| Devices | Sine half wave conduction |      |      |      |      | Rect. wave conduction |      |      |      |      | Units                     |
|---------|---------------------------|------|------|------|------|-----------------------|------|------|------|------|---------------------------|
|         | 180°                      | 120° | 90°  | 60°  | 30°  | 180°                  | 120° | 90°  | 60°  | 30°  |                           |
| IRK.105 | 0.04                      | 0.05 | 0.06 | 0.08 | 0.12 | 0.03                  | 0.05 | 0.06 | 0.08 | 0.12 | $^\circ\text{C}/\text{W}$ |

## IRK.105..P Series

Bulletin I27215 01/07

International  
**IOR** Rectifier


### Ordering Information Table

| Device Code |                                                                 |     |   |    |     |   |
|-------------|-----------------------------------------------------------------|-----|---|----|-----|---|
| IRK         | T                                                               | 105 | / | 16 | S90 | P |
| ①           | ②                                                               | ③   |   | ④  | ⑤   | ⑥ |
| <b>1</b>    | Module type                                                     |     |   |    |     |   |
| <b>2</b>    | Circuit configuration (See Circuit Configuration table below)   |     |   |    |     |   |
| <b>3</b>    | Current code **                                                 |     |   |    |     |   |
| <b>4</b>    | Voltage code (See Voltage Ratings table)                        |     |   |    |     |   |
| <b>5</b>    | dv/dt code: S90 = dv/dt 1000 V/μs<br>No letter = dv/dt 500 V/μs |     |   |    |     |   |
| <b>6</b>    | P = Lead-Free                                                   |     |   |    |     |   |

IRK.106 types  
With no auxiliary cathode

\*\* Available with no auxiliary cathode.  
To specify change: 105 to 106  
e.g. : IRKT106/16P etc.

### Outline Table



**NOTE: To order the Optional Hardware see Bulletin I27900**




Fig. 1 - Current Ratings Characteristics




Fig. 2 - Current Ratings Characteristics




Fig. 3 - On-state Power Loss Characteristics




Fig. 4 - On-state Power Loss Characteristics




Fig. 5 - Maximum Non-Repetitive Surge Current




Fig. 6 - Maximum Non-Repetitive Surge Current

## IRK.105..P Series

Bulletin I27215 01/07

International  
**IOR** Rectifier




Fig. 7 - On-state Power Loss Characteristics




Fig. 8 - On-state Power Loss Characteristics




Fig. 9 - On-state Power Loss Characteristics




Fig. 10 - On-state Voltage Drop Characteristics




Fig. 11 - Recovery Charge Characteristics




Fig. 12 - Recovery Current Characteristics




Fig. 13 - Thermal Impedance  $Z_{thJC}$  Characteristics

## IRK.105..P Series

Bulletin I27215 01/07

International  
**IR** Rectifier




Fig. 14- Gate Characteristics

Data and specifications subject to change without notice.  
This product has been designed and qualified for Industrial Level and Lead-Free.  
Qualification Standards can be found on IR's Web site.

International  
**IR** Rectifier

IR WORLD HEADQUARTERS: 233 Kansas St., El Segundo, California 90245, USA Tel: (310) 252-7105  
TAC Fax: (310) 252-7309  
01/07



### Notice

The products described herein were acquired by Vishay Intertechnology, Inc., as part of its acquisition of International Rectifier's Power Control Systems (PCS) business, which closed in April 2007. Specifications of the products displayed herein are pending review by Vishay and are subject to the terms and conditions shown below.

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.

International Rectifier®, IR®, the IR logo, HEXFET®, HEXSense®, HEXDIP®, DOL®, INTERO®, and POWIRTRAIN® are registered trademarks of International Rectifier Corporation in the U.S. and other countries. All other product names noted herein may be trademarks of their respective owners.