


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


PANDUIT PART #	TAB SIZE in. [mm]	WIRE RANGE		COLOR	DIMENSIONS in. [mm]				TOOL CHART	
		ENGLISH AWG	METRIC mm ²		MAX. WIRE INSULATION DIAMETER	L ± .03 [0,8]	W ± .01 [0,3]	H ± .01 [0,3]	PRESSES: CP-861, CP-862, CP-871	
									APPLICATOR DIES: CA9, CA-800EZ	
DNF18250FIBX	.250 X .032 [6,3 X 0,8]	22-18	0,5-1,0	RED	.21 [5,4]	.93 [23,6]	.35 [8,9]	.22 [5,5]	CD-800-6 CD9-6B	
DNF18205FIBX	.205/.187 X .032 [5,2/4,8 X 0,8]					.87 [22,1]	.31 [7,9]	.22 [5,5]		
DNF18206FIBX	.205/.187 X .020 [5,2/4,8 X 0,5]					.87 [22,1]	.31 [7,9]	.22 [5,5]		
DNF14250FIBX	.250 X .032 [6,3 X 0,8]	16-14	1,5-2,5	BLUE	.24 [6,1]	.93 [23,6]	.35 [8,9]	.22 [5,5]	CD-800-8 CD9-8B	
DNF14205FIBX	.205/.187 X .032 [5,2/4,8 X 0,8]					.87 [22,1]	.31 [7,9]	.22 [5,5]		
DNF14206FIBX	.205/.187 X .020 [5,2/4,8 X 0,5]					.87 [22,1]	.31 [7,9]	.22 [5,5]		

NOTES:

1. USED FOR:
 - A. STRANDED COPPER WIRE ONLY
 - B. 221°F [105°C] MAX. OPERATING TEMPERATURE
 - C. 600V. MAX. BLDG WIRE
 - D. 6-12 LBS INTIAL INSERTION/WITHDRAWAL FORCE
2. MATERIAL:
 - A. STAMPING: CDA 260 BRASS, TIN PLATED
 - B. HOUSING: TYPE 66 NYLON
3. WIRE STRIP LENGTH: $9/32'' \begin{smallmatrix} +1/32 \\ -0 \end{smallmatrix} [7,1 \begin{smallmatrix} +0,8 \\ -0 \end{smallmatrix}]$
4. SEE www.panduit.com FOR PACKAGE QUANTITIES INDICATED BY PART NUMBER SUFFIX
5. DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT
6. COLORS ARE TRANSLUCENT



LISTED CERTIFIED
20H3 LR31212
E78522

TITLE					FEMALE DISCONNECTS, NYLON FULLY INSULATED - EXPANDED WIRE ENTRY	
ITEM REVISION NAME					CUSTOMER DRAWING	
N41167BA/05						
DATASET FILE NAME						
N41167BA_DC/05A					MATERIAL: SEE NOTES	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .1 [2.54] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 °					DRAWING NUMBER: A41167	
 THIRD ANGLE PROJECTION					DRAWN BY DSM	
DATE -					SIZE A	
CHK -					SHT 1 OF 1	
SCALE N.T.S.						