

Feature -

compact size
reflow soldering available

Application -


consumer products
computer products
instrumentation
communication equipments
hand-held devices



► SPECIFICATIONS



SWITCH SPECIFICATIONS	
POLE - POSITION	3P2T , SMT TYPE
CONTACT RATING	6 V DC , 0.3 A
CONTACT RESISTANCE	50 mΩ MAX. 1.5 V DC ; 100 mA , by Method of Voltage DROP
INSULATION RESISTANCE	100 MΩ MIN. 500 V DC
DIELECTRIC STRENGTH	Breakdown is not Allowable ; 500 V AC for 1 Minute
OPERATING FORCE	200 ± 150gf
OPERATING LIFE	10,000 cycles
OPERATING TEMPERATURE RANGE	-20°C ~ 70°C
TOTAL TRAVEL	2.0 ± 0.2 mm

► HOW TO ORDER




► DIMENSION


SS001-S32NAPA




BOTTON VIEW




► CIRCUIT DIAGRAM



► P.C.B. LAYOUT



► REFLOW SOLDERING



► MATERIAL

- COVER : STAINLESS STEEL
- ACTUATOR : PA + GF
- BASE FRAME : PA + GF
- TERMINAL : SILVER PLATING

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Well Buying:](#)

[SS001-S032NAPA1.2](#)