


⊕ Ø 0.05 (S) X Y
ALL PLATED THRU HOLES



RECOMMENDED PC BOARD
LAYOUT, BACKPLANE,
COMPONENT SIDE SHOWN
SCALE 4:1

- ① REFERENCE APPLICATION SPEC I14-13059 FOR RECOMMENDED PLATED THRU HOLE DIAMETER AND PLATING THICKNESSES.
- ② MATERIAL: CONTACT AND SHIELD - PHOSPHOR BRONZE HOUSING - GLASS FILLED POLYESTER. UL 94V-0.
- ③ FINISH: SIGNAL AND GROUND CONTACTS: MATING AREA: MEETS THE PERFORMANCE REQUIREMENTS OF PRODUCT SPECIFICATION I08-2055; BASED ON TELCORDIA GR-1217-CORE, APPLICATIONS IN UNCONTROLLED ENVIRONMENTS
COMPLIANT PIN AREA: 0.5 µm MIN BRIGHT TIN-LEAD OVER BASE PLATING
- ④ CONNECTOR MARKED WITH PART NUMBER AND DATE CODE.
- ⑤ DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
- ⑥ THE FOUR GROUNDS IN EACH COLUMN ARE COMMONED.
- ⑦ CONTACT AREA LUBRICATED WITH BELLCORE APPROVED LUBRICANT. TECHNICAL REFERENCE: GR-1217-CORE, ISSUE I, NOVEMBER 1995.
- ⑧ DIMENSION APPLIES TO FIRST AND LAST CIRCUITS.
- ⑨ OBSOLETE.

3.80	1469074-2
5.30	1469074-1
DIM M	PART NUMBER
RECOMMENDED PC BOARD LAYOUT, BACKPLANE, COMPONENT SIDE SHOWN SCALE 4:1	
THIS DRAWING IS A CONTROLLED DOCUMENT. DWN S. MAGARO 27SEP01 CHG R. PATTERSON 16AUG2007 APVD N. SCHROLL 27SEP01 PRODUCT SPEC APPLICATION SPEC MATERIAL 1/2 FINISH 3 WEIGHT - CAGE CODE A100779 DRAWING NO. C=1469074 RESTRICTED TO - Customer Drawing SHEET 1 OF 1 REV G	