





PIN NUMBER	DIM. L
25,26	3.50
ALL OTHER PINS	4.25
1, 13, 38, 50	5.00

NOTES :

- MATERIAL :
 INSULATOR : HIGH TEMPERATURE THERMOPLASTIC
 FLAMMABILITY RATING: UL94V-0
 COLOR: IVORY
 CONTACT : COPPER ALLOY
 GROUND MOUNTING EAR: COPPER ALLOY
- PLATING :
 CONTACT AREA: SELECTIVE GOLD (SEE P/N DESCRIPTION)
 UNDER PLATING: 50u" NICKEL OVERALL
 SOLDER TAIL AREA: 100u" TIN/LEAD OR 100u" MATTE TIN.
 GROUND MOUNT EAR AREA: 100u" TIN/LEAD OR 100u" MATTE TIN.
- SOLDERTAILS TO BE WITHIN 0.05 UPWARD
 AND 0.2 DOWNWARD FROM Z-DATUM PLACE,
 AND COPLANARITY OF SOLDER TAILS TO BE
 WITHIN 0.10mm.
- PRODUCT SPEC: GS-12-240.
- PACKAGING SPEC: GS-14-980.



mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY	FCI	
ltr	ecn no	dr	date	linear	.X ± 0.30		www.fciconnect.com	
A	T04-0429	A.C.	12/16/04	linear	.XX ± 0.20	projection	title	
B	T05-0256	A.C.	11/09/05	linear	.XXX ± 0.10	projection	CF HEADER TYPE II REVERSE	
C	T06-0172	A.C.	10/09/06	angles	0° ± 2°	projection	S/O=0.0MM	
D	T09-1098	S.LIN	07/09/09	dr	ALLEN CHANG	MM	product family	CF
E	T09-1114	S.LIN	09/03/09	engr	ALLEN CHANG	MM	size	dwg no
F	T09-1144	S.LIN	11/27/09	chr	STERLING LIN	scale	A4	10044079
				appd	H.C LIU	NA		
sheet	revision	F	F					
index	sheet	1	2					

6.Part Number Description:

P/N: 10044079-XX50XX

PLATING ON SOLDER TAIL AREA:
BLANK: 100u" TIN/LEAD.
LF: 100u" MATTE TIN.

BLANK: WITHOUT CAP+TRAY PACKING
2: WITH CAP+TRAY PACKING
3: WITH CAP+T&R PACKING


PIN COUNT.

KEY TYPE:
1: REVERSE TYPE

GOLD PLATING:
B: 10u" GOLD PLATE
E: 30u" GOLD PLATE



7. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE
FOR 10 SECONDS IN A CONVECTION, IR OR VAPER PHASE REFLOW OVEN.

8. THIS PRODUCT (10053868-XXXXXLF) MEETS THE EUROPEAN UNION DIRECTIVE
AS DESCRIBED IN GS-22-008.



General Tolerance +/-0.05mm

Recommended PCB Pattern

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY	 www.fciconnect.com	
ltr	ecn no	dr	date	linear	.X ± 0.30			
F	-	-	-	linear	.XX ± 0.20	projection	 title	
				angles	.XXX ± 0.10	 		
					0° ±2°	MM	product family CF size dwg no	
				dr	ALLEN CHANG 12/16/04	scale		
				engr	ALLEN CHANG 12/16/04	NA	A4 10044079	
				chr	STERLING LIN 12/16/04			
				appd	H.C LIU 12/16/04		code TWN sheet 2 of 2	
sheet index	revision sheet							