

13000 series

Professional quick-break momentary pushbutton switches

Distinctive features and specifications



- ☐ PC and panel mount models
- ☐ Bushing Ø 6,35 (1/4) and 11,9 (15/32)
- ☐ UL and CECC approved

B2

ELECTRICAL SPECIFICATIONS

- Max. current/voltage rating with resistive load :
 - silver contacts (A-AD2) : 4A 30VDC
 - gold plated contacts (CD) : 100mA 30V
- Minimum load (AD2-CD contacts) : 10mA 50mV, 10µA 5V min.
- Initial contact resistance : 10 mΩ max.
- Insulation resistance : 1.000 MΩ min. at 500VDC
- Dielectric strength :
 - 1.000 Vrms 50 Hz min. between terminals
 - 2.000 Vrms 50 Hz min. between poles and between terminals and frame
- Contact bounce : 2 ms max.
- Electrical life :

Contacts	Max. current/voltage rating	Number of cycles
A	4A 30VDC	50.000
AD2	4A 30VDC (gold plating : 100mA 30VDC max.)	20.000
CD	100mA 30VDC	50.000
	Low level or mechanical life	150.000

MATERIALS

- Case : diallylphthalate (DAP)
- Actuator : brass, nickel plated
- Bushing : brass, nickel plated
- Housing : brass, nickel plated
- Contacts : **A** : silver
AD2 : silver, gold plated
(2 micron gold)
CD : brass, gold plated
- Terminal seal : epoxy

Note : AD2 contacts can be used for high level applications. In this case, the gold layer is considered only as a protection against oxidation during storage.

GENERAL SPECIFICATIONS

- Torque : 1,25 Nm (.922 Ft.lb)
max. applied to nut
- Standard panel thickness : 2 mm
(.078) max.
- Total travel : 2 mm (.078)
- Operating temperature :
-40°C to +85°C

13000 series

Professional quick-break momentary pushbutton switches

Specifications

RELIABILITY - RUN-IN TEST

Upon request, each individual switch can be submitted to a low level run-in test of 50 or 250 cycles to ensure suitability for special applications requiring a very high level of reliability (military, space, etc.).

AGENCY APPROVALS



2A 125VAC/250VAC



CECC 96401-001

Designed to **MIL** specifications

Availability :

UL : all models with silver or gold plated silver contacts

CECC : consult factory for details of approved models.

Marking : to order switches marked UL or CECC, complete appropriate box of ordering format.

Dimensions : first dimensions are in mm while inches are shown as bracketed numbers.



Sealing boots are available to protect the switches against dust and water. They are presented in section H.



Mounting accessories : standard hardware supplied with all models : 2 hex nuts 8 mm (.314) across flats, 1 locking ring and 1 lockwasher.

Standard and special hardware available are presented in section I.




Packaging unit : 50 pieces.

13000 series

Professional quick-break momentary pushbutton switches

Overview



NOTICE : please note that not all combinations of above numbers are available. Refer to the following pages for further information.

ABOUT THIS SERIES

On the following pages, you will find successively :


- model structure of switches
- options in the same order as in above chart

13000 series



Professional quick-break momentary pushbutton switches

Solder lug terminals : 13400 - Straight PC terminals : 13200


→ Keyway



- Threaded bushing $\varnothing 6,35$ mm (1/4)
- Epoxy sealed terminals standard



MODEL
STRUCTURE



B2

Solder lug terminals : 13400

→ Keyway



Single pole
13435




Double pole
13445



ON



MOM



Straight PC terminals : 13200

→ Keyway



Single pole
13235




Double pole
13245



ON




MOM




PANEL CUT-OUT


13400 - 13200



Standard



With K
sealing option



With X640
sealing option

Right angle terminals : 13400W


• • •

→ Keyway



1-3
ON

1-2
MOM



Panel cut-out, see previous page.

A	Silver
AD2	Silver, gold plated (2 micron gold)
CD	Brass, gold plated

A diagram of a linked list with 8 nodes. The nodes are represented as rectangles connected by horizontal lines. The 3rd node from the left is highlighted with a red border.

Dash compulsory before plunger code.

Blank Standard plunger for Ø 6,35 (1/4) bushing

-4 4 mm (.157) long plunger for Ø 11,9 (15/32) bushing (X768 option)


-9 9 mm (.354) long plunger for Ø 11,9 (15/32) bushing (X768 option)



13000 series

Professional quick-break momentary pushbutton switches

FINISH



Blank Bright chrome finish


G Black finish on bushing, actuator and hardware

SEALING




K Front panel sealing by one O-ring and sealing washer. Protects the switch against water and dust. Panel seal withstands 1 bar pressure and remains sealed even when switch is operated.

Reinforced sealing : see X640 under "Special options".



SPECIAL OPTIONS




X640 Front panel sealing by three O-rings. Flatted bush for precise orientation. Protects the switch against water and dust. Panel seal withstands 1 bar pressure and remains sealed even when switch is operated.



Available on models with Ø 6,35 (1/4) bushing only.

X935 C-ring on plunger for positive stop



13000 series

Professional quick-break momentary pushbutton switches

OPTIONS
● ● ●

X768 Sealed switch with Ø 11,9 (15/32) flatted bushing. Chrome plated actuator. Solder lug terminals, double pole. Contact and finish options available.

Security cap for this model : see section I.



With short plunger
13445 -4 X768

With long plunger
13445 -9 X768




ON





MOM


→ Flat




Short (-4)



Long (-9)



AGENCY APPROVALS



UL

CECC CECC 96401-001

Availability :

UL : all models with silver or gold plated silver contacts





CECC : consult factory for details of approved models.

Marking : to order switches marked UL or CECC, please complete above box with desired approval.

Blank : no agency approval required.



A diagram showing a sequence of nodes connected by arrows. The nodes are represented by rectangles of different widths and heights. The sequence starts with a dark grey node, followed by a light grey node, then another light grey node, then a small light grey node, then another small light grey node, then a medium light grey node, then a large light grey node, and finally a node pointing to a box containing '+ U...'.




Cap colours	
Replace last "0" by number	
1	blue
1/4	dark blue
2	black
3	green
4	grey
5	yellow
6	red
7	ivory
7/1	white
9	orange

DRESS NUTS

Chrome plated



For models with Ø 6,35 (1/4) bushing only.



Dress nuts are to be ordered separately.