

Technical data

Reference:	OTe 60/220-240/12 P
For LED modules:	12V LED Modules with respect to the output conditions: BackLED BoxLED
Nominal Voltage:	220 – 240 V _{AC}
Line current, nominal:	0,32 A @ 230V
Mains frequency:	50/60 Hz
Protection Class:	I
Output voltage: (Remark)	12,5V DC Tolerance: ± 0,5V
Output Power:	60W
Rated Power factor:	> 0,9 (full load) @ 230V
Power loss:	< 13W max.
ECG efficiency: (Remark)	> 83 % full load at 230V
Power Loss in no load condition:	< 2 W
Input Voltage: (Remark)	198 – 264 VAC Permitted voltage range
DC Voltage:	No
Inrush current: (Remark)	≤ 35A $t_{width@ 420\mu s}$
Ambient temperature range, t _a :	-25 °C to +55 °C
Max. case temperature at t _c point:	90°C
ECG Lifetime: (Remark)	50.000h at t _a +45 °C and 10% failure rate
Maximum casing temperature in case of fault	120°C

OPTOTRONIC®


OTe 60/220-240/12 P

Constant Voltage LED Power Supply for 12V LED
- Modules

Technical Information

Edition: April 2011
subject to change

Dimmable:	No
No-load proof:	Yes
Short circuit protection:	Automatic, reversible
Overload protection:	Automatic, reversible
Overtemperature protection:	Automatic, manual reset
Cable cross section input side / output side: (Remark)	Input: ~ 0,83 mm ² / Output: ~ 0,83 mm ² Input: 18 AWG / Output: 18 AWG <i>Flexible</i>
Cable length Input side / output side:	~ 33cm / ~ 33cm
Max. cable length – system:	10 m
Geometry (l x b x h):	170 x 53 x 38 mm ³
Mounting hole spacing/length:	163 mm
Mounting hole spacing/width:	35 mm
Weight:	500g
IP Code:	IP65
Suitable for fixtures with protection class:	Class I
ECG outdoor protection against humidity:	PCB fully encapsulated + dust proof metal housing
Safety:	IEC 61347-1, IEC 61347-2-13
Performance:	IEC 62384
Radio interference:	CISPR 15
Harmonic content:	IEC 61000-3-2
Voltage fluctuations:	IEC 61000-3-3
Immunity:	IEC 61547
Surge capability:	L-N: 2kV; L/N – Ground: 4kV;
Galvanic isolation primary/secondary : (Remark)	3,75 kVrms <i>SELV-equivalent</i>
Approvals:	CE

Geometry

$l = 170\text{mm}$, $l_1 = 163\text{mm}$, $b = 53\text{mm}$, $b_1 = 35\text{mm}$, $h = 38\text{mm}$

Ordering information

	EAN 10	EAN 40
OTe 60/220-240/12 P	4008321974457	4008321655318

Installation notes

1. The luminaire manufacturer is responsible for providing the required clearances and creepage distances and also for the protection against electrical shock, especially for the line and load wires.
2. Ground connection of the OTe 60/220-240/12 P is mandatory for safety and EMC reasons. The ground connection could be done either with the input cable or via the housing case. If ground connection is done via the housing case, proper countersunk screws should be used.
3. Ballast losses and LED Module heat radiation can lead to heat accumulation in a complete closed case. Therefore it is necessary to ensure, that the temperature at the measuring point t_c does not exceed the maximum value.

Instruction sheet

Please consult the instruction sheet for further important information on e.g. wire stripping and wiring limitations in system installations. The instruction sheet is enclosed with the device or available upon request.