

Distinctive Characteristics

Available in flat frame and bracketed PC mounting types.

Over-center actuator block and plunger design gives crisp actuation with clear indication of circuit status; this design also diminishes sparking and increases operating life.

Guide interlocked with actuator block prevents window locking and maintains correct plunger alignment to assure contact stability.

Antijamming design protects contacts from damage due to excessive downward force on the actuator.


High internal barriers between poles and insulating sheet between case and actuator block give added protection to contacts.

Specially composed silver alloy contacts for power applications or gold contacts for logic level applications give high contact reliability.


Prominent external insulating barriers increase insulation resistance and dielectric strength.

Epoxy sealed terminals prevent entry of flux, solvents, and other contaminants.

Clinching of frame to case well above base and terminals provides 1,500V dielectric strength.



Actual Size



General Specifications

Electrical Capacity (Resistive Load)

Power Level (code W): 6A @ 125V AC or 3A @ 250V AC

Logic Level (code G): 0.4VA maximum @ 28V AC/DC maximum

(Applicable Range 0.1mA ~ 0.1A @ 20mV ~ 28V)

Logic/Power Level (code A): Combines W & G ratings

Note: Find additional explanation of dual rating & operating range in Supplement section.

Other Ratings

Contact Resistance: 10 milliohms maximum for silver; 20 milliohms maximum for gold

Insulation Resistance: 1,000 megohms minimum @ 500V DC

Dielectric Strength: 1,000V AC minimum between contacts for 1 minute minimum;

1,500V AC minimum between contacts & case for 1 minute minimum

Mechanical Life: 100,000 operations minimum

Electrical Life: 25,000 operations minimum for silver; 50,000 operations minimum for gold

Contact Timing: Nonshorting (break-before-make)

Total Travel: On-None-On circuit .087" (2.2mm); all other circuits .138" (3.5mm)

Materials & Finishes

Actuator: Glass fiber reinforced polyester

Frame: Stainless steel for panel & PCB mount; phosphor bronze with tin plating for bracket mount

Dust Cover: Phosphor bronze with nickel plating

Case: Glass fiber reinforced dialyl phthalate resin (UL94V-0)

Movable Contacts: Silver alloy (code W); copper with gold plating (code G); or silver alloy with gold plating (code A)

Stationary Contacts: Silver capped copper with silver plating (code W); copper with gold plating (code G); or silver alloy with gold plating (code A)

Terminals: Copper or brass with silver or gold plating

Environmental Data

Operating Temp Range: -30°C through +85°C (-22°F through +185°F)

Humidity: 90 ~ 95% humidity for 96 hours @ 40°C (104°F)

Vibration: 10 ~ 55Hz with peak-to-peak amplitude of 1.5mm traversing the frequency range

& returning in 1 minute; 3 right angled directions for 2 hours

Shock: 50G (490m/s²) acceleration (tested in 6 right angled directions, with 5 shocks in each direction)

Processing

Soldering: Wave Soldering recommended (PC Mount). See Profile B in Supplement section.

Manual Soldering: 4 seconds max. @ 390°C max. Panel Mount (F) to be manual soldering only.

Cleaning: These devices are not process sealed. Hand clean locally using alcohol based solution.

See Cleaning Specifications in Supplement section.

Standards & Certifications

Flammability Standards: UL94V-0 rated case



UL Recognized: All Double Throw models recognized at 6A @ 125V AC & 3A @ 250V AC;

UL File No. WOYR2.E44145; add "/U" to end of part number to order UL mark on switch.



C-UL Recognized: All Double Throw models recognized at 6A @ 125V AC & 3A @ 250V AC;


UL File No. WOYR8.E44145; add "/UC" to end of part number to order C-UL mark on switch.



CSA Certified: All Single & Double Throw models certified at 6A @ 125V AC, 3A @ 250V AC, &


0.4VA maximum @ 28V DC; CSA File No. 023535-0-000; add "/C" to end of part number to order CSA mark on switch.

TYPICAL SWITCH ORDERING EXAMPLE





DESCRIPTION FOR TYPICAL ORDERING EXAMPLE





MS12ASG30




POLES & CIRCUITS

		Slide Position			Connected Terminals			Throw & Schematics	
Pole	Model	Left	Center	Right	Left	Center	Right	Note: Terminal numbers are not actually on the switch.	
SP	MS12 MS13	ON ON	NONE OFF	ON ON	2-1	OPEN	2-3	SPDT	
DP	MS22 MS23	ON ON	NONE OFF	ON ON	2-1 5-4	OPEN	2-3 5-6	DPDT	



For 3 Throw (3-On)

		Connected Terminals & Schematics				
Pole	Model	Left	Center	Right	External Connection	
SP	MS20	ON  2-1 5-4	ON  2-1 5-6	ON  2-3 5-6	The SP3T model utilizes a double pole base. External connections must be made during field installation.	

ACTUATORS

A .150" (3.8mm) Wide for Single Pole


.150" (3.8mm) Wide for Double Pole


B .323" (8.2mm) Wide for Double Pole Only


CONTACT MATERIALS & RATINGS



Silver over Silver

Power Level

6A @ 125V AC & 3A @ 250V AC



Gold over Brass or Copper

Logic Level

0.4VA maximum @ 28V AC/DC maximum

Note: Complete explanation of operating range in Supplement section.



Gold over Silver

Power Level or Logic Level

6A @ 125V AC or 0.4VA maximum @ 28V AC/DC maximum

Note: This dual rated option is suitable when two or more identical switches are used in logic and in power circuits within the same application. See Supplement section for complete explanation of dual rating and operating range.


MOUNTING TYPES & TERMINALS

F Panel Mount
(Combines with Solder Lug Terminal 01 only)




Dimension A =
.268" (6.8mm) for on-none-on
.319" (8.1mm) for on-off-on & on-on-on

Maximum Panel Thickness: .197" (5.0mm)



SP or DP with .150" (3.8mm) Actuator



DP only with .323" (8.2mm) Actuator


N Straight PC Mount
(Combines with Straight PC Terminal 03 only)



S Support Bracket Mount
(For Terminals 13, 30, & 40)


Maximum Panel Thickness:

For Straight PC w/Bracket Terminal 13: .197" (5.0mm)
For Angle Mount Terminals 30 & 40: .177" (4.5mm)




01 Solder Lug

The .043" x .079" (1.1mm x 2.0mm) oblong hole accommodates 1 solid 18-ga wire or 2 solid or stranded 20-ga wires.



03 Straight PC




13 Straight PC with Bracket

30 Right Angle PC

40 Vertical PC



TYPICAL SWITCH DIMENSIONS

Solder Lug Terminals




Actuator in LEFT Position

Single Pole






MS12AFW01

Solder Lug Terminals



Double Pole



Actuator in LEFT Position