

COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△					△				
△					△				

APPLICABLE STANDARD				
RATING	OPERATING TEMPERATURE RANGE	-30°C TO +85°C (NOTE 1)	STORAGE TEMPERATURE RANGE	-10°C TO +60°C
	VOLTAGE	250 V	APPLICABLE CONTACT	
	CURRENT	2 A	APPLICABLE CONNECTOR	
			APPLICABLE CABLE	

SPECIFICATIONS

ITEM	TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION				
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	○	○
MARKING	CONFIRMED VISUALLY.		○	○
ELECTRICAL CHARACTERISTICS				
CONTACT RESISTANCE	100 mA (DC OR 1000 Hz).	80 mΩ MAX. (NOTE 2)	○	—
CONTACT RESISTANCE MILLIVOLT LEVEL METHOD.	20 mV MAX. mA (DC OR 1000 Hz).	mΩ MAX.	—	—
INSULATION RESISTANCE	V DC	MΩ MIN.	—	—
VOLTAGE PROOF	V AC FOR 1 min	NO FLASHOVER OR BREAKDOWN.	—	—
MECHANICAL CHARACTERISTICS				
CONTACT INSERTION AND EXTRACTION FORCES	BY STEEL GAUGE.	INSERTION FORCE N MAX. EXTRACTION FORCE N MIN.	—	—
INSERTION AND WITHDRAWAL FORCES	MEASURED BY APPLICABLE CONNECTOR.	INSERTION FORCE N MAX. EXTRACTION FORCE N MIN.	—	—
MECHANICAL OPERATION	30 TIMES INSERTIONS AND EXTRACTIONS	① CONTACT RESISTANCE: 80 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	○	—
VIBRATION	FREQUENCY 10 TO 55 Hz, TOTAL AMPLITUDE 1.5 mm, — mm/s ² AT ≥ 1 FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 10 mΩ. ② CONTACT RESISTANCE: 80 mΩ MAX. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	○	—
SHOCK	490 m/s ² DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 10 mΩ. ② CONTACT RESISTANCE: 80 mΩ MAX. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	○	—
ENVIRONMENTAL CHARACTERISTICS				
DAMP HEAT (STEADY STATE)	EXPOSED AT °C, %, h.	① CONTACT RESISTANCE: mΩ MAX. ② INSULATION RESISTANCE: MΩ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	+	—
RAPID CHANGE OF TEMPERATURE	TEMPERATURE -55-5-35-+85-5-35°C TIME 30-10-15-30-10-15 min UNDER 5 CYCLES.	① CONTACT RESISTANCE: 80 mΩ MAX. ② INSULATION RESISTANCE: 1000 MΩ. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	○	—
RESISTANCE TO SOLDERING HEAT	SOLDER TEMPERATURE, °C FOR IMMERSION, DURATION, s.	NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.	—	—
SOLDERABILITY	SOLDERED AT SOLDER TEMPERATURE, °C FOR IMMERSION DURATION, s.	A NEW UNIFORM COATING OF SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMersed.	—	—

NOTE 2. INCLUDE THE TWO CONTACTS.
(INCLUDE THE CABLE AND 2P 80mm.)

REMARKS NOTE 1 INCLUDE THE TEMPERATURE RISING BY TURNING ON ELECTRICITY. Unless otherwise specified, refer to MIL-STD-1344.	DRAWN T. Miyazaki 94.9.29	DESIGNED T. Miyazaki 94.9.29	CHECKED C. Hanami 94.10.3	APPROVED U. Yamamoto 94.10.5	RELEASED HRS 1029/02 USA
---	---------------------------------	------------------------------------	---------------------------------	------------------------------------	-----------------------------------

Note QT: Qualification Test AT: Assurance Test ○: Applicable Test

HRS HIROSE ELECTRIC CO., LTD.	SPECIFICATION SHEET	PART NO. DF11-XDP-SP1
CODE NO. (OLD) CL	DRAWING NO. ELC4-084801-01	CODE NO. CL543-0609-1 CL543-0611-3

FOR REFERENCE ONLY

Subject to change without notice

TO

INC

COUNT DESCRIPTION OF REVISIONS		BY CHG	DATE	COUNT	DESCRIPTION OF REVISIONS	BY CHG	DATE
1				1			
2				1			
3				1			
4				1			
5				1			
6				1			
7				1			
8				1			

HRS NO.	PART NO.	NUMBER OF CONTACT	A	B
CL543-0609-1	DF11-4DP-SP1	4	6.6	2
CL543-0610-0	DF11-6DP-SP1	6	8.6	4
CL543-0611-3	DF11-8DP-SP1	8	10.6	6

C - C

D - D

FOR REFERENCE ONLY
Subject to change without notice

NO.	MATERIAL	FINISH . REMARKS	DRAWN	DESIGNED	CHECKED	APPROVED	TIN PLATED
2	BRASS						ULS4V-O(BLACK)
1	POLYAMIDE						FINISH . REMARKS

CODE NO. (OLD)	DRAWING NO.	PART NO.
	EDC3-084801-01	DF11-*DP-SP1

SCALE	UNITS	FORM NO.
10 : 1	mm	8

DATE	BY	REMARKS
10/29/02	J. Higuchi	C. Henrich