






CIRCUIT: SPST



NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: $X.X = \pm 0.4$
 $X.XX = \pm 0.25$
3. RATING: 12VDC @ 50mA
4. CONTACT RESISTANCE: $100m\Omega$ MAX.
5. INSULATION RESISTANCE: $100M\Omega$ MIN @100VDC.
- ▲ 6. OPERATING FORCE: $260 \pm 50gf$
- ⑦ 7. TRAVEL: $0.3+0.1/-0.1mm$
8. OPERATING TEMPERATURE: -25°C TO 85°C
9. OPERATING LIFE: 100,000 CYCLES
10. SILVER CONTACTS.
11. SEALED TO IP67
12. ▲ DENOTES CRITICAL PARAMETERS
13. 2002/95/EC (ROHS) COMPLIANT
14. PARTS ARE RADIAL PACKAGED, 1000 PIECES PER PACK. PARTS ARE ZIG-ZAG FOLDED AND 1 SWITCH IS REMOVED AT EVERY FOLD.

B	18734	change travel tol from +.2/- .1	12/8/09	rc
A	18411	New Release	2/18/09	rc
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED



TITLE TL52AF260Q

SCALE 2=1

DATE 1/19/2009

DR	rc
----	----

DWG	P002000
-----	---------

REV
B