


SmartRack 18U Wall-Mount Standard-Depth Rack Enclosure Cabinet

MODEL NUMBER: **SRW18US**



Description

The SRW18US 18U Wall-Mount Rack Enclosure Cabinet is designed to integrate wall-mounting, easy equipment access, and cable management in IT network applications with limited floor space. Ventilated front door and side panels allow generous airflow to keep equipment operating safely. Adjustable rack rails with square mounting holes accommodate up to 18U of standard 19" rackmount equipment. Supports up to 250lbs of equipment. A sturdy hinge between the cabinet and the wall-mount bracket allows the cabinet to swing away from the wall for easy access to equipment and cabling. Top and bottom panels include convenient cutouts for cable routing.

Features

- 18U wall-mounted enclosure
- Adjustable mounting depths from 3" to 20.5" inches
- Heavy duty construction to handle added leverage
- Ventilated front door and side panels for increased airflow
- Hinged cabinet swings away from wall bracket for easy equipment and cable access
- Locking, reversible front door
- Locking, removable side panels
- Top and bottom panel cable access openings
- Fully assembled for quick installation
- Meets all enclosure requirements towards PCI DSS (Payment Card Industry Data Security Standard) Compliance

Specifications

SELECTOR	RACK EQUIPMENT
Selector Type	

Highlights

- 18U with adjustable front and rear vertical rackmount rails
- Hinged cabinet swings away from wall bracket for easy equipment access (swing direction is reversible)
- Locking, reversible front door and locking, removable side panels
- Fully assembled for quick installation
- Meets all enclosure requirements towards PCI DSS (Payment Card Industry Data Security Standard) Compliance
- Interior vertical posts have square holes for cage nuts plus 12-24 threaded mounting holes

Package Includes

- SRW18US Wallmount Rack Enclosure
- (42) M6 screws
- (42) M6 cage nuts
- (42) M6 washers
- (2) Keys
- Owner's Manual

General Info	
Product Group	RACKS
TAA Compliant	No
OVERVIEW	
Style	Wall Mounted
Rack Type	Wall-Mount
PHYSICAL	
Installed Whole System Maximum Rack Depth (in.)	20.5
Installed Whole System Maximum Rack Depth (cm)	52.07
Installed Whole System Minimum Rack Depth (in.)	3
Installed Whole System Minimum Rack Depth (cm)	7.62
Rack Height (U Spaces)	18
Shipping Dimensions (hwd / in.)	41.3 x 25.5 x 23.6
Shipping Dimensions (hwd / cm)	104.9 x 64.77 x 59.9
Shipping Weight (lbs.)	110
Shipping Weight (kg)	49.9
Unit Dimensions (hwd / in.)	35.6 x 23.6 x 21.6
Unit Weight (lbs.)	96
Unit Weight (kg)	43.54
Unit Dimensions (cm)	EXTERNAL DIMENSIONS: 90.42 x 60 x 54.9 (HWD)
Color	Black
Weight Capacity - Stationary (lbs.)	250
Weight Capacity - Stationary (kg)	113.4
Factory Preset Rack Depth (in.)	9.84
Factory Preset Rack Depth (cm)	24.99
Cable Access Hole Measurement (inches)	9.812 x 2.35 (l x w)
Hinged (Swings Away from Wall Bracket)	Yes
SPECIAL FEATURES	
Grounding Lug	Front and Back door frames



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

CERTIFICATIONS

NOM (Mexico)	Tested to NOM (Mexico)
Approvals	EIA-310-D, IEC 60297-3-100, DIN 41494, IP20 Protection Rating, RoHS

WARRANTY

Product Warranty Period (Worldwide)	5-year limited warranty
-------------------------------------	-------------------------

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.