Is Now Part of

ON Semiconductor®

To learn more about ON Semiconductor, please visit our website at
www.onsemi.com

Please note: As part of the Fairchild Semiconductor integration, some of the Fairchild orderable part numbers will need to change in order to meet ON Semiconductor's system requirements. Since the ON Semiconductor product management systems do not have the ability to manage part nomenclature that utilizes an underscore (_), the underscore (_) in the Fairchild part numbers will be changed to a dash (-). This document may contain device numbers with an underscore (_). Please check the ON Semiconductor website to verify the updated device numbers. The most current and up-to-date ordering information can be found at www.onsemi.com. Please email any questions regarding the system integration to Fairchild_questions@onsemi.com.

FAIRCHILD SEMICONDUCTOR™

October 1996
Revised June 2005

74VCX16245
Low Voltage 16-Bit Bidirectional Transceiver with 3.6V Tolerant Inputs and Outputs

General Description

The VCX16245 contains sixteen non-inverting bidirectional buffers with 3-STATE outputs and is intended for bus oriented applications. The device is byte controlled. Each byte has separate 3-STATE control inputs which can be shorted together for full 16-bit operation. The T/$\overline{R}$ inputs determine the direction of data flow through the device. The $\overline{OE}$ inputs disable both the A and B ports by placing them in a high impedance state.

The 74VCX16245 is designed for low voltage (1.2V to 3.6V) V_{CC} applications with I/O compatibility up to 3.6V.

The 74VCX16245 is fabricated with an advanced CMOS technology to achieve high speed operation while maintaining low CMOS power dissipation.

Features

- 1.2V to 3.6V V_{CC} supply operation
- 3.6V tolerant inputs and outputs
- t_{PD}
  2.5 ns max for 3.0V to 3.6V V_{CC}
- Power-off high impedance inputs and outputs
- Supports live insertion/withdrawal (Note 1)
- Static Drive (I_{OH}/I_{OL})
  ±24 mA @ 3.0V V_{CC}
- Uses proprietary noise/EMI reduction circuitry
- Latchup performance exceeds 300 mA
- ESD performance:
  Human body model > 2000V
  Machine model >200V
- Also packaged in plastic Fine-Pitch Ball Grid Array (FBGA)

Note 1: To ensure the high-impedance state during power up or power down, $\overline{OE}$ should be tied to V_{CC} through a pull-up resistor; the minimum value of the resistor is determined by the current-sourcing capability of the driver.

Ordering Code:

Order Number	Package Number	Package Description
74VCX16245G (Note 2)(Note 3)	BGA54A	54-Ball Fine-Pitch Ball Grid Array (FBGA), JEDEC MO-205, 5.5mm Wide
74VCX16245MTD (Note 3)	MTD48	48-Lead Thin Shrink Small Outline Package (TSSOP), JEDEC MO-153, 6.1mm Wide

Note 2: Ordering code "G" indicates Trays.

Note 3: Devices also available in Tape and Reel. Specify by appending the suffix letter "X" to the ordering code.

Logic Symbol



Connection Diagrams

Pin Assignment of TSSOP



Pin Assignment for FBGA



(Top Thru View)

Pin Descriptions

Pin Names	Description
$\overline{OE}_n$	Output Enable Input (Active LOW)
$T/\overline{R}_n$	Transmit/Receive Input
A_0–A_{15}	Side A Inputs or 3-STATE Outputs
B_0–B_{15}	Side B Inputs or 3-STATE Outputs
NC	No Connect

FBGA Pin Assignments

	1	2	3	4	5	6
A	B_0	NC	$T/\overline{R}_1$	$\overline{OE}_1$	NC	A_0
B	B_2	B_1	NC	NC	A_1	A_2
C	B_4	B_3	V_{CC}	V_{CC}	A_3	A_4
D	B_6	B_5	GND	GND	A_5	A_6
E	B_8	B_7	GND	GND	A_7	A_8
F	B_{10}	B_9	GND	GND	A_9	A_{10}
G	B_{12}	B_{11}	V_{CC}	V_{CC}	A_{11}	A_{12}
H	B_{14}	B_{13}	NC	NC	A_{13}	A_{14}
J	B_{15}	NC	$T/\overline{R}_2$	$\overline{OE}_2$	NC	A_{15}

Truth Tables

Inputs		Outputs
$\overline{OE}_1$	$T/\overline{R}_1$	
L	L	Bus B_0–B_7 Data to Bus A_0–A_7
L	H	Bus A_0–A_7 Data to Bus B_0–B_7
H	X	HIGH Z State on A_0–A_7, B_0–B_7

Inputs		Outputs
$\overline{OE}_2$	$T/\overline{R}_2$	
L	L	Bus B_8–B_{15} Data to Bus A_8–A_{15}
L	H	Bus A_8–A_{15} Data to Bus B_8–B_{15}
H	X	HIGH Z State on A_8–A_{15}, B_8–B_{15}

H = HIGH Voltage Level
L = LOW Voltage Level
X = Immaterial (HIGH or LOW, inputs and I/O's may not float)
Z = High Impedance

Logic Diagram



Absolute Maximum Ratings (Note 4)

Supply Voltage (V_{CC})	−0.5V to +4.6V
DC Input Voltage (V_I)	−0.5V to +4.6V
Output Voltage (V_O)	
Outputs 3-STATE	−0.5V to +4.6V
Outputs Active (Note 5)	−0.5 to V_{CC} + 0.5V
DC Input Diode Current (I_{IK}) V_I < 0V	−50 mA
DC Output Diode Current (I_{OK})	
V_O < 0V	−50 mA
V_O > V_{CC}	+50 mA
DC Output Source/Sink Current (I_{OH}/I_{OL})	±50 mA
DC V_{CC} or Ground Current per Supply Pin (I_{CC} or Ground)	±100 mA
Storage Temperature Range (T_{STG})	−65°C to +150°C

Recommended Operating Conditions (Note 6)

Power Supply	
Operating	1.2V to 3.6V
Input Voltage	−0.3V to 3.6V
Output Voltage (V_O)	
Output in Active States	0V to V_{CC}
Output in 3-STATE	0.0V to 3.6V
Output Current in I_{OH}/I_{OL}	
V_{CC} = 3.0V to 3.6V	±24 mA
V_{CC} = 2.3V to 2.7V	±18 mA
V_{CC} = 1.65V to 2.3V	±6 mA
V_{CC} = 1.4V to 1.6V	±2 mA
V_{CC} = 1.2V	±100 μA
Free Air Operating Temperature (T_A)	−40°C to +85°C
Minimum Input Edge Rate ($\Delta t/\Delta V$)	
V_{IN} = 0.8V to 2.0V, V_{CC} = 3.0V	10 ns/V

Note 4: The "Absolute Maximum Ratings" are those values beyond which the safety of the device cannot be guaranteed. The device should not be operated at these limits. The parametric values defined in the "Electrical Characteristics" table are not guaranteed at the Absolute Maximum Ratings. The Recommended Operating Conditions tables will define the conditions for actual device operation.

Note 5: I_O Absolute Maximum Rating must be observed.

Note 6: Floating or unused pin (inputs or I/O's) must be held HIGH or LOW.

DC Electrical Characteristics

Symbol	Parameter	Conditions	V_{CC} (V)	Min	Max	Units
V_{IH}	HIGH Level Input Voltage		2.7 - 3.6	2.0		
			2.3 - 2.7	1.6		
			1.65 - 2.3	0.65 x V_{CC}		V
			1.4 - 1.6	0.65 x V_{CC}		
			1.2	0.65 x V_{CC}		
V_{IL}	LOW Level Input Voltage		2.7 - 3.6		0.8	
			2.3 - 2.7		0.7	
			1.65 - 2.3		0.35 x V_{CC}	V
			1.4 - 1.6		0.35 x V_{CC}	
			1.2		0.05 x V_{CC}	
V_{OH}	HIGH Level Output Voltage	I_{OH} = −100 μA	2.7 - 3.6	V_{CC} - 0.2		
		I_{OH} = −12 mA	2.7	2.2		
		I_{OH} = −18 mA	3.0	2.4		
		I_{OH} = −24 mA	3.0	2.2		
		I_{OH} = −100 μA	2.3 - 2.7	V_{CC} - 0.2		
		I_{OH} = −6 mA	2.3	2.0		
		I_{OH} = −12 mA	2.3	1.8		V
		I_{OH} = −18 mA	2.3	1.7		
		I_{OH} = −100 μA	1.65 - 2.3	V_{CC} - 0.2		
		I_{OH} = −6 mA	1.65	1.25		
		I_{OH} = −100 μA	1.4 - 1.6	V_{CC} - 0.2		
		I_{OH} = −2 mA	1.4	1.05		
		I_{OH} = −100 μA	1.2	V_{CC} - 0.2		

DC Electrical Characteristics (Continued)

Symbol	Parameter	Conditions	V_{CC} (V)	Min	Max	Units
V_{OL}	LOW Level Output Voltage	I_{OL} = 100 μA	2.7 - 3.6		0.2	V
		I_{OL} = 12 mA	2.7		0.4	
		I_{OL} = 18 mA	3.0		0.4	
		I_{OL} = 24 mA	3.0		0.55	
		I_{OL} = 100 μA	2.3 - 2.7		0.2	
		I_{OL} = 12 mA	2.3		0.4	
		I_{OL} = 18 mA	2.3		0.6	
		I_{OL} = 100 μA	1.65 - 2.3		0.2	
		I_{OL} = 6 mA	1.65		0.3	
		I_{OL} = 100 μA	1.4 - 1.6		0.2	
		I_{OL} = 2 mA	1.4		0.35	
		I_{OL} = 100 μA	1.2		V_{CC} - 0.1	
I_I	Input Leakage Current	0V ≤ V_I ≤ 3.6V	1.2 - 3.6		±5.0	μA
I_{OZ}	3-STATE Output Leakage	0V ≤ V_O ≤ 3.6V V_I = V_{IH} or V_{IL}	1.2 - 3.6		±10	μA
I_{OFF}	Power Off Leakage Current	0V ≤ (V_I, V_O) ≤ 3.6V	0		10	μA
I_{CC}	Quiescent Supply Current	V_I = V_{CC} or GND	1.2 - 3.6		20	μA
		V_{CC} ≤ (V_I, V_O) ≤ 3.6V (Note 7)	1.2 - 3.6		±20	
ΔI_{CC}	Increase in I_{CC} per Input	V_{IH} = V_{CC} − 0.6V	2.7 - 3.6		750	μA

Note 7: Outputs disabled or 3-STATE only.

AC Electrical Characteristics (Note 8)

Symbol	Parameter	Conditions	V_{CC}	T_A = −40°C to +85°C		Units	Figure Number
			(V)	Min	Max		
t_{PHL} t_{PLH}	Propagation Delay	C_L = 30 pF, R_L = 500Ω	3.3 ± 0.3	0.8	2.5	ns	Figures 1, 2
			2.5 ± 0.2	1.0	3.0		
			1.8 ± 0.15	1.0	6.0		
		C_L = 15 pF, R_L = 2kΩ	1.5 ± 0.1	1.0	12.0		Figures 5, 6
			1.2	1.5	30		
t_{PZL} t_{PZH}	Output Enable Time	C_L = 30 pF, R_L = 500Ω	3.3 ± 0.3	0.8	3.8	ns	Figures 1, 3, 4
			2.5 ± 0.2	1.0	4.9		
			1.8 ± 0.15	1.5	9.3		
		C_L = 15 pF, R_L = 2kΩ	1.5 ± 0.1	1.0	18.6		Figures 5, 7, 8
			1.2	1.5	46.5		
t_{PLZ} t_{PHZ}	Output Disable Time	C_L = 30 pF, R_L = 500Ω	3.3 ± 0.3	0.8	3.7	ns	Figures 1, 3, 4
			2.5 ± 0.2	1.0	4.2		
			1.8 ± 0.15	1.5	7.6		
		C_L = 15 pF, R_L = 2kΩ	1.5 ± 0.1	1.0	15.2		Figures 5, 7, 8
			1.2	1.5	38		
t_{OSHL} t_{OSLH}	Output to Output Skew (Note 9)	C_L = 30 pF, R_L = 500Ω	3.3 ± 0.3		0.5	ns	
			2.5 ± 0.2		0.5		
			1.8 ± 0.15		0.75		
		C_L = 15 pF, R_L = 2kΩ	1.5 ± 0.1		1.5		
			1.2		1.5		

Note 8: For C_L = 50pF, add approximately 300ps to the AC maximum specification.

Note 9: Skew is defined as the absolute value of the difference between the actual propagation delay for any two separate outputs of the same device. The specification applies to any outputs switching in the same direction, either HIGH-to-LOW (t_{OSHL}) or LOW-to-HIGH (t_{OSLH}).

Dynamic Switching Characteristics

Symbol	Parameter	Conditions	V_{CC} (V)	$T_A = +25°C$ Typical	Units
V_{OLP}	Quiet Output Dynamic Peak V_{OL}	C_L = 30 pF, $V_{IH} = V_{CC}$, V_{IL} = 0V	1.8	0.25	V
			2.5	0.6	
			3.3	0.8	
V_{OLV}	Quiet Output Dynamic Valley V_{OL}	C_L = 30 pF, $V_{IH} = V_{CC}$, V_{IL} = 0V	1.8	−0.25	V
			2.5	−0.6	
			3.3	−0.8	
V_{OHV}	Quiet Output Dynamic Valley V_{OH}	C_L = 30 pF, $V_{IH} = V_{CC}$, V_{IL} = 0V	1.8	1.5	V
			2.5	1.9	
			3.3	2.2	

Capacitance

Symbol	Parameter	Conditions	$T_A = +25°C$ Typical	Units
C_{IN}	Input Capacitance	V_{CC} = 1.8V, 2.5V, or 3.3V, V_I = 0V or V_{CC}	6	pF
$C_{I/O}$	Output Capacitance	V_I = 0V, or V_{CC}, V_{CC} = 1.8V, 2.5V or 3.3V	7	pF
C_{PD}	Power Dissipation Capacitance	V_I = 0V or V_{CC}, F = 10 MHz, V_{CC} = 1.8V, 2.5V or 3.3V	20	pF

AC Loading and Waveforms (V_{CC} 3.3V ± 0.3V to 1.8V ± 0.15V)



FIGURE 1. AC Test Circuit

TEST	SWITCH
t_{PLH}, t_{PHL}	Open
t_{PZL}, t_{PLZ}	6V at V_{CC} = 3.3 ± 0.3V; V_{CC} x 2 at V_{CC} = 2.5 ± 0.2V; 1.8V ± 0.15V
t_{PZH}, t_{PHZ}	GND



FIGURE 2. Waveform for Inverting and Non-inverting Functions



FIGURE 3. 3-STATE Output High Enable and Disable Times for Low Voltage Logic



FIGURE 4. 3-STATE Output Low Enable and Disable Times for Low Voltage Logic

Symbol	V_{CC}		
	3.3V ± 0.3V	2.5V ± 0.2V	1.8V ± 0.15V
V_{mi}	1.5V	V_{CC}/2	V_{CC}/2
V_{mo}	1.5V	V_{CC}/2	V_{CC}/2
V_X	V_{OL} + 0.3V	V_{OL} + 0.15V	V_{OL} + 0.15V
V_Y	V_{OH} − 0.3V	V_{OH} − 0.15V	V_{OH} − 0.15V

AC Loading and Waveforms (V_{CC} 1.5V ± 0.1V to 1.2V)



TEST	SWITCH
t_{PLH}, t_{PHL}	Open
t_{PZL}, t_{PLZ}	V_{CC} x 2 at V_{CC} = 1.5 ± 0.1V

FIGURE 5. AC Test Circuit



FIGURE 6. Waveform for Inverting and Non-Inverting Functions



FIGURE 7. 3-STATE Output High Enable and Disable Times for Low Voltage Logic



FIGURE 8. 3-STATE Output Low Enable and Disable Times for Low Voltage Logic

Symbol	V_{CC}
	1.5V ± 0.1V
V_{mi}	$V_{CC}/2$
V_{mo}	$V_{CC}/2$
V_X	V_{OL} + 0.1V
V_Y	V_{OH} − 0.1V

Physical Dimensions inches (millimeters) unless otherwise noted



NOTES:

A. THIS PACKAGE CONFORMS TO JEDEC M0-205
B. ALL DIMENSIONS IN MILLIMETERS
C. LAND PATTERN RECOMMENDATION: NSMD (Non Solder Mask Defined)
.35MM DIA PADS WITH A SOLDERMASK OPENING OF .45MM CONCENTRIC TO PADS
D. DRAWING CONFORMS TO ASME Y14.5M-1994

BGA54ArevD

54-Ball Fine-Pitch Ball Grid Array (FBGA), JEDEC MO-205, 5.5mm Wide
Package Number BGA54A

Physical Dimensions inches (millimeters) unless otherwise noted (Continued)



NOTES:

A. CONFORMS TO JEDEC REGISTRATION MO-153, VARIATION ED, DATE 4/97.

B. DIMENSIONS ARE IN MILLIMETERS.

C. DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH, AND TIE BAR EXTRUSIONS.

D. DIMENSIONS AND TOLERANCES PER ANSI Y14.5M, 1982.

MTD48REVC

48-Lead Thin Shrink Small Outline Package (TSSOP), JEDEC MO-153, 6.1mm Wide
Package Number MTD48

LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury to the user.
2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

www.fairchildsemi.com

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:
Literature Distribution Center for ON Semiconductor
19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA
Phone: 303−675−2175 or 800−344−3860 Toll Free USA/Canada
Fax: 303−675−2176 or 800−344−3867 Toll Free USA/Canada
Email: orderlit@onsemi.com

N. American Technical Support: 800−282−9855 Toll Free USA/Canada
Europe, Middle East and Africa Technical Support:
Phone: 421 33 790 2910
Japan Customer Focus Center
Phone: 81−3−5817−1050

ON Semiconductor Website: **www.onsemi.com**

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative