



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

| PANDUIT P/N | WEIGHT                             |
|-------------|------------------------------------|
| NKPP24P     | .49 LB/10 PCS<br>(220.9 g/EACH PC) |

1.04  
A [26.3]



NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.
4. THE PATCH PANEL IS DESIGNED FOR MOUNTING TO 19" UNIVERSAL RACKS.
5. PART INCLUDES:
  - 1- PANEL ASSEMBLY
  - 4- LABEL COVERS
  - 4- LABELS
  - 1- SCREW KIT (INCLUDES FOUR #12-24 SCREWS)
  - 1- SCREW KIT (INCLUDES FOUR M6 SCREWS)
6. LABELS ARE PRE-NUMBERED (1-24) WITH BLANK SIDE FOR CUSTOM LABELING.

|                  |                   |           |
|------------------|-------------------|-----------|
| MODEL FILENAME   | 10M163AB/00       | SIZE<br>A |
| DRAWING FILENAME | 10M163AB_DC02/00B |           |

NETKEY 24 PORT ALL MOLDED MODULAR  
PATCH PANEL CUSTOMER DRAWING

**PANDUIT**<sup>®</sup>  
TINLEY PARK, IL 60487

I.I. NUMBER  
N/A


PRODUCT SPEC/ PKG SPEC  
N/A

ASSY METHOD/ TEST METHOD  
N/A

SCALE  
NONE

PART NO.  
NKPP24P

DRAWING NO.  
10M163AB-02



THIRD ANGLE  
PROJECTION

ALL DIMENSIONS ARE GIVEN IN INCHES,  
UNLESS OTHERWISE SPECIFIED.  
DIMENSIONAL TOLERANCES ARE:  
(.X) ± (.XXX) ± .010(.3)  
(.XX) ± .031(.8) ANGLES ±

DRAWN BY  
BJN

DATE  
12-28-10

CHK'D  
JSP

REVIEW DRAWING NUMBERS

MAT'L  
BASE- REINFORCED PBT  
COVER- ABS

| REV | DATE     | BY  | CHK | DESCRIPTION                    | ECN        | R | CUST | SUP | OTH |
|-----|----------|-----|-----|--------------------------------|------------|---|------|-----|-----|
| I   | 1-21-11  | BJN | JSP | A. ADDED DIMENSION TO TOP VIEW | 0M163AB-02 |   | mmr  |     |     |
| R   | 12-28-10 | BJN | JSP | RELEASED TO PRODUCTION         | 0M163AB-02 |   | MMR  |     |     |