

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

75710-3208

Status:

Active

Overview:

GbX I-Trac™ Backplane Connector System

Description:

GbX I-Trac™ Right-Angle Daughtercard Module, 1.85mm by 3.70mm Pitch, Left Guide, 11 Rows, 8 Columns, 176 Circuits, Lead-Free, Polarization Key B

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Test Summary TS-75710-998 (PDF)

Agency Certification

UL

E29179

General

Product Family

Backplane Connectors

Series

75710

Application

Coplanar, Daughtercard

Component Type

PCB Receptacle

Overview

GbX I-Trac™ Backplane Connector System

Product Name

GbX I-Trac™

Style

N/A

UPC

884982248946

Physical

Circuits (Loaded)

176

Circuits (maximum)

176

Color - Resin

Black

Durability (mating cycles max)

200

First Mate / Last Break

No

Flammability

94V-0

Guide to Mating Part

Yes

Keying to Mating Part

Yes

Material - Metal

High Performance Alloy (HPA)

Material - Plating Mating

Gold

Material - Plating Termination

Tin

Material - Resin

High Temperature Thermoplastic

Net Weight

26.613/g

Number of Columns

8

Number of Pairs

Open Pin Field

Number of Rows

11

Orientation

Right Angle

PC Tail Length

2.00mm

PCB Locator

Yes

PCB Retention

Yes

PCB Thickness - Recommended

1.60mm

Packaging Type

Tray

Pitch - Mating Interface

1.85mm, 3.70mm

Pitch - Termination Interface

1.00mm, 2.70mm

Plating min - Mating

0.762µm

Plating min - Termination

0.762µm

Polarized to PCB

Yes

Stackable

No

Surface Mount Compatible (SMC)

Yes

Temperature Range - Operating

-55°C to +80°C

Termination Interface: Style

Through Hole - Compliant Pin



Series
image - Reference only

EU RoHS

ELV and RoHS
Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
75710Series

Mates With
75705 GbX I-Trac™ Vertical Header Module. 75910 GbX I-Trac™ Right Angle Header Module

Use With
78234 GbX I-Trac™ Right Angle Power Header. 76153 Pirate Cannon Wide Guide Module

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Press-In Tool for Right Angle Receptacle and	0622018618

Electrical

Current - Maximum per Contact	1A
Data Rate	12.0 Gbps
Shield Type	N/A
Shielded	No
Voltage - Maximum	120V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Sales Drawing	SD-75710-002
Test Summary	TS-75710-998

Header 11-Row, 8-Column	
Daughter Card	<u>0622023000</u>
Signal Module	
Removal Tool	

This document was generated on 09/05/2013

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION