

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

,19



(C) COPYRIGHT 19

BY AMP INCORPORATED. ALL RIGHTS RESERVED.


LOC	DIST	REVISIONS					
CM	53	P	LTR	DESCRIPTION	DATE	DWN	APVD
			S	REVISED PER EC 063B-0079-00	21-FEB-00	KW	SR

1. WIRE RANGE: 20-14 AWG (0.5-2MM²).

INSULATION RANGE: .125 MAX.



SECTION A-A
SCALE 10:1



SECTION B-B
SCALE 10:1

.050	1.27	.139	3.53	.180	4.57	-	-
.043	1.09	.135	3.43	.165	4.19	-	-
.035	0.89	.130	3.30	.156	3.96	-	-
.018	0.46	.125	3.18	.155	3.94	.770	19.56
.015	0.38	.115	2.92	.152	3.86	.750	19.05
.005	0.13	.063	1.60	.148	3.76	.189	4.80
IN	MM	IN	MM	IN	MM	IN	MM
CONVERSION TABLE							

METRIC

PRELIMINARY	TIN	.018 PH BRZ	61085-3
	TIN	.018 BRASS	61085-1
	FINISH	MATERIAL	PART NO
THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN J. HUFFMAN CHK R. SWING APVD C. MARTIN	12-07-95 12-07-95 12-07-95
DIMENSIONS: mm [INCHES]		NAME SOCKET, .156 MATE-N-LOK™	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ± .005 4 PLC ±- ANGLES ±0°30' FINISH -		APPLICATION SPEC - WEIGHT -	SIZE A2
MATERIAL -		CAGE CODE 00779	DRAWING NO C-61085
CUSTOMER DRAWING		SCALE 5:1	SHEET 1 OF 1 REV 5