








SECTION A-A
BACKGROUND OMITTED



BACKGROUND OMITTED

NOTES:

1. CRIMP ACCEPTS .18 TO .20 GA. WIRE WITH (.279) .110 MAX. INSUL. DIA. WHEN USED WITH 2574 CONNECTOR. (.254) .100 MAX. INSUL. DIA. WHEN USED WITH 2139 CONNECTOR
2. CRIMP ACCEPTS (.300) .118 MAX. INSUL. DIA. WITH SPECIAL TOOLING.
3. DIMENSIONS GIVEN ACROSS CENTERLINES ARE SYMMETRICAL ABOUT THOSE CENTERLINES WITHIN HALF THE TOTAL TOLERANCE.
4. (.86+.05)/.034+.002 IS AN OPTIONAL DESIGN.
5. THIS PART CONFORMS TO PRODUCT SPEC. 08-50.



CHANGE TO MEIO EC NO: LCP2005-0930 DESKAPARTNO: 2004/11/16 CHKD: SANEK 2004/11/02 APPR: MARCUS 2004/11/02 AM	QUALITY SYMBOLS ▼=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED): mm INCH 4 PLACES ±--- ±--- 3 PLACES ±--- ±.005 2 PLACES ±0.13 ±.010 1 PLACE ±0.25 ±--- ANGULAR ±1/2°	DIMENSION STYLE IN/MM		SCALE	DESIGN UNITS INCH	THIRD ANGLE PROJECTION
			DRAWN BY DATE COMSTOCK 11/29/88	TITLE TERMINAL DBL CANTILEVER KK CRIMP TYPE BIFURCATED			
			CHECKED BY DATE PATEL 11/29/88	MOLEX MOLEX INCORPORATED			
			APPROVED BY DATE LENZ 11/29/88	MATERIAL NO. DOCUMENT NO. SHEET NO. SEE CHART SD-2878 1 OF 2			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE D THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					

	20	19	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	
	2878-A-A(*)*			2878-B-A(*)*			2878-A-B(*)*														
	PART NO.	ENG. NO.		PART NO.	ENG. NO.		PART NO.	ENG. NO.		PART NO.	ENG. NO.		PART NO.	ENG. NO.		PART NO.	ENG. NO.		PART NO.	ENG. NO.	
	08-50-0115	2878-A-A(P909)B					08-55-0138	2878-A-B(555)B													
	08-50-0116	2878-A-A(P909)L						2878-A-B(555)L													
				08-52-0126	2878-B-A(P909)B																
				08-52-0127	2878-B-A(P909)L																
				08-65-0118	2878-B-A(555)B																
				08-65-0119	2878-B-A(555)L																
				08-58-0127	2878-B-A(550)B																
				08-58-0128	2878-B-A(550)L																