


Halogen Lamps



Specification Table

Volts	Watts	MOL Inches (mm)	MOD Inches (mm)	Filament	Base	Lumens	Colour Temperature Degree K	Average Life (Hours)	Rating at 120V (Hours)	Beam Angle	Part Number
PAR 20											
130	50	3.25 (82.6)	2.56 (65)	CC-8	E26	550	2,800	2,000	5,000	32	14067
PAR 30											
130	50	3.63 (92.1)	3.82 (9)	CC-8	E26	660	2,800	2,000	5,000	42	14073
130	75					1,100					14079
PAR 30 (Long Neck)											
130	50	4.69 (119.1)	3.82 (97)	CC-8	E26	660	2,800	2,000	5,000	25	14107
130	75					1,100				38	14123
PAR 38											
120	45	5.31 (135)	5.32 (135)	CC-8	E26	520	2,800	2,000	---	32	14053
120	90					1,270	2,900		---		14061
130	45					520	2,800		5,000		14085
130	90					1,270	2,900		5,000		14093

Dimensions : Inches (Millimetres)

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.