




D




20.70 MAX





LOC		DIST		REVISIONS					
CM		00		REV	DESCRIPTION	DATE	DWN	APVD	
				AK2	REVISED PER ECO-11-004587	11MAR11	RK	HMR	
				AL	REVISED PER ECR-14-016405	07APR2015	AV	DZ	

1. MATES WITH APPROPRIATE UNIVERSAL MATE-N-LOK™ PLUG.
2. RECOMMENDED PANEL THICKNESS 0.76 - 2.29.
3. PANEL MUST BE PUNCHED SO THAT THE HOUSING ENTERS THE PANEL IN THE SAME DIRECTION AS THE PUNCH.
4. OPTIONAL FOR KEYING HOUSING IN PANEL.
5. CIRCUIT NUMBER 1 LOCATION.
6. DIMENSION REPRESENTS POTENTIAL MAXIMUM GROWTH DUE TO MOISTURE ABSORPTION.
7. FOUR RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION. NO RIBS OR SIX RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION, OPTIONAL.
8. UNDERWRITERS RECOGNIZED COMPONENT LOGO AND CSA CERTIFICATION LOGO TO BE LOCATED ONCE EACH ON SIDE OF HOUSING.
9. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

DETAIL A
OPTIONAL CONSTRUCTIONS




25.91^{+0.13}_{-0.25}




RECOMMENDED PANEL CUT OUT

3-DIMENSIONAL MODEL
NTS



6.35	.250	—	—
4.45	.175	27.43	1.080
2.79	.110	26.43	1.041
2.54	.100	25.91	1.020
2.29	.090	20.70	.815
0.76	.030	20.32	.800
0.38	.015	12.19	.480
0.25	.010	8.13	.320
0.13	.005	6.99	.275
MM	IN	MM	IN
CONVERSION TABLE			








9 SUPERSEDED BY 1-480707-0	9 OBSOLETE	BLACK	1-480707-9
		GRAY	1-480707-8
		BLUE	1-480707-6
		GREEN	1-480707-5
		YELLOW	1-480707-4
		ORANGE	1-480707-3
		RED	1-480707-2
		BROWN	1-480707-1
		NATURAL	1-480707-0


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER 29JUL04	NAME	
DIMENSIONS: mm		CHK S. RIDGILL 29JUL04	CAP, 9 CIRCUIT, UNIVERSAL MATE-N-LOK(TM)	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0. PLC ± - 1. PLC ± - 2. PLC ± 0.13 3. PLC ± - 4. PLC ± - ANGLES ± 0°30' FINISH -		APVD S. RIDGILL 29JUL04	RESTRICTED TO	
MATERIAL NYLON, UL94V-2		PRODUCT SPEC	SIZE A1	
		APPLICATION SPEC	CAGE CODE 00779	
		WEIGHT	DRAWING NO 480707	
		CUSTOMER DRAWING		SCALE 4:1
		SHEET 1 OF 2		REV AL

LOC	DIST	REVISIONS				
CM	00	REV	LTR	DESCRIPTION	DATE	DWN
		—		SEE SHEET 1	—	—

1. STAMP NUMBERS 3.18 HIGH AT WIRE END OF HOUSING (12 POINT DAVID TYPE);CLARIFICATION MARKS UNDER THE 6 & 9.
2. CHARACTERS TO BE STAMPED ON HOUSING IN A MANNER AS TO BE READ FROM WIRE END ONLY.
3. VIOLET,BLACK,BROWN,AND BLUE COLORED BLOCKS TO BE STAMPED WITH WHITE CHARACTERS. ALL OTHER COLORED BLOCKS TO BE STAMPED WITH BLACK CHARACTERS.



5.08	.200	—	—
4.70	.185	27.43	1.080
3.18	.125	25.91	1.020
0.38	.015	20.70	.815
0.25	.010	20.32	.800
0.13	.005	8.13	.320
MM	IN	MM	IN
CONVERSION TABLE			



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER	29JUL04	NATURAL		2-480707-0
		CHK S. RIDGILL	29JUL04	COLOR		PART NO
		APP'D S. RIDGILL	29JUL04	NAME		TE Connectivity
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		CAP, 9 CIRCUIT, UNIVERSAL MATE-N-LOK(TM)
		0. PLC ± —		APPLICATION SPEC		SIZE
		1. PLC ± —		WEIGHT		CAGE CODE
		2. PLC ± 0.13				DRAWING NO
		3. PLC ± —				RESTRICTED TO
		4. PLC ± —				
		ANGLES ± 0°30'				
MATERIAL NYLON, UL94V-2		FINISH —		CUSTOMER DRAWING		SCALE
						4:1
						SHEET
						2
						OF
						2
						REV
						AL