

Types 380L, 382L, 380LX & 382LX, 85 °C High-Capacitance Snap-In

2-pin Types: 380L and 380LX. 4-pin or 5-pin Types: 382L and 382LX



The excellent value of Type 380L/LX capacitors finds application in switching power supply input and output circuits and even motor drives where the high surface area of multiple units in parallel approaches the ripple capability of our Type 520C computer-grade capacitor. Type 380LX delivers more capacitance per can size while Type 380L available in the largest case sizes gives lower ESR for the same capacitance. Types 382L and 382LX give the choice of 4 or 5 leads for stable, reverse proof mounting.

Highlights

- Latest available ratings, worldwide
- Top performance in power supplies and motor drives
- Big selection of 46 case sizes
- 2, 4 and 5 leads available

Specifications

Operating Temperature:	–40 °C to 85 °C up to 300 V, –25 °C to 85 °C ≥315 V
Rated Voltage:	16 Vdc to 500 Vdc
Capacitance:	33 µF to 270,000 µF ±20%
Leakage Current:	$\leq 3\sqrt{CV}$ µA at 5 min.

Ripple Current Multipliers:

Ambient Temperature

45 °C	60 °C	70 °C	85 °C
1.5	1.4	1.3	1.0

Frequency

	50 Hz	60 Hz	120 Hz	500 Hz	2 kHz	10 kHz & up
16-100 Vdc	0.93	0.95	1.00	1.05	1.08	1.15
160-450 Vdc	0.75	0.80	1.00	1.20	1.25	1.40


EIA Ripple Life:	3,000 h @ full load at +85 °C per EIA IS-749 ΔCapacitance ±20% ESR 150% of limit DCL 100% of limit
Load Life Test:	3,000 h @ full load at +85 °C ΔCapacitance ±20% ESR 200% of limit DCL 100% of limit
Shelf Life:	1,000 h @ 85 °C, capacitance, ESR and DCL, initial requirements
Vibration:	10 to 55 Hz, 0.06" and 10 g max, 2 h in each plane

Types 380L, 382L, 380LX & 382LX, 85 °C High-Capacitance Snap-In

Outline Drawings


Two Pins

380L/LX (22 through 40 mm diameter)




Four Pins

382L/LX (35 and 40 mm diameter)




Five Pins

382L/382LX (40 and 50 mm diameter)



Terminal	Connection	
	40 mm Dia.	50 mm Dia.
A	dummy	negative (-)
B	dummy	dummy
C	positive (+)	positive (+)
D	dummy	positive (+)
-	negative (-)	negative (-)



Type	P	P ₁	W	W ₁
V	3.75±0.1	0.6 min.	1.5±0.1	0.7

Notes:

* Use dummy terminals for mechanical support only. Make no electrical connection because they resistively connect through the electrolyte to the negative terminal.

** Safety Vent may be on the bottom or on the side of the can.

Types 380L, 382L, 380LX & 382LX, 85 °C High-Capacitance Snap-In

Insulated Case Dimensions

Case Code	DIAMETER "D"		LENGTH "L"		Typical Weight (grams)
	mm	inches	mm	inches	
H20	22	0.87	20	0.79	14
H01	22	0.87	25	0.98	16
H02	22	0.87	30	1.18	19
H03	22	0.87	35	1.38	22
H04	22	0.87	40	1.57	24
H45	22	0.87	45	1.77	28
H05	22	0.87	50	1.97	31
J20	25	0.98	20	0.79	16
J01	25	0.98	25	0.98	20
J02	25	0.98	30	1.18	24
J03	25	0.98	35	1.38	27
J04	25	0.98	40	1.57	31
J45	25	0.98	45	1.77	35
J05	25	0.98	50	1.97	38
K20	30	1.18	20	0.79	25
K01	30	1.18	25	0.98	30
K02	30	1.18	30	1.18	35
K03	30	1.18	35	1.38	40
K04	30	1.18	40	1.57	44
K45	30	1.18	45	1.77	48
K05	30	1.18	50	1.97	53


Case Code	DIAMETER "D"		LENGTH "L"		Typical Weight (grams)
	mm	inches	mm	inches	
A20	35	1.38	20	0.79	35
A01	35	1.38	25	0.98	42
A02	35	1.38	30	1.18	48
A03	35	1.38	35	1.38	54
A04	35	1.38	40	1.57	62
A45	35	1.38	45	1.77	67
A05	35	1.38	50	1.97	74
A06	35	1.38	63	2.48	88
A07	35	1.38	70	2.76	98
A08	35	1.38	80	3.15	112
A10	35	1.38	105	4.13	144
N04	40	1.57	40	1.57	82
N05	40	1.57	50	1.97	105
N06	40	1.57	63	2.48	130
N08	40	1.57	80	3.15	185
N10	40	1.57	105	4.13	265
B05	50	1.97	50	1.97	136
B06	50	1.97	63	2.48	168
B08	50	1.97	80	3.15	239
B09	50	1.97	92	3.62	241
B10	50	1.97	105	4.13	325

Part Numbering System


382LX	272	M	200	N05	2	V
Type 380L (2 pins) 380LX (2 pins) 382L (4 or 5 pins) 382LX (4 or 5 pins)	Capacitance 272 = 2700 µF 333 = 33000 µF	Tolerance M = ±20%	Rated Voltage Vdc	Case Code	Insulation 2 = PVC	382L/LX 4 or 5 Pin Mount blank = 4 pins (35 or 40 mm dia) V = 5 pins (40 or 50 mm dia)

Typical Performance Curves

Life Test Data 380L222M050K012
Capacitance, DF, Leakage Current






Life Test Data 380LX222M100J042
Capacitance, DF, Leakage Current



Types 380L, 382L, 380LX & 382LX, 85 °C High-Capacitance Snap-In

Typical Performance Curves



Ratings

Cap. (μ F)	Catalog Part Number	Max. ESR Ω @ 25 °C 120 Hz 20 kHz	Ripple Amps Max. @ 85 °C 120 Hz 20 kHz	Nominal Size D x L (mm)
16 Vdc (20 Vdc Surge)				
4700	380LX472M016H202	0.160	0.135	1.60 1.80
4700	380LX472M016H012	0.160	0.135	1.77 2.00
6800	380LX682M016H012	0.110	0.092	2.60 3.00
6800	380LX682M016J202	0.110	0.092	1.80 2.10
8200	380LX822M016H012	0.090	0.078	3.10 3.60
10000	380LX103M016H022	0.075	0.062	3.80 4.30
10000	380LX103M016J012	0.075	0.062	3.80 4.30
10000	380LX103M016K202	0.084	0.070	2.40 2.80
12000	380LX123M016H022	0.062	0.052	4.50 5.20
12000	380LX123M016J012	0.062	0.052	4.50 5.20
15000	380LX153M016H032	0.054	0.045	5.30 6.00
15000	380LX153M016J022	0.054	0.045	5.30 6.00
15000	380LX153M016A202	0.055	0.048	3.20 3.70
18000	380LX183M016H042	0.045	0.040	5.60 6.40
18000	380LX183M016J022	0.045	0.040	5.60 6.40
22000	380LX223M016H452	0.038	0.032	6.10 7.00
22000	380LX223M016J032	0.038	0.032	6.10 7.00
22000	380LX223M016K022	0.038	0.032	6.10 7.00
27000	380LX273M016J452	0.031	0.025	6.30 7.30
27000	380LX273M016K032	0.031	0.025	6.30 7.30
33000	380LX333M016J052	0.025	0.021	6.80 7.80
33000	380LX333M016K042	0.025	0.021	6.80 7.90
33000	380LX333M016A022	0.025	0.021	6.80 7.90
39000	380LX393M016K452	0.022	0.018	6.95 8.00
39000	380LX393M016A032	0.022	0.018	6.95 8.00
47000	380LX473M016K052	0.020	0.017	7.50 8.60
47000	380LX473M016A042	0.022	0.020	7.50 8.60
56000	380LX563M016A452	0.020	0.018	8.70 10.00

Cap. (μ F)	Catalog Part Number	Max. ESR Ω @ 25 °C 120 Hz 20 kHz	Ripple Amps Max. @ 85 °C 120 Hz 20 kHz	Nominal Size D x L (mm)
56000	382LX563M016N042	0.022	0.021	9.00 10.40
68000	380LX683M016A052	0.018	0.017	9.00 10.40
82000	380LX823M016A062	0.016	0.015	10.00 11.50
82000	382LX823M016N052	0.016	0.015	10.30 11.80
100000	380LX104M016A082	0.015	0.014	11.00 12.70
100000	382LX104M016N062	0.018	0.017	11.40 13.00
120000	380LX124M016A102	0.014	0.013	12.81 14.73
120000	382LX124M016N082	0.017	0.016	12.40 14.30
120000	382LX124M016B052V	0.014	0.013	13.17 15.15
150000	382LX154M016B062V	0.012	0.011	14.40 16.56
180000	382LX184M016N102	0.013	0.012	14.85 17.08
180000	382LX184M016B082V	0.011	0.010	15.69 18.04
220000	382LX224M016B092V	0.010	0.009	16.73 19.24
270000	382LX274M016B102V	0.009	0.008	17.79 20.46
25 Vdc (32 Vdc Surge)				
3300	380LX332M025H202	0.177	0.140	1.60 1.80
3300	380LX332M025H012	0.161	0.130	1.70 1.90
4700	380LX472M025H012	0.110	0.090	2.40 2.75
4700	380LX472M025J202	0.125	0.100	1.80 2.10
5600	380LX562M025H012	0.095	0.075	2.90 3.30
6800	380LX682M025H022	0.078	0.063	3.50 4.00
6800	380LX682M025J012	0.078	0.063	3.50 4.00
6800	380LX682M025K202	0.078	0.063	2.30 2.60
8200	380LX822M025H022	0.065	0.049	3.60 4.10
8200	380LX822M025J012	0.065	0.049	3.60 4.10
10000	380LX103M025H032	0.058	0.046	3.80 4.30
10000	380LX103M025J022	0.058	0.046	3.80 4.30
10000	380LX103M025K012	0.058	0.046	3.80 4.30
10000	380LX103M025A202	0.060	0.050	2.70 3.10

Types 380L, 382L, 380LX & 382LX, 85 °C High-Capacitance Snap-In

Cap. (µF)	Catalog Part Number	Max. ESR Ω@ 25 °C 120 Hz 20 kHz	Ripple Amps Max. @ 85 °C 120 Hz20 kHz	Nominal Size D x L (mm)
25 Vdc (32 Vdc Surge)				
10000	380LX103M025A202	0.060	0.050	2.70 3.10 35 x 20
12000	380LX123M025H042	0.050	0.040	4.10 4.70 22 x 40
12000	380LX123M025J032	0.050	0.040	4.10 4.70 25 x 35
12000	380LX123M025K022	0.050	0.040	4.10 4.70 30 x 30
15000	380LX153M025H052	0.040	0.030	4.60 5.30 22 x 50
15000	380LX153M025J042	0.040	0.030	4.60 5.30 25 x 40
15000	380LX153M025K022	0.040	0.030	4.60 5.30 30 x 30
18000	380LX183M025J452	0.035	0.028	5.50 6.30 25 x 45
18000	380LX183M025K032	0.035	0.028	5.50 6.30 30 x 35
22000	380LX223M025J052	0.030	0.023	6.10 7.00 25 x 50
22000	380LX223M025K042	0.030	0.023	6.10 7.00 30 x 40
27000	380LX273M025K452	0.023	0.020	6.20 7.10 30 x 45
27000	380LX273M025A03	0.023	0.020	6.20 7.10 35 x 35
33000	380LX333M025K052	0.020	0.017	6.80 7.90 30 x 50
33000	380LX333M025A042	0.020	0.017	6.80 7.90 35 x 40
33000	382L333M025N042	0.026	0.016	7.30 8.00 40 x 40
39000	380LX393M025A452	0.020	0.017	7.40 8.50 35 x 45
39000	382LX393M025N042	0.020	0.018	8.00 9.20 40 x 40
47000	380LX473M025A052	0.017	0.015	8.00 9.20 35 x 50
47000	380L473M025A062	0.017	0.009	8.30 9.50 35 x 63
56000	380L563M025A072	0.015	0.008	9.10 10.30 35 x 70
56000	382L563M025N062	0.015	0.009	9.50 10.30 40 x 63
56000	380LX563M025A062	0.015	0.013	8.60 9.90 35 x 63
56000	382LX563M025N052	0.016	0.015	9.00 10.30 40 x 50
68000	380LX683M025A082	0.013	0.011	10.40 12.00 35 x 80
68000	382LX683M025N062	0.017	0.015	10.25 11.80 40 x 63
82000	382LX823M025B052V	0.016	0.015	12.29 14.13 50 x 50
100000	380LX104M025A102	0.010	0.008	11.97 13.77 35 x 105
100000	382LX104M025B062V	0.014	0.013	13.45 15.47 50 x 63
100000	382LX104M025N082	0.012	0.011	12.00 13.40 40 x 80
120000	382LX124M025B082V	0.012	0.011	15.29 17.58 50 x 80
150000	382LX154M025N102	0.011	0.010	14.07 16.18 40 x 105
150000	382LX154M025B092V	0.011	0.010	16.01 18.41 50 x 92
180000	382LX184M025B102V	0.010	0.009	16.89 19.42 50 x 105
35 Vdc (44 Vdc Surge)				
2200	380LX222M035H202	0.211	0.160	1.40 1.60 22 x 20
2200	380LX222M035H012	0.166	0.125	1.50 1.75 22 x 25
3300	380LX332M035H012	0.110	0.085	2.30 2.60 22 x 25
3300	380LX332M035J202	0.120	0.090	1.70 2.00 25 x 20
3900	380LX392M035H012	0.095	0.070	2.70 3.10 22 x 25
4700	380LX472M035H022	0.080	0.060	3.30 3.70 22 x 30
4700	380LX472M035J012	0.080	0.060	3.30 3.70 25 x 25
4700	380LX472M035K202	0.090	0.066	2.00 2.30 30 x 20
5600	380LX562M035H022	0.083	0.063	3.40 3.90 22 x 30
5600	380LX562M035J012	0.083	0.063	3.40 3.90 25 x 25
6800	380LX682M035H032	0.068	0.051	3.70 4.20 22 x 35
6800	380LX682M035A202	0.070	0.053	2.40 2.80 35 x 20
6800	380LX682M035J022	0.069	0.051	3.70 4.20 25 x 30
8200	380LX822M035H042	0.057	0.043	4.00 4.60 22 x 40
8200	380LX822M035J032	0.057	0.043	4.00 4.60 25 x 35
10000	380LX103M035H452	0.050	0.037	4.40 5.10 22 x 45
10000	380LX103M035J042	0.050	0.037	4.40 5.10 25 x 40
10000	380LX103M035K022	0.050	0.037	4.40 5.10 30 x 30
10000	380LX103M035A012	0.050	0.037	4.40 5.10 35 x 25

Cap. (µF)	Catalog Part Number	Max. ESR Ω@ 25 °C 120 Hz 20 kHz	Ripple Amps Max. @ 85 °C 120 Hz20 kHz	Nominal Size D x L (mm)
12000	380LX123M035J452	0.044	0.033	5.10 5.80 25 x 45
12000	380LX123M035K032	0.044	0.033	5.10 5.80 30 x 35
12000	380LX123M035A022	0.044	0.033	5.10 5.80 35 x 30
15000	380LX153M035J052	0.036	0.027	5.60 6.40 25 x 50
15000	380LX153M035K042	0.036	0.027	5.60 6.40 30 x 40
15000	380LX153M035A022	0.036	0.027	5.60 6.40 35 x 30
18000	380LX183M035K452	0.030	0.023	5.70 6.50 30 x 45
18000	380LX183M035A032	0.030	0.023	5.70 6.50 35 x 35
22000	380LX223M035K052	0.026	0.020	6.10 7.00 30 x 50
22000	380LX223M035A042	0.026	0.020	6.10 7.00 35 x 40
27000	380LX273M035A452	0.021	0.017	6.80 7.90 35 x 45
27000	382LX273M035N042	0.021	0.017	6.80 7.90 40 x 40
33000	380LX333M035A052	0.018	0.014	7.15 8.22 35 x 50
33000	380L333M035A062	0.018	0.009	7.80 8.70 35 x 63
39000	380LX393M035A062	0.015	0.012	7.90 9.10 35 x 63
39000	380L393M035A072	0.015	0.008	8.60 9.50 35 x 70
39000	382LX393M035N052	0.017	0.014	8.00 9.20 40 x 50
47000	380LX473M035A082	0.015	0.011	9.50 10.90 35 x 80
47000	382LX473M035N062	0.016	0.013	9.60 11.00 40 x 63
56000	382LX563M035B052V	0.015	0.012	10.94 12.58 50 x 50
56000	382LX563M035N082	0.015	0.012	10.30 11.90 40 x 80
68000	380LX683M035A102	0.010	0.008	10.62 12.21 35 x 105
68000	382LX683M035B062V	0.013	0.011	11.93 13.72 50 x 63
82000	382LX823M035N102	0.012	0.009	12.02 13.82 40 x 105
82000	382LX823M035B082V	0.012	0.010	13.06 15.02 50 x 80
100000	382LX104M035B092V	0.011	0.009	13.97 16.07 50 x 92
120000	382LX124M035B102V	0.010	0.008	14.86 17.09 50 x 105
50 Vdc (63 Vdc Surge)				
1500	380LX152M050H202	0.255	0.200	1.20 1.40 22 x 20
1500	380LX152M050H012	0.220	0.170	1.25 1.45 22 x 25
2200	380LX222M050H012	0.150	0.115	1.80 2.10 22 x 25
2200	380LX222M050J202	0.175	0.130	1.40 1.60 25 x 20
2700	380LX272M050H012	0.125	0.095	2.20 2.60 22 x 25
3300	380LX332M050H022	0.100	0.075	2.70 3.10 22 x 30
3300	380LX332M050J012	0.100	0.075	2.70 3.10 25 x 25
3300	380LX332M050K202	0.117	0.090	1.70 2.00 30 x 20
3900	380LX392M050H022	0.085	0.065	2.80 3.20 22 x 30
3900	380LX392M050J012	0.085	0.065	2.80 3.20 25 x 25
4700	380LX472M050H032	0.070	0.055	3.00 3.50 22 x 35
4700	380LX472M050J022	0.070	0.055	3.00 3.50 25 x 30
4700	380LX472M050K012	0.070	0.055	3.00 3.50 30 x 25
4700	380LX472M050A202	0.080	0.060	2.10 2.40 35 x 20
5600	380LX562M050H042	0.060	0.045	3.40 3.90 22 x 40
5600	380LX562M050J032	0.060	0.045	3.40 3.90 25 x 35
5600	380LX562M050K022	0.060	0.045	3.40 3.90 30 x 30
6800	380LX682M050H052	0.050	0.040	3.90 4.40 22 x 50
6800	380LX682M050J042	0.050	0.040	3.90 4.40 25 x 40
6800	380LX682M050K022	0.050	0.040	3.90 4.40 30 x 30
8200	380LX822M050J452	0.040	0.030	4.40 5.10 25 x 45
8200	380LX822M050K032	0.040	0.030	4.40 5.10 30 x 35
10000	380LX103M050J052	0.040	0.030	5.00 5.70 25 x 50
10000	380LX103M050K042	0.040	0.030	5.00 5.70 30 x 40
10000	380LX103M050A022	0.040	0.030	5.00 5.70 35 x 30
12000	380LX123M050K452	0.033	0.025	5.60 6.40 30 x 45
12000	380LX123M050A032	0.033	0.025	5.60 6.40 35 x 35

Types 380L, 382L, 380LX & 382LX, 85 °C High-Capacitance Snap-In

Cap. (µF)	Catalog Part Number	Max. ESR Ω@ 25 °C		Ripple Amps Max. @ 85 °C		Nominal Size D x L (mm)
		120 Hz	20 kHz	120 Hz	20 kHz	
15000	380LX153M050K052	0.027	0.020	6.40	7.40	30 x 50
15000	380LX153M050A042	0.027	0.020	6.40	7.40	35 x 40
18000	380L183M050A062	0.018	0.010	7.80	8.70	35 x 63
18000	380LX183M050A452	0.022	0.017	6.90	7.90	35 x 45
18000	382LX183M050N042	0.023	0.017	6.94	7.98	40 x 40
22000	380L223M050A072	0.015	0.008	8.60	9.50	35 x 70
22000	380LX223M050A052	0.020	0.016	7.60	8.70	35 x 50
27000	380L273M050A082	0.013	0.008	9.30	10.10	35 x 80
27000	382L273M050N062	0.018	0.009	9.00	9.60	40 x 63
27000	380LX273M050A062	0.018	0.015	8.30	9.60	35 x 63
27000	382LX273M050N052	0.018	0.015	8.10	9.30	40 x 50
33000	380LX333M050A082	0.015	0.012	9.20	10.60	35 x 80
33000	382LX333M050N062	0.018	0.014	9.10	10.50	40 x 63
33000	382LX333M050B052V	0.018	0.014	10.48	12.05	50 x 50
47000	382LX473M050B062V	0.013	0.010	11.54	13.27	50 x 63
47000	380LX473M050A102	0.014	0.011	10.27	11.81	35 x 105
56000	382LX563M050N102	0.012	0.009	11.47	13.19	40 x 105
56000	382LX563M050B082V	0.012	0.009	12.46	14.33	50 x 80
68000	382LX683M050B092V	0.011	0.009	13.17	15.15	50 x 92
82000	382LX823M050B102V	0.011	0.008	13.87	15.95	50 x 105
63 Vdc (79 Vdc Surge)						
1000	380LX102M063H202	0.380	0.290	1.20	1.40	22 x 20
1000	380LX102M063H012	0.332	0.250	1.20	1.40	22 x 25
1500	380LX152M063H012	0.221	0.167	1.70	2.00	25 x 20
1500	380LX152M063J202	0.250	0.190	1.30	1.50	25 x 20
2200	380LX222M063H022	0.151	0.114	2.50	2.90	22 x 30
2200	380LX222M063J012	0.151	0.114	2.50	2.90	25 x 25
2200	380LX222M063K202	0.170	0.130	1.50	1.70	30 x 20
2700	380LX272M063H032	0.123	0.093	3.70	4.30	22 x 35
2700	380LX272M063J022	0.123	0.093	3.70	4.30	25 x 30
3300	380LX332M063H042	0.110	0.080	4.10	4.70	22 x 40
3300	380LX332M063J022	0.110	0.080	4.10	4.70	25 x 30
3300	380LX332M063K012	0.110	0.080	4.10	4.70	30 x 25
3300	380LX332M063A202	0.125	0.095	1.70	2.00	35 x 20
3900	380LX392M063H452	0.100	0.075	4.40	5.10	22 x 45
3900	380LX392M063J032	0.100	0.075	4.40	5.10	25 x 35
3900	380LX392M063K022	0.100	0.075	4.40	5.10	30 x 30
4700	380LX472M063H052	0.080	0.060	4.90	5.60	22 x 50
4700	380LX472M063J042	0.080	0.060	4.90	5.60	25 x 40
4700	380LX472M063K022	0.080	0.060	4.90	5.60	30 x 30
4700	380LX472M063A012	0.080	0.060	4.90	5.60	35 x 25
5600	380LX562M063A022	0.070	0.050	5.40	6.20	35 x 30
5600	380LX562M063J452	0.070	0.050	5.40	6.20	25 x 45
5600	380LX562M063K032	0.070	0.050	5.40	6.20	30 x 35
6800	380LX682M063J052	0.060	0.045	5.80	6.70	25 x 50
6800	380LX682M063K042	0.060	0.045	5.80	6.70	30 x 40
6800	380LX682M063A022	0.060	0.045	5.80	6.70	35 x 30
8200	380LX822M063K452	0.050	0.040	6.00	6.90	30 x 45
8200	380LX822M063A032	0.050	0.040	6.00	6.90	35 x 35
10000	382L103M063N042	0.028	0.017	6.60	7.20	40 x 40
10000	380LX103M063A042	0.033	0.025	6.50	7.50	35 x 40
12000	380L123M063A062	0.019	0.010	7.70	8.60	35 x 63
12000	382LX123M063N042	0.035	0.028	7.15	8.22	40 x 40
15000	380L153M063A072	0.016	0.009	8.50	9.40	35 x 70
15000	380LX153M063A062	0.028	0.021	7.70	8.90	35 x 63

Cap. (µF)	Catalog Part Number	Max. ESR Ω@ 25 °C		Ripple Amps Max. @ 85 °C		Nominal Size D x L (mm)
		120 Hz	20 kHz	120 Hz	20 kHz	
18000	382LX183M063N062	0.028	0.022	9.25	10.60	40 x 63
18000	380LX183M063A082	0.023	0.012	9.40	10.80	35 x 80
27000	382LX273M063N082	0.018	0.015	10.00	11.50	40 x 80
27000	380LX273M063A102	0.015	0.012	10.38	11.94	35 x 105
27000	382LX273M063B052V	0.018	0.015	10.86	12.49	50 x 50
33000	382LX333M063N102	0.015	0.012	11.76	13.52	40 x 105
33000	382LX333M063B062V	0.017	0.013	11.57	13.42	50 x 63
47000	382LX473M063B082V	0.013	0.010	12.78	14.70	50 x 80
51000	382LX513M063B092V	0.012	0.010	13.34	15.34	50 x 92
56000	382LX563M063B102V	0.012	0.009	13.93	16.02	50 x 105
80 Vdc (100 Vdc Surge)						
680	380LX681M080H202	0.450	0.330	1.00	1.20	22 x 20
680	380LX681M080H012	0.390	0.295	1.00	1.20	22 x 25
1000	380LX102M080H012	0.265	0.200	1.50	1.75	22 x 25
1000	380LX102M080J202	0.300	0.225	1.20	1.40	25 x 20
1200	380LX122M080H012	0.220	0.170	1.80	2.10	22 x 25
1500	380LX152M080H022	0.177	0.134	2.30	2.60	22 x 30
1500	380LX152M080J012	0.177	0.134	2.30	2.60	25 x 25
1500	380LX152M080K202	0.200	0.150	1.40	1.60	30 x 20
1800	380LX182M080H032	0.147	0.109	2.50	2.90	22 x 35
1800	380LX182M080J022	0.147	0.109	2.50	2.90	25 x 30
2200	380LX222M080H042	0.121	0.092	2.70	3.10	22 x 40
2200	380LX222M080J022	0.121	0.092	2.70	3.10	25 x 30
2200	380LX222M080K012	0.121	0.092	2.70	3.10	30 x 25
2200	380LX222M080A202	0.135	0.100	1.70	2.00	35 x 20
2700	380LX272M080H452	0.098	0.075	2.80	3.20	22 x 45
2700	380LX272M080J032	0.098	0.075	2.80	3.20	25 x 35
2700	380LX272M080K022	0.098	0.075	2.80	3.20	30 x 30
3300	380LX332M080H052	0.085	0.065	3.20	3.70	22 x 50
3300	380LX332M080J042	0.085	0.065	3.20	3.70	25 x 40
3300	380LX332M080K022	0.085	0.065	3.20	3.70	30 x 30
3900	380LX392M080J452	0.080	0.060	3.60	4.10	25 x 45
3900	380LX392M080K032	0.080	0.060	3.60	4.10	30 x 35
4700	380LX472M080J052	0.065	0.050	4.10	4.70	25 x 50
4700	380LX472M080K042	0.065	0.050	4.10	4.70	30 x 40
5600	380LX562M080K452	0.055	0.040	4.60	5.20	30 x 45
5600	380LX562M080A032	0.055	0.040	4.60	5.20	35 x 35
6800	380LX682M080K052	0.045	0.035	5.20	5.90	30 x 50
6800	380LX682M080A042	0.045	0.035	5.20	5.90	35 x 40
8200	380LX822M080A052	0.040	0.030	5.80	6.70	35 x 50
8200	382LX822M080N042	0.040	0.030	5.83	6.70	40 x 40
10000	380LX103M080A062	0.033	0.025	6.40	7.34	35 x 63
12000	380L123M080A072	0.020	0.012	8.10	9.00	35 x 70
12000	382L123M080N052	0.025	0.016	7.50	8.00	40 x 50
15000	380L153M080A082	0.017	0.010	8.80	9.60	35 x 80
15000	382L153M080N062	0.020	0.013	8.50	9.20	40 x 63
18000	382L183M080N082	0.014	0.009	10.30	10.80	40 x 80
18000	382LX183M080B052V	0.023	0.017	10.00	11.50	50 x 50
22000	380LX223M080A102	0.015	0.011	9.86	11.34	35 x 105
22000	382LX223M080B062V	0.019	0.014	11.08	12.74	50 x 63
27000	382LX273M080N102	0.015	0.012	11.35	13.05	40 x 105
27000	382LX273M080B082V	0.015	0.012	12.33	14.18	50 x 80
33000	382LX333M080B092V	0.014	0.010	13.37	15.38	50 x 92
39000	382LX393M080B102V	0.013	0.010	14.34	16.49	50 x 105

Types 380L, 382L, 380LX & 382LX, 85 °C High-Capacitance Snap-In

Cap. (µF)	Catalog Part Number	Max. ESR Ω @ 25 °C 120 Hz 20 kHz	Ripple Amps Max. @ 85 °C 120 Hz20 kHz	Nominal Size D x L (mm)	Cap. (µF)	Catalog Part Number	Max. ESR Ω @ 25 °C 120 Hz 20 kHz	Ripple Amps Max. @ 85 °C 120 Hz20 kHz	Nominal Size D x L (mm)
100 Vdc (125 Vdc Surge)					180 Vdc (225 Vdc Surge)				
470	380LX471M100H202	0.450	0.300	1.00 1.20	22 x 20	330	380LX331M160H012	0.603 0.308	1.50 2.00 22 x 25
470	380LX471M100H212	0.450	0.300	1.10 1.30	22 x 25	390	380LX391M160H012	0.470 0.240	1.60 2.30 22 x 25
560	380LX561M100H012	0.400	0.250	1.30 1.50	22 x 25	390	380LX391M160H022	0.470 0.240	1.60 2.30 22 x 30
680	380LX681M100H012	0.320	0.210	1.60 1.85	22 x 25	390	380LX391M160J012	0.470 0.240	1.60 2.30 25 x 25
680	380LX681M100J202	0.390	0.295	1.10 1.30	25 x 20	390	380LX391M160K202	0.600 0.300	1.10 1.50 30 x 20
1000	380LX102M100H022	0.220	0.150	2.00 2.30	22 x 30	470	380LX471M160H022	0.423 0.216	2.10 3.00 22 x 30
1000	380LX102M100J012	0.220	0.150	2.00 2.30	25 x 25	470	380LX471M160J012	0.423 0.216	2.10 3.00 25 x 25
1000	380LX102M100K202	0.250	0.165	1.20 1.40	30 x 20	560	380LX561M160H022	0.355 0.178	2.25 3.15 22 x 30
1200	380LX122M100H032	0.195	0.125	2.30 2.70	22 x 35	560	380LX561M160J012	0.355 0.178	2.25 3.15 25 x 25
1200	380LX122M100J022	0.180	0.120	2.30 2.70	25 x 30	560	380LX561M160A202	0.420 0.210	1.30 1.80 35 x 20
1500	380LX152M100H042	0.155	0.100	2.60 3.00	22 x 40	680	380LX681M160H032	0.293 0.146	2.50 3.50 22 x 35
1500	380LX152M100J022	0.155	0.100	2.60 3.00	25 x 30	680	380LX681M160J022	0.293 0.146	2.50 3.50 25 x 30
1500	380LX152M100K012	0.155	0.100	2.60 3.00	30 x 25	680	380LX681M160K012	0.293 0.149	2.50 3.50 30 x 25
1500	380LX152M100A202	0.177	0.120	1.50 1.70	35 x 20	820	380LX821M160H042	0.260 0.130	2.50 3.50 22 x 40
1800	380LX182M100H452	0.130	0.085	2.80 3.30	22 x 45	820	380LX821M160H452	0.260 0.130	2.80 3.90 22 x 45
1800	380LX182M100J032	0.140	0.090	2.80 3.30	25 x 35	820	380LX821M160J032	0.260 0.130	2.80 3.90 25 x 35
1800	380LX182M100K022	0.140	0.090	2.80 3.30	30 x 30	820	380LX821M160K012	0.260 0.130	2.75 3.85 30 x 25
2200	380LX222M100H052	0.121	0.080	3.10 3.60	22 x 50	1000	380LX102M160H452	0.220 0.110	3.00 4.20 22 x 45
2200	380LX222M100J042	0.121	0.080	3.10 3.60	25 x 40	1000	380LX102M160J042	0.220 0.110	3.00 4.20 25 x 40
2200	380LXM222100K022	0.121	0.080	3.10 3.60	30 x 30	1000	380LX102M160K022	0.220 0.110	3.00 4.20 30 x 30
2200	380LX222M100A012	0.121	0.078	3.14 3.61	35 x 25	1200	380LX122M160J052	0.210 0.115	3.25 4.55 25 x 50
2700	380LX272M100J452	0.104	0.068	3.70 4.30	25 x 45	1200	380LX102M160K032	0.210 0.115	3.25 4.55 30 x 35
2700	380LX272M100K032	0.104	0.068	3.70 4.30	30 x 35	1200	380LX122M160A022	0.210 0.115	3.25 4.55 35 x 30
2700	380LX272M100A022	0.104	0.068	3.70 4.30	35 x 30	1500	380LX152M160J052	0.170 0.090	3.70 5.20 25 x 50
3300	380LX332M100J052	0.090	0.060	4.10 4.70	25 x 50	1500	380LX152M160K032	0.170 0.090	3.70 5.20 30 x 35
3300	380LX332M100K042	0.090	0.060	4.10 4.70	30 x 40	1500	380LX152M160A022	0.166 0.091	3.73 5.22 35 x 30
3900	380LX392M100K452	0.080	0.050	4.50 5.20	30 x 45	1800	380LX182M160K052	0.140 0.085	4.20 5.90 30 x 50
3900	380LX392M100A032	0.080	0.050	4.50 5.20	35 x 35	1800	380LX182M160A032	0.140 0.085	4.20 5.90 35 x 35
4700	380LX472M100K052	0.070	0.050	5.10 5.90	30 x 50	2200	380LX222M160K052	0.105 0.053	4.78 6.69 30 x 50
4700	380LX472M100A042	0.070	0.050	5.10 5.90	35 x 40	2200	380LX222M160A042	0.115 0.075	4.78 6.69 35 x 40
5600	382LX562M100N042	0.060	0.045	5.80 6.60	40 x 40	2700	380LX272M160A052	0.090 0.060	5.50 7.60 35 x 50
5600	380LX562M100A452	0.060	0.040	5.80 6.60	35 x 45	2700	382LX272M160N042	0.080 0.045	5.50 7.60 40 x 40
6800	380LX682M100A052	0.050	0.040	6.60 7.60	35 x 50	3300	380LX332M160A062	0.065 0.040	6.30 8.80 35 x 63
6800	380L682M100A062	0.024	0.014	7.20 8.10	35 x 63	3300	380LX332M160N052	0.065 0.040	6.30 8.80 40 x 50
6800	382L682M100N052	0.026	0.017	7.40 7.90	40 x 50	3900	380LX392M160A082	0.055 0.030	7.30 10.20 35 x 80
8200	380LX822M100A062	0.040	0.030	7.00 8.10	35 x 63	3900	380LX392M160N062	0.055 0.030	7.30 10.20 40 x 63
8200	380L822M100A072	0.021	0.012	8.00 8.90	35 x 70	4700	382L472M160N082	0.036 0.020	6.60 8.50 40 x 80
8200	382LX822M100N052	0.040	0.030	7.30 8.40	40 x 50	5600	382LX562M160N082	0.040 0.020	8.30 11.70 40 x 80
8200	382L822M100N062	0.021	0.013	8.40 9.10	40 x 63	5600	382LX562M160B052V	0.040 0.020	8.25 9.50 50 x 50
10000	380LX103M100A082	0.033	0.025	8.70 9.60	35 x 80	6800	380LX682M160A102	0.032 0.017	9.10 12.70 35 x 105
10000	382LX103M100N062	0.033	0.025	8.00 9.20	40 x 63	8200	382LX822M160B062V	0.026 0.015	8.90 12.50 50 x 63
10000	382LX103M100B052V	0.033	0.025	8.82 10.14	50 x 50	10000	382LX103M160N102	0.022 0.012	9.90 13.80 40 x 105
12000	382LX123M100N082	0.028	0.021	8.65 10.00	40 x 80	10000	382LX103M160B082V	0.022 0.012	9.80 13.70 50 x 80
12000	380LX123M100A102	0.028	0.021	8.57 9.86	35 x 105	12000	382LX123M160B092V	0.018 0.010	12.90 18.10 50 x 92
15000	382LX153M100N102	0.022	0.017	10.12 11.64	40 x 105	15000	382LX153M160B092V	0.014 0.008	14.10 19.70 50 x105
15000	382LX153M100B062V	0.022	0.017	10.07 11.58	50 x 63	160 Vdc (200 Vdc Surge)			
18000	382LX183M100B082V	0.018	0.014	11.00 12.65	50 x 80	220	380LX221M160H202	1.000 0.500	0.80 1.10 22 x 20
22000	382LX223M100B092V	0.015	0.011	11.76 13.52	50 x 92	220	380LX221M160H012	0.850 0.420	0.90 1.25 22 x 25
27000	382LX273M100B102V	0.014	0.010	12.53 14.41	50 x 105	270	380LX271M160H012	0.700 0.340	1.20 1.65 22 x 25
					270	380LX271M160J202	0.800 0.400	0.90 1.20 25 x 20	

Types 380L, 382L, 380LX & 382LX, 85 °C High-Capacitance Snap-In

Cap. (µF)	Catalog Part Number	Max. ESR Ω @ 25 °C		Ripple Amps Max. @ 85 °C		Nominal Size D x L (mm)
		120 Hz	20 kHz	120 Hz	20 kHz	
680	380LX681M180K022	0.293	0.149	2.50	3.50	30 x 30
820	380LX821M180H452	0.243	0.124	2.80	3.90	22 x 45
820	380LX821M180J042	0.243	0.124	2.80	3.90	25 x 40
820	380LX821M180K022	0.243	0.124	2.80	3.90	30 x 30
1000	380LX102M180J452	0.199	0.102	3.00	4.20	25 x 45
1000	380LX102M180K032	0.199	0.102	3.00	4.20	30 x 35
1200	380LX122M180J052	0.166	0.085	3.30	4.60	25 x 50
1200	380LX122M180K042	0.166	0.085	3.30	4.60	30 x 40
1200	380LX122M180A032	0.166	0.085	3.30	4.60	35 x 35
1500	380LX152M180K452	0.133	0.068	3.80	5.40	30 x 45
1500	380LX152M180A042	0.133	0.068	3.80	5.40	35 x 40
1800	380LX182M180K052	0.111	0.057	4.30	6.00	30 x 50
1800	380LX182M180A042	0.111	0.057	4.30	6.00	35 x 40
2200	380LX222M180A052	0.090	0.046	4.90	6.90	35 x 50
2700	382L272M180N062	0.051	0.027	5.00	6.50	40 x 63
2700	380L272M180A072	0.054	0.027	4.80	6.20	35 x 70
3300	380L332M180A082	0.046	0.023	5.40	7.10	35 x 80
4700	382L472M180N082	0.036	0.020	6.60	8.50	40 x 80
200 Vdc (250 Vdc Surge)						
150	380LX151M200H202	1.330	0.600	0.65	0.90	22 x 20
150	380LX151M200H012	1.220	0.550	0.70	1.00	22 x 25
220	380LX221M200H012	0.083	0.380	1.00	1.45	22 x 25
220	380LX221M200J202	0.905	0.410	0.90	1.20	25 x 20
270	380LX271M200H012	0.610	0.280	1.40	2.00	22 x 25
330	380LX331M200H012	0.550	0.250	1.60	2.20	22 x 25
330	380LX331M200K202	0.603	0.308	1.00	1.40	30 x 20
390	380LX391M200H022	0.470	0.210	1.70	2.40	22 x 30
390	380LX391M200J012	0.470	0.210	1.70	2.40	25 x 25
470	380LX471M200H032	0.390	0.180	1.90	2.60	22 x 35
470	380LX471M200J022	0.390	0.180	1.90	2.60	25 x 30
470	380LX471M200K012	0.423	0.216	1.90	2.60	30 x 25
470	380LX471M200A202	0.460	0.210	1.30	1.80	35 x 20
560	380LX561M200H042	0.330	0.150	2.40	3.40	22 x 40
560	380LX561M200J022	0.330	0.150	2.43	3.40	25 x 30
560	380LX561M200K012	0.330	0.150	2.40	3.40	30 x 25
680	380LX681M200H452	0.270	0.120	2.70	3.80	22 x 45
680	380LX681M200J032	0.270	0.120	2.70	3.80	25 x 35
680	380LX681M200K022	0.270	0.120	2.70	3.80	30 x 30
820	380LX821M200J452	0.220	0.100	2.90	4.10	25 x 45
820	380LX821M200K022	0.220	0.100	2.90	4.10	30 x 30
820	380LX821M200A012	0.243	0.124	2.90	4.10	35 x 25
1000	380LX102M200J452	0.199	0.090	3.25	4.55	25 x 45
1000	380LX102M200K032	0.199	0.090	3.25	4.55	30 x 35
1000	380LX102M200A022	0.199	0.102	3.30	4.60	35 x 30
1200	380LX122M200K042	0.166	0.075	3.50	4.90	30 x 40
1200	380LX122M200A022	0.166	0.075	3.50	4.90	35 x 30
1500	380LX152M200K452	0.144	0.072	3.87	5.42	30 x 45
1500	380LX152M200A032	0.144	0.072	3.87	5.42	35 x 35
1800	380LX182M200K052	0.120	0.060	4.32	6.05	30 x 50
1800	380LX182M200A042	0.120	0.060	4.32	6.05	35 x 40
2200	380LX222M200A452	0.098	0.054	4.92	6.89	35 x 45
2200	382LX222M200N042	0.098	0.054	4.92	6.89	40 x 40
2700	380LX272M200A062	0.080	0.045	5.50	7.70	35 x 63
2700	382LX272M200N052	0.080	0.045	5.40	7.60	40 x 50
3300	380LX332M200A082	0.065	0.037	6.40	9.00	35 x 80
250 Vdc (300 Vdc Surge)						
120	380LX121M250H202	1.658	0.846	0.50	0.60	22 x 20
120	380LX121M250H012	1.520	0.610	0.71	1.00	22 x 25
150	380LX151M250H012	1.220	0.490	0.90	1.25	22 x 25
150	380LX151M250J202	1.326	0.530	0.70	0.90	25 x 20
180	380LX181M250H012	0.920	0.370	1.10	1.50	22 x 25
220	380LX221M250H012	0.754	0.301	1.17	1.64	22 x 25
220	380LX221M250K202	0.830	0.330	0.90	1.20	30 x 20
270	380LX271M250H022	0.620	0.250	1.30	1.80	22 x 30
270	380LX271M250J012	0.620	0.250	1.30	1.80	25 x 25
330	380LX331M250H032	0.550	0.220	1.80	2.50	22 x 35
330	380LX331M250J022	0.550	0.220	1.80	2.50	25 x 30
330	380LX331M250K012	0.550	0.220	1.80	2.50	30 x 25
330	380LX331M250A202	0.550	0.220	1.10	1.50	35 x 20
390	380LX391M250H042	0.510	0.260	1.90	2.70	22 x 40
390	380LX391M250J022	0.468	0.187	1.91	2.67	25 x 30
390	380LX391M250K012	0.510	0.260	1.90	2.70	30 x 25
470	380LX471M250H452	0.390	0.155	2.10	3.00	22 x 45
470	380LX471M250J032	0.390	0.155	2.10	3.00	25 x 35
470	380LX471M250K012	0.353	0.141	2.10	3.00	30 x 25
560	380LX561M250J042	0.326	0.130	2.30	3.20	25 x 40
560	380LX561M250K022	0.326	0.130	2.30	3.20	30 x 30
560	380LX561M250A012	0.326	0.130	2.30	3.20	35 x 25
680	380LX681M250J452	0.268	0.107	2.50	3.50	25 x 45
680	380LX681M250K032	0.268	0.107	2.50	3.50	30 x 35
680	380LX681M250A022	0.293	0.149	2.50	3.50	35 x 30
820	380LX821M250K042	0.222	0.089	2.80	3.90	30 x 40
820	380LX821M250A022	0.222	0.089	2.80	3.90	35 x 30
1000	380LX102M250K452	0.182	0.073	3.32	4.65	30 x 45
1000	380LX102M250A032	0.182	0.073	3.32	4.65	35 x 35
1200	380LX122M250A042	0.166	0.083	3.53	4.94	35 x 40
1500	380LX152M250A052	0.133	0.068	4.00	5.70	35 x 50
1500	382LX152M250N042	0.133	0.066	4.04	5.66	40 x 40
1800	380LX182M250A062	0.110	0.055	4.50	6.30	35 x 63
1800	382LX182M250N052	0.110	0.055	4.50	6.30	40 x 50
1800	382L182M250N062	0.062	0.030	4.80	6.40	40 x 63
2200	380LX222M250A082	0.090	0.045	4.90	6.90	35 x 80
2200	382LX222M250N062	0.090	0.045	4.90	6.90	40 x 63
2700	382L272M250N082	0.043	0.021	6.30	8.40	40 x 80
2700	382LX272M250B052V	0.074	0.037	6.77	7.79	50 x 50
3300	382LX332M250N082	0.060	0.030	7.00	9.80	40 x 80
3300	382LX332M250B062V	0.060	0.030	7.79	10.91	50 x 63
3900	380LX392M250A102	0.051	0.026	7.47	10.46	35 x 105
4700	382LX472M250N102	0.042	0.021	8.88	12.43	40 x 105
4700	382LX472M250B082V	0.042	0.021	9.65	13.51	50 x 80

Types 380L, 382L, 380LX & 382LX, 85 °C High-Capacitance Snap-In

Cap. (µF)	Catalog Part Number	Max. ESR Ω @ 25 °C		Ripple Amps Max. @ 85 °C		Nominal Size D x L (mm)
		120 Hz	20 kHz	120 Hz	20 kHz	
5600	382LX562M250B092V	0.036	0.018	10.80	15.12	50 x 92
6800	382LX682M250B102V	0.029	0.015	12.16	17.02	50 x 105
315 Vdc (365 Vdc Surge)						
100	380LX101M315H012	1.989	1.015	.90	1.30	22 x 25
120	380LX121M315H022	1.658	0.856	1.00	1.40	22 x 30
120	380LX121M315J012	1.658	0.856	1.00	1.40	25 x 25
150	380LX151M315H022	1.326	0.677	1.10	1.60	22 x 30
150	380LX151M315J012	1.326	0.677	1.10	1.60	25 x 25
180	380LX181M315H032	1.105	0.546	1.20	1.70	22 x 35
180	380LX181M315J022	1.105	0.546	1.20	1.70	25 x 30
180	380LX181M315K012	1.105	0.546	1.20	1.70	30 x 25
220	380LX221M315H042	0.904	0.461	1.40	2.00	22 x 40
220	380LX221M315J032	0.904	0.461	1.40	2.00	25 x 35
220	380LX221M315K012	0.904	0.461	1.40	2.00	30 x 25
270	380LX271M315H452	0.737	0.376	1.60	2.20	22 x 45
270	380LX271M315J042	0.737	0.376	1.60	2.20	25 x 40
270	380LX271M315K022	0.737	0.376	1.60	2.20	30 x 30
330	380LX331M315J452	0.603	0.308	1.80	2.50	25 x 45
330	380LX331M315K022	0.603	0.308	1.80	2.50	30 x 30
330	380LX331M315A012	0.603	0.308	1.80	2.50	35 x 25
390	380LX391M315J052	0.510	0.260	2.00	2.80	25 x 50
390	380LX391M315K032	0.510	0.260	2.00	2.80	30 x 35
390	380LX391M315A022	0.510	0.260	2.00	2.80	35 x 30
470	380LX471M315K042	0.423	0.216	2.30	3.20	30 x 40
470	380LX471M315A032	0.423	0.216	2.30	3.20	35 x 35
560	380LX561M315K452	0.355	0.181	2.60	3.60	30 x 45
560	380LX561M315A032	0.355	0.181	2.60	3.60	35 x 35
680	380LX681M315A452	0.293	0.149	2.90	4.00	35 x 45
820	380LX821M315A052	0.243	0.124	3.30	4.60	35 x 50
1000	380L 102M315A062	0.218	0.129	2.70	3.60	35 x 63
1200	380L 122M315A072	0.182	0.107	3.20	4.20	35 x 70
1200	382L 122M315N052	0.202	0.122	2.90	3.90	40 x 50
1500	380L 152M315A082	0.153	0.090	3.60	4.80	35 x 80
1500	382L 152M315N062	0.162	0.098	3.40	4.50	40 x 63
1800	382L 182M315N082	0.113	0.069	4.50	6.00	40 x 80
350 Vdc (400 Vdc Surge)						
82	380LX820M350H012	2.022	0.708	.83	1.16	22 x 25
100	380LX101M350H022	1.660	0.580	.90	1.30	22 x 30
120	380LX121M350H022	1.382	0.484	1.00	1.40	22 x 30
120	380LX121M350J012	1.382	0.484	1.00	1.40	25 x 25
150	380LX151M350H032	1.110	0.390	1.10	1.60	22 x 35
150	380LX151M350J012	1.110	0.390	1.10	1.60	25 x 25
150	380LX151M350K012	1.110	0.390	1.10	1.60	30 x 25
180	380LX181M350H042	0.920	0.320	1.20	1.70	22 x 40
180	380LX181M350J022	0.920	0.320	1.22	1.70	25 x 30
180	380LX181M350K012	0.920	0.320	1.20	1.70	30 x 25
220	380LX221M350H452	0.750	0.260	1.44	2.00	22 x 45
220	380LX221M350J032	0.750	0.260	1.44	2.00	25 x 35
220	380LX221M350K012	0.750	0.260	1.44	2.00	30 x 25
220	380LX221M350A012	0.750	0.260	1.44	2.00	35 x 25
270	380LX271M350J042	0.614	0.215	1.66	2.32	25 x 40
270	380LX271M350K022	0.614	0.215	1.66	2.32	30 x 30
270	380LX271M350A012	0.614	0.215	1.66	2.32	35 x 25
270	380LX271M350A012	0.614	0.215	1.70	2.30	35 x 25
330	380LX331M350J052	0.500	0.180	1.90	2.60	25 x 50

Cap. (µF)	Catalog Part Number	Max. ESR Ω @ 25 °C		Ripple Amps Max. @ 85 °C		Nominal Size D x L (mm)
		120 Hz	20 kHz	120 Hz	20 kHz	
330	380LX331M350K032	0.500	0.180	1.90	2.60	30 x 35
330	380LX331M350A022	0.500	0.180	1.90	2.60	35 x 30
390	380LX391M350J052	0.425	0.149	2.06	2.88	25 x 50
390	380LX391M350K042	0.425	0.149	2.06	2.88	30 x 40
390	380LX391M350A022	0.425	0.149	2.06	2.88	35 x 30
470	380LX471M350K052	0.390	0.140	2.40	3.40	30 x 50
470	380LX471M350A032	0.390	0.140	2.40	3.40	35 x 35
560	380LX561M350K052	0.326	0.114	2.60	3.64	30 x 50
560	380LX561M350A042	0.326	0.114	2.60	3.64	35 x 40
680	380LX681M350A452	0.293	0.117	2.96	4.14	35 x 45
680	382LX681M350N042	0.293	0.117	3.00	4.10	40 x 40
820	380LX821M350A052	0.243	0.097	3.55	4.97	35 x 50
1000	380LX102M350A062	0.250	0.110	3.80	5.30	35 x 63
1000	382LX102M350N052	0.250	0.110	3.80	5.30	40 x 50
1200	380LX122M350A082	0.210	0.095	4.40	6.20	35 x 80
1200	382LX122M350N062	0.210	0.095	4.40	6.20	40 x 63
1200	382LX122M350B052V	0.207	0.093	5.18	5.96	50 x 50
1500	382LX152M350B062V	0.166	0.075	6.01	8.41	50 x 63
1800	380LX182M350A102	0.138	0.062	5.79	8.11	35 x 105
1800	382LX182M350N082	0.138	0.062	5.85	8.20	40 x 80
1800	382LX182M350B082V	0.138	0.062	6.89	9.65	50 x 80
2200	382LX222M350N102	0.113	0.051	6.91	9.67	40 x 105
2200	382LX222M350B092V	0.113	0.051	7.79	10.91	50 x 92
2700	382LX272M350B102V	0.092	0.041	8.80	12.32	50 x 105
400 Vdc (450 Vdc Surge)						
47	380LX470M400H202	3.530	1.240	.25	.35	22 x 20
47	380LX470M400H012	3.530	1.240	.47	.66	22 x 25
68	380LX680M400H012	2.440	0.850	.70	.97	22 x 25
68	380LX680M400J202	2.930	1.000	.35	.50	25 x 20
82	380LX820M400H012	2.000	0.710	.80	1.20	22 x 25
100	380LX101M400H022	1.650	0.580	.90	1.30	22 x 30
100	380LX101M400J012	1.650	0.580	.90	1.30	25 x 25
100	380LX101M400K202	1.990	0.700	.50	.70	30 x 20
120	380LX121M400H032	1.380	0.490	1.00	1.40	22 x 35
120	380LX121M400J012	1.380	0.490	1.02	1.43	25 x 25
150	380LX151M400H042	1.100	0.390	1.20	1.60	22 x 40
150	380LX151M400J022	1.100	0.390	1.20	1.60	25 x 30
150	380LX151M400K012	1.100	0.390	1.20	1.60	30 x 25
150	380LX151M400A202	1.330	0.470	.60	.80	35 x 20
180	380LX181M400H452	0.920	0.320	1.40	2.00	22 x 45
180	380LX181M400J022	0.920	0.320	1.40	2.00	25 x 30
220	380LX221M400H052	0.750	0.260	1.50	2.10	22 x 50
220	380LX221M400J042	0.750	0.260	1.50	2.10	25 x 40
220	380LX221M400K022	0.750	0.260	1.50	2.10	30 x 30
270	380LX271M400J452	0.680	0.240	1.70	2.30	25 x 45
270	380LX271M400K032	0.680	0.240	1.70	2.30	30 x 35
270	380LX271M400A022	0.680	0.240	1.70	2.30	35 x 30
330	380LX331M400K042	0.550	0.200	1.90	2.70	30 x 40
330	380LX331M400A022	0.550	0.200	1.90	2.70	35 x 30
390	380LX391M400K452	0.470	0.160	2.10	3.00	30 x 45
390	380LX391M400A032	0.470	0.160	2.10	3.00	35 x 35
470	380LX471M400A042	0.388	0.136	2.39	3.35	35 x 40
560	380LX561M400A452	0.326	0.114	2.69	3.77	35 x 45
560	382LX561M400N042	0.326	0.114	2.70	3.80	40 x 40
680	380LX681M400A052	0.270	0.095	3.00	4.20	35 x 50

Types 380L, 382L, 380LX & 382LX, 85 °C High-Capacitance Snap-In

Cap. (µF)	Catalog Part Number	Max. ESR Ω @ 25 °C 120 Hz 20 kHz		Ripple Amps Max. @ 85 °C 120 Hz 20 kHz		Nominal Size D x L (mm)
820	380LX821M400A062	0.222	0.078	3.55	4.97	35 x 63
820	382LX821M400N052	0.222	0.078	3.40	4.70	40 x 50
1000	380L102M400A082	0.179	0.099	3.60	4.80	35 x 80
1000	382LX102M400N062	0.249	0.127	3.40	4.80	40 x 63
1000	382LX102M400B052V	0.199	0.080	4.76	5.47	50 x 50
1200	380LX122M400A082	0.152	0.053	4.52	6.33	35 x 80
1200	382LX122M400N062	0.152	0.053	4.52	6.33	40 x 63
1200	382LX122M400B062V	0.166	0.066	5.47	7.66	50 x 63
1500	380LX152M400A102	0.122	0.043	5.44	7.62	35 x 105
1500	382LX152M400N082	0.122	0.043	5.50	7.70	40 x 80
1500	382LX152M400B082V	0.133	0.053	6.47	9.06	50 x 80
1800	382LX182M400N102	0.101	0.035	6.53	9.14	40 x 105
1800	382LX182M400B092V	0.111	0.044	7.35	10.29	50 x 92
2200	382LX222M400B102V	0.090	0.036	8.43	11.80	50 x 105
420 Vdc (470 Vdc Surge)						
82	380LX820M420H022	2.430	0.850	.80	1.15	22 x 30
100	380LX101M420H022	2.000	0.700	0.90	1.30	22 x 30
100	380LX101M420J012	2.000	0.700	0.90	1.30	25 x 25
120	380LX121M420H032	1.660	0.590	1.00	1.40	22 x 35
120	380LX121M420J022	1.660	0.590	1.00	1.40	25 x 30
150	380LX151M420H042	1.330	0.450	1.15	1.60	22 x 40
150	380LX151M420J022	1.330	0.450	1.15	1.60	25 x 30
150	380LX151M420K012	1.330	0.450	1.15	1.60	30 x 25
180	380LX181M420J012	1.100	0.390	1.45	2.00	22 x 45
180	380LX181M420J032	1.100	0.390	1.45	2.00	25 x 35
180	380LX181M420K022	1.100	0.390	1.45	2.00	30 x 30
220	380LX221M420J452	0.900	0.320	1.50	2.10	25 x 45
220	380LX221M420K022	0.900	0.320	1.50	2.10	30 x 30
220	380LX221M420A012	0.900	0.320	1.50	2.10	35 x 25
270	380LX271M420J052	0.740	0.260	1.70	2.30	25 x 50
270	380LX271M420K032	0.740	0.260	1.70	2.30	30 x 35
270	380LX271M420A022	0.740	0.260	1.70	1.93	35 x 30
330	380LX331M420K452	0.600	0.210	1.90	2.68	30 x 45
330	380LX331M420A032	0.600	0.210	1.90	2.68	35 x 35
390	380LX391M420K052	0.500	0.180	2.10	3.00	30 x 50
390	380LX391M420A042	0.500	0.180	2.10	3.00	35 x 40
470	380LX471M420A452	0.420	0.150	2.40	3.35	35 x 45
560	380LX561M450A052	0.355	0.125	2.70	3.80	35 x 50
450 Vdc (500 Vdc Surge)						
33	380LX330M450H202	6.029	2.400	.20	.30	22 x 20
33	380LX330M450H012	6.029	2.400	0.40	0.57	22 x 25
47	380LX470M450H012	4.230	1.690	0.59	0.83	25 x 20
47	380LX470M450J202	4.230	1.690	0.30	0.40	25 x 20
56	380LX560M450H012	3.000	1.190	0.70	1.00	22 x 25
68	380LX680M450H022	2.926	1.170	0.80	1.10	22 x 30
68	380LX680M450K202	2.926	1.170	0.40	0.50	30 x 20
82	380LX820M450H022	2.000	0.810	0.80	1.20	22 x 30
82	380LX820M450J012	2.000	0.810	0.80	1.20	25 x 25
100	380LX101M450H032	1.660	0.660	0.90	1.30	22 x 35
100	380LX101M450J022	1.660	0.660	.90	1.30	25 x 30
100	380LX101M450K012	1.989	1.015	0.90	1.30	30 x 25
100	380LX101M450A202	1.989	1.015	0.50	0.70	35 x 20
120	380LX121M450H042	1.380	0.550	1.00	1.50	22 x 40
120	380LX121M450J022	1.380	0.550	1.00	1.50	25 x 30
120	380LX121M450K012	1.380	0.550	1.00	1.50	30 x 25
500 Vdc (550 Vdc Surge)						
33	380LX330M500H012	3.850	2.353	.60	.80	22 x 25
47	380LX470M500H012	3.500	1.410	0.63	0.88	22 x 25
56	380LX560M500H022	2.980	1.184	0.70	0.98	22 x 30
68	380LX680M500H032	2.438	0.975	0.78	1.09	22 x 35
68	380LX680M500J012	2.438	0.975	0.78	1.09	25 x 25
82	380LX820M500H042	2.022	0.809	0.88	1.23	22 x 40
82	380LX820M500J022	2.022	0.809	0.88	1.23	25 x 30
82	380LX820M500K012	1.960	1.186	0.90	1.20	30 x 25
100	380LX101M500H452	1.658	0.663	0.99	1.39	22 x 45
100	380LX101M500J032	1.658	0.663	0.99	1.39	25 x 35
100	380LX101M500J042	1.340	0.828	1.10	1.50	25 x 40
100	380LX101M500K022	1.440	0.871	1.10	1.50	30 x 30
100	380LX101M500A012	1.580	0.962	1.10	1.50	35 x 25
120	380LX121M500H052	1.382	0.553	1.13	1.58	22 x 50
120	380LX121M500J042	1.382	0.553	1.13	1.58	25 x 40
120	380LX121M500K022	1.382	0.553	1.13	1.58	30 x 30
120	380LX121M500K032	1.130	0.683	1.40	1.90	30 x 35
120	380LX121M500A022	1.160	0.707	1.40	1.90	35 x 30
150	380LX151M500J452	1.105	0.442	1.29	1.80	25 x 45
150	380LX151M500J052	0.945	0.585	1.40	1.90	25 x 50
150	380LX151M500K032	1.105	0.442	1.29	1.80	30 x 35
150	380LX151M500K042	0.926	0.562	1.60	2.20	30 x 40
150	380LX151M500A012	1.105	0.442	1.29	1.80	35 x 25

Types 380L, 382L, 380LX & 382LX, 85 °C High-Capacitance Snap-In

Cap. (µF)	Catalog Part Number	Max. ESR Ω@ 25 °C 120 Hz 20 kHz		Ripple Amps Max. @ 85 °C 120 Hz20 kHz		Nominal Size D x L (mm)
180	380LX181M500J052	0.920	0.368	1.38	1.93	25 x 50
180	380LX181M500K042	0.92	0.368	1.38	1.93	30 x 40
180	380LX181M500A022	0.921	0.388	1.38	1.93	35 x 30
180	380LX181M500A032	0.92	0.555	1.60	2.20	35 x 35
220	380LX221M500K452	0.754	0.339	1.50	2.10	30 x 45
220	380LX221M500K052	0.654	0.397	2.00	2.70	30 x 50
220	380LX221M500A032	0.754	0.339	1.50	2.10	35 x 35
220	380LX221M500A042	0.749	0.456	1.90	2.50	35 x 40
270	380LX271M500A042	0.614	0.278	1.76	2.46	35 x 40
270	380LX271M500A052	0.529	0.322	2.30	3.10	35 x 50
270	382L271M500N042	0.549	0.342	2.40	3.20	40 x 40
330	380LX331M500A452	0.502	0.251	1.99	2.79	35 x 45
330	382LX331M500N042	0.502	0.276	2.16	3.00	40 x 40
390	380LX391M500A052	0.425	0.234	2.22	3.11	35 x 50
390	380LX391M500A062	0.423	0.257	2.70	3.60	35 x 63
390	382L391M500N052	0.388	0.242	2.90	3.90	40 x 50
390	380LX391M500A062	0.423	0.257	2.70	3.60	35 x 63
470	380LX471M500A062	0.353	0.194	2.58	3.61	35 x 63
470	380LX471M500A072	0.353	0.215	3.20	4.20	35 x 70
470	382LX471M500N052	0.353	0.194	2.70	3.78	40 x 50
470	382L471M500N062	0.311	0.194	3.40	4.50	40 x 63
560	380LX561M500A082	0.295	0.179	3.60	4.80	35 x 80
560	382LX561M500N062	0.326	0.179	3.11	4.35	40 x 63
560	382LX561M500B052V	0.355	0.195	3.52	4.05	50 x 50
680	382L681M500N082	0.218	0.135	4.50	6.00	40 x 80
680	380LX681M500A0822	0.244	0.134	3.21	4.49	35 x 80
680	382LX681M500B062V	0.293	0.161	4.07	5.70	50 x 63
820	380LX821M500A102	0.202	0.111	3.97	5.56	35 x 105
820	382LX821M500N082	0.222	0.122	3.88	5.43	40 x 80
1000	382LX102M500B082V	0.199	0.109	5.05	7.07	50 x 80
1200	382LX122M500N102	0.152	0.084	5.90	8.26	40 x 105
1200	382LX122M500B092V	0.166	0.091	5.74	8.04	50 x 92
1500	382LX152M500B102V	0.144	0.079	6.65	9.31	50 x 105

Cap. (µF)	Catalog Part Number	Max. ESR Ω@ 25 °C 120 Hz 20 kHz		Ripple Amps Max. @ 85 °C 120 Hz20 kHz		Nominal Size D x L (mm)
150	380LX151M500J452	1.105	0.442	1.29	1.80	25 x 45
150	380LX151M500A012	1.105	0.442	1.29	1.80	35 x 25
180	380LX181M500A032	0.912	0.555	1.60	2.20	35 x 35
180	380LX181M500J052	0.921	0.388	1.38	1.93	25 x 50
180	380LX181M500A022	0.921	0.388	1.38	1.93	35 x 30
220	380LX221M500K052	0.654	0.397	2.00	2.70	30 x 50
220	380LX221M500A042	0.749	0.456	1.90	2.50	35 x 40
220	380LX221M500K452	0.754	0.339	1.50	2.10	30 x 45
220	380LX221M500A032	0.754	0.339	1.50	2.10	35 x 35
270	380LX271M500A052	0.529	0.322	2.30	3.10	35 x 50
270	382L271M500N042	0.549	0.342	2.40	3.20	40 x 40
270	380LX271M500A042	0.614	0.278	1.76	2.46	35 x 40
330	380LX331M500A452	0.502	0.251	1.99	2.79	35 x 45
330	382LX331M500N042	0.502	0.276	2.16	3.00	40 x 40
390	382L391M500N052	0.388	0.242	2.90	3.90	40 x 50
390	380LX391M500A062	0.423	0.257	2.70	3.60	35 x 63
390	380LX391M500A052	0.425	0.234	2.22	3.11	35 x 50
470	382L471M500N062	0.311	0.194	3.40	4.50	40 x 63
470	380LX471M500A062	0.353	0.194	2.58	3.61	35 x 63
470	380LX471M500A072	0.353	0.215	3.20	4.20	35 x 70
470	382LX471M500N052	0.353	0.194	2.70	3.78	40 x 50
560	380LX561M500A082	0.295	0.179	3.60	4.80	35 x 80
560	382LX561M500N062	0.326	0.179	3.11	4.35	40 x 63
560	382LX561M500B052V	0.355	0.195	3.52	4.05	50 x 50
680	382L681M500N082	0.218	0.135	4.50	6.00	40 x 80
680	380LX681M500A082	0.244	0.134	3.21	4.49	35 x 80
680	382LX681M500B062V	0.293	0.161	4.07	5.70	50 x 63
820	380LX821M500A102	0.202	0.111	3.97	5.56	35 x 105
820	382LX821M500N082	0.222	0.122	3.88	5.43	40 x 80
1000	382LX102M500B082V	0.199	0.109	5.05	7.07	50 x 80
1200	382LX122M500N102	0.152	0.084	5.90	8.26	40 x 105
1200	382LX122M500B092V	0.166	0.091	5.74	8.04	50 x 92
1500	382LX152M500B102V	0.144	0.079	6.65	9.31	50 x 105