


SuperServer 6016GT-TF

[Products](#) ▶ [Systems](#) ▶ [1U](#) ▶ **[6016GT-TF]**



Integrated Boards



X8DTG-DF

Available Colors:

Black



[▶ Drivers & Utilities](#)
[▶ BIOS](#)
[▶ IPMI](#)
[▶ Tested Memory](#)
[▶ Manuals](#)
[▶ Drive Options](#)

Note: Image above may show a varied configuration or optional parts. Please refer to parts list for standard parts included.

Key Features

1. Intel® Xeon® processor 5600/5500 series, with QPI up to 6.4 GT/s
2. Up to 192GB DDR3 1333/ 1066/ 800MHz ECC Registered DIMM / 48GB Unbuffered DIMM
3. 1 (x4) PCI-E 2.0 (Low Profile)
4. Integrated IPMI 2.0 with KVM and Dedicated LAN
5. Intel® 82576 Dual-Port Gigabit Ethernet Controller
6. 3x Hot-swap SATA Drive Bays
7. 1400W Gold-level High-efficiency Power Supply
8. 2x PCI-E 2.0 (x16) slots (1 on each side)

Specifications

Product SKUs - Discontinued SKU (EOL). Please contact sales-rep for alternative options.

SYS-6016GT-TF ■ SuperServer 6016GT-TF (Black)

Motherboards

[Super X8DTG-DF](#)

Processor/Cache

- Dual 1366-pin LGA Sockets
- Supports up to two Intel® 64-bit Xeon® processor(s) of the same type below:

CPU

- Intel® Xeon® Processor X5600/E5600/L5600 Series (Westmere) 40W - 95W
- Intel® Xeon® Processor X5500/E5500/L5500 Series (Nehalem-EP) 38W - 95W

QPI

- up to 6.4 GT/s

System Memory

- 12x 240-pin DIMM slots
- Supports up to 192 GB 1333 / 1066 / 800MHz DDR3 ECC Registered memory
- Supports up to 48 GB 1333 / 1066 / 800MHz DDR3 ECC / Non ECC Unbuffered memory
- Memory Mirroring supported

Memory Type

- 1333 / 1066 / 800MHz ECC Registered / ECC or Non ECC Unbuffered DDR3 SDRAM
- 72-bit, 240-pin gold-plated DIMMs

DIMM Sizes

- 1GB, 2GB, 4GB , 8GB , 16GB

Memory Voltage

- 1.5 V / 1.35V

Error Detection

- Corrects single-bit errors
- Detects double-bit errors (using ECC memory)
- Supports Intel® x4 and x8 Single Device Data Correction (SDDC)

On-Board Devices

Chipset

- Intel® 5520 (Tylersburg) chipset
- ICH10R + IOH-36D

SATA

- Intel ICH10R SATA 3.0Gbps Controller
- RAID 0, 1, 5, 10 support (Windows)
- RAID 0, 1, 10 support (Linux)
- Support for Intelligent Platform Management Interface v.2.0

Chassis

Form Factor ■ 1U Rackmount

Model ■ [CSE-818G-1400B](#)

Dimensions

Height ■ 1.7" (43mm)

Width ■ 17.2" (437mm)

Depth ■ 28.2" (716mm)

Gross Weight ■ 38 lbs (17.2 kg)

Available Color ■ Black

Front Panel

Buttons ■ Power On/Off button
■ System Reset button

LEDs

- Power LED
- Hard drive activity LED
- 2x Network activity LEDs
- System Overheat LED / Fan fail LED / UID LED

Expansion Slots

PCI-Express ■ 1 (x4) PCI-E 2.0 (in x16 slot -Low Profile)
■ [AOC Compatibility Matrix](#)

Drive Bays

Hot-swap ■ 3x 3.5" Hot-swap drive bays

Backplane

SAS/SATA HDD Backplane
(SAS support requires optional SAS controller)

System Cooling

Fans ■ 8x 4cm heavy-duty counter-rotating PWM fans with optimal fan speed control

Power Supply

1400W high-efficiency power supply with PMBus


AC Input ■ 1200W: 100 - 140V, 50 - 60Hz, 10.5 - 14.7 Amp
■ 1400W: 180 - 240V, 50 - 60Hz, 7.2 - 9.5 Amp

DC Output +5V standby ■ 4 Amp

DC Output +12V ■ 100 Amp @ 100-140V
■ 117 Amp @ 180-240V

With Power Distributor ■ +5V: 14 Amp

IPMI	<ul style="list-style-type: none"> ■ IPMI 2.0 with virtual media over LAN and KVM-over-LAN support ■ Nuvoton WPCM450 BMC
Network Controllers	<ul style="list-style-type: none"> ■ Intel® 82576 Dual-Port Gigabit Ethernet Controller ■ Supports 10BASE-T, 100BASE-TX, and 1000BASE-T, RJ45 output ■ Intel® I/OAT 3 support for fast, scaleable, and reliable networking ■ VMDq support for better performance of virtualization ■ 1x Realtek RTL8201N PHY (dedicated IPMI)
Graphics	<ul style="list-style-type: none"> ■ Matrox G200eW 16MB DDR2
Super I/O	<ul style="list-style-type: none"> ■ Winbond W83527HG chip
Clock Generator	<ul style="list-style-type: none"> ■ 932S421 chip
Input / Output	
Serial ATA	<ul style="list-style-type: none"> ■ Six Serial ATA ports ■ Six SATA hard drives supported
LAN	<ul style="list-style-type: none"> ■ 2x RJ45 LAN ports ■ 1x RJ45 Dedicated IPMI LAN port
USB	<ul style="list-style-type: none"> ■ 2 rear + 1 header (2 Ports) ■ 4 total USB ports, 2.0 Compliant / 1.1 Compliant
VGA	<ul style="list-style-type: none"> ■ 1x VGA Port
Serial Port	<ul style="list-style-type: none"> ■ 1 Fast UART 16550 serial port
System BIOS	
BIOS Type	<ul style="list-style-type: none"> ■ 32Mb SPI Flash EEPROM with AMI® BIOS
BIOS Features	<ul style="list-style-type: none"> ■ Plug and Play (PnP) ■ PCI 2.2 ■ ACPI up to 3.0 ■ USB Keyboard support

Certification	 Gold Certified [Test Report]
PC Health Monitoring	
CPU	<ul style="list-style-type: none"> ■ Monitors for CPU Cores, +1.5V, +3.3V, +5V, +12V, +5 Stdbby, +3.3 Stdbby, VBAT, Memory Voltages. ■ CPU Core 6-Phase-switching voltage regulator
FAN	<ul style="list-style-type: none"> ■ Total of four 4-pin PWM fans ■ 4x fans with tachometer monitoring ■ Status monitor for speed control ■ Status monitor for on/off control ■ Low noise fan speed control
Temperature	<ul style="list-style-type: none"> ■ Monitoring for CPU and chassis environment ■ CPU thermal trip support ■ Thermal Control for 4x Fan Connectors ■ PSU I²C temperature sensing logic ■ Thermal Monitor 2 (TM2) support ■ PECI
LED	<ul style="list-style-type: none"> ■ Power Fail / Overheat LED ■ Suspend-state Indicator LED ■ UID LED
Other Features	<ul style="list-style-type: none"> ■ SDDC Support
Operating Environment / Compliance	
RoHS	<ul style="list-style-type: none"> ■ RoHS Compliant
Environmental Spec.	<ul style="list-style-type: none"> ■ Operating Temperature: 10° to 35° C (50° to 95° F) ■ Non-operating Temperature: -40° to 70° C (-40° to 158° F) ■ Operating Relative Humidity: 8% to 90% (non-condensing) ■ Non-operating Relative Humidity: 5 to 95% (non-condensing)

Parts List

[See Parts List](#)

[Terms & Conditions](#) | [Privacy](#) | [Investor Relations](#) | [Jobs](#) | [Site Map](#)

[SuperServer®](#) | [Motherboard](#) | [Chassis](#) | [Rack Cabinet](#) | [SuperBlade®](#) | [Embedded](#) | [Networking](#) | [Storage](#) | [Accessories](#) | [AMD Solution](#) | [Power Supplies](#)

Copyright © 2019 Super Micro Computer, Inc.

Information in this document is subject to change without notice.

Other products and companies referred to herein are trademarks or registered trademarks of their respective companies or mark holders.