

[Worldwide](#)

1519L Multifunction 15-inch Desktop Touchmonitor

The 1519L is a wide-screen display that is easier to use and incorporate into more environments than traditional desktop touchmonitors. It allows extra content on the screen and is well-suited for corporate environment uses such as spreadsheets, publishing, and dual-window applications. The 1519L is available in five industry-leading Elo touch technologies: zero-bezel APR, which senses touch on the display by recognizing the unique pattern of sounds, standard-bezel IntelliTouch surface acoustic wave, zero-bezel AccuTouch 5-wire resistive, zero-bezel iTouch surface acoustic wave which combines the pure-glass surface of IntelliTouch with the stylish glass-to-edge design of APR and projected capacitive (PCAP) for superior optical performance. Additional applications well-suited to take advantage of the monitor's features include point-of-sale (POS), point-of-information (POI), point-of-service, interactive digital signage, loyalty systems, kiosk information systems, light industrial shop-floor automation and home control.

As featured in Hearst Electronic Products Magazine

The Elo Touch Solutions 1519L with PCAP technology for a sensitive touch response.

[Read more](#)[Press release](#) • [Compare Elo touchmonitors](#)

Features	Specifications	Accessories	Part Numbers	Support	How-to-Buy
Touch Technology ?	Touch Interface ?	Part Number	Region	Surface Treatment	Bezel Color
iTouch	USB and Serial	E176449	ASIA-Pacific	Clear	Black
iTouch	USB and Serial	E114849	EMEA	Clear	Black
iTouch	USB and Serial	E997831	Japan	Clear	Black
iTouch	USB and Serial	E232070	Americas	Clear	Black
IntelliTouch	USB and Serial	E037021	ASIA-Pacific	Anti-glare	Black
IntelliTouch	USB and Serial	E264492	EMEA	Anti-glare	Black
IntelliTouch	USB and Serial	E353788	Japan	Anti-glare	Black
IntelliTouch	USB and Serial	E830343	Americas	Anti-glare	Black
AccuTouch	USB and Serial	E821837	ASIA-Pacific	Anti-glare	Black
AccuTouch	USB and Serial	E175716	EMEA	Anti-glare	Black
AccuTouch	USB and Serial	E577820	Japan	Anti-glare	Black
AccuTouch	USB and Serial	E732007	Americas	Anti-glare	Black
Acoustic Pulse Recognition (APR)	USB	E819123	ASIA-Pacific	Anti-glare	Black
Acoustic Pulse Recognition (APR)	USB	E525398	EMEA	Anti-glare	Black
Acoustic Pulse Recognition (APR)	USB	E740169	Japan	Anti-glare	Black
Acoustic Pulse Recognition (APR)	USB	E883482	Americas	Anti-glare	Black
Projected Capacitive (PCAP)	USB	E651942	Worldwide	Clear	Black

Optional Peripherals

Peripheral	Part #
Power Brick Kits	North America: E005277 EMEA : E162361 UK & Korea: E180092 China: E558862 Taiwan: E818655 Japan: E182546 Argentina: E887099
Cable Kit for replacement cables	P/N E378229 (Gray); E410150 (Beige)
Magnetic Stripe Reader	E039290
Stand	E069296

Elo Touch Solutions Quick Links

[Contact Us](#)

[Careers at Elo](#)

[Languages](#)

[Site Map](#)

[Newsletter](#)

Resources Quick Links

[Warranty Policies](#)

[Locate a reseller](#)

[Find Documents & Drawings](#)