


Dimensions in mm (inches).



LCC2 (MO-041BB) Pinouts

Pin 1 – Collector 1 Pin 4 – Collector 2
Pin 2 – Base 1 Pin 5 – Emitter 2
Pin 3 – Base 2 Pin 6 – Emitter 1

Dual Bipolar NPN Devices in a hermetically sealed LCC2 Ceramic Surface Mount Package for High Reliability Applications

Dual Bipolar NPN Devices.

$$V_{CEO} = 40V$$

$$I_c = 0.05A$$

All Semelab hermetically sealed products can be processed in accordance with the requirements of BS, CECC and JAN, JANTX, JANTXV and JANS specifications.

Parameter	Test Conditions	Min.	Typ.	Max.	Units
V_{CEO}^*				40	V
$I_{C(ONT)}$				0.05	A
h_{FE}	@ 5/10m (V_{CE} / I_C)	150		600	-
f_t			60M		Hz
P_D				1.2	W

* Maximum Working Voltage

This is a shortform datasheet. For a full datasheet please contact sales@semelab.co.uk.

Semelab Plc reserves the right to change test conditions, parameter limits and package dimensions without notice. Information furnished by Semelab is believed to be both accurate and reliable at the time of going to press. However Semelab assumes no responsibility for any errors or omissions discovered in its use.