





# HIGH FREQUENCY WIRE WOUND TRANSFORMERS



## EI22 Platforms - THT



- AC/DC and DC/DC Switching Transformers**
- Reinforced Insulation**
- 3000Vrms Hi-Pot**
- Topology: Flyback**
- Custom Design Available**

### Electrical Specifications @ 25°C — Operating Temperature -40°C to 130°C<sup>1</sup>

|           |                 |              |                        |                |   |
|-----------|-----------------|--------------|------------------------|----------------|---|
| PA2653NL  | Pri. Inductance | (3 - 1)      | 910 $\mu$ H $\pm$ 10%  |                |  |
|           | Lk. Inductance  | (3 - 1)      | 15 $\mu$ H MAX         |                |   |
|           | w/              | (4, 5, 8, 9) | shorted                |                |   |
|           | DCR             | (3-1)        | 875                    | m $\Omega$ Max |   |
|           |                 | (5-4)        | 17.5                   |                |   |
|           |                 | (9-8)        | 75                     |                |   |
| Hi-Pot    | Pri-Sec         | 3000 Vrms    |                        |                |   |
| K1 Factor | 3616.8          |              |                        |                |   |
| PA2813NL  | Pri. Inductance | (4 - 5)      | 1200 $\mu$ H $\pm$ 10% |                |  |
|           | Lk. Inductance  | (4 - 5)      | 20 $\mu$ H MAX         |                |   |
|           | w/              | (1, 2, 7, 8) | shorted                |                |   |
|           | DCR             | (4-5)        | 2500                   | m $\Omega$ Max |   |
|           |                 | (1-2)        | 200                    |                |   |
|           |                 | (7-8)        | 60                     |                |   |
| Hi-Pot    | Pri-Sec         | 3000 Vrms    |                        |                |   |
| K1 Factor | 5148            |              |                        |                |   |



#### NOTES:


- The temperature of the component (ambient plus temperature rise) must be within the stated operating temperature range.
- The above transformers and inductors have been tested and approved by Pulse's power IC partners and are sited in the appropriate datasheet or evaluation board documentation at these companies. To determine which IC and IC partners are matched with the above Pulse part numbers please consult the IC Cross Reference on the Pulse website.
- For flyback topology applications, it is necessary to ensure that the transformer will not saturate in the application. The peak flux density (Bpk) should remain below 2700Gauss. To calculate the peak flux density use the following formula:  

$$B_{pk} \text{ (Gauss)} = K1\_Factor * I_{pk}(A)$$
- In high volt- $\mu$ sec applications, it is important to calculate the core loss of the transformer. Approximate transformer core loss can be calculated as:  

$$CoreLoss \text{ (W)} = 4.1769 \times 10^{-7} \times (Freq\_kHz)^{1.62} \times (DB\_Gauss)^{2.65}$$
where DB can be calculated as:  
For Flyback Topology:  $DB = K1\_Factor * D(A)$   
For Forward Topology:  $DB = K1\_Factor * Volt\text{-}\mu sec$
- The "NL" suffix indicates an RoHS-compliant part number. Non-NL suffixed parts are not necessarily RoHS compliant, but are electrically and mechanically equivalent to NL versions. If a part number does not have the "NL" suffix, but an RoHS compliant version is required, please contact Pulse for availability.


# HIGH FREQUENCY WIRE WOUND TRANSFORMERS

## EI22 Platforms - THT




### Mechanical

#### PA2653NL



### Mechanical

#### PA2813NL



### For More Information:

**Pulse North America Headquarters**  
12220 World Trade Dr.  
San Diego, CA 92128  
U.S.A.

**Pulse European Headquarters**  
Einsteinstrasse 1  
D-71083 Herrenberg  
Germany

**Pulse China Headquarters**  
B402, Shenzhen Academy of  
Aerospace Technology Bldg.  
10th Kejinan Rd.  
High-Tech Zone  
Nanshan District  
Shenzhen, PR China 518057

**Pulse North China**  
Room 1503  
XinYin Building  
No. 888 YiShan Rd.  
Shanghai 200233  
China

**Pulse South Asia**  
150 Kampong Ampat  
#07-01/02  
KA Centre  
Singapore 368324

**Pulse North Asia**  
No. 26  
Kao Ching Rd.  
Yang Mei Chen  
Taoyuan Hsien  
Taiwan, R. O. C.  
32667

TEL: 858 674 8100  
FAX: 858 674 8262

TEL: 49 7032 7806 0  
FAX: 49 7032 7806 12

TEL: 86 755 33966678  
FAX: 86 755 33966700

TEL: 86 21 32181071  
FAX: 86 21 32181396

TEL: 65 6287 8998  
FAX: 65 6280 0080

TEL: 886 3 4643715  
FAX: 886 3 4641911

This is a "Preliminary" product data sheet. Products mentioned on this data sheet are in development and in the process of being qualified. These products are not fully released nor are they in production. Features, specifications and performance of products offered are subject to change without notice. Other brand and product names mentioned herein may be products and/or registered trademarks of their respective owners. For current information on this product, please contact the Pulse office nearest you and ask for the "Power Applications Engineer." Pulse and the Squarewave logo are trademarks of Pulse Electronics, Inc., registered in the U.S. and other countries.

© Copyright, 2010. Pulse Electronics, Inc. All rights reserved.