

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

10

23.24	17	36	8-103916-8
63.88	49	100	8-103916-7
51.18	39	80	8-103916-6
46.1	35	72	8-103916-5
38.48	29	60	8-103916-4
32.13	24	50	8-103916-3
28.32	21	44	8-103916-2
25.78	19	40	8-103916-1
21.97	16	34	8-103916-0
19.43	14	30	7-103916-9
16.89	12	26	7-103916-8
15.62	11	24	7-103916-7
10.54	7	16	7-103916-6
9.27	6	14	7-103916-5
8.00	5	12	7-103916-4
5.46	3	8	7-103916-3
13.08	9	20	7-103916-2
6.73	4	10	7-103916-1

4

23.24	17	36	6-103916-8
63.88	49	100	6-103916-7
51.18	39	80	6-103916-6
38.48	29	60	6-103916-4
32.13	24	50	6-103916-3
25.78	19	40	6-103916-1
19.43	14	30	5-103916-9
10.54	7	16	5-103916-6
5.46	3	8	5103916-3
13.08	9	20	5-103916-2
6.73	4	10	5-103916-1

FINISH

DIM_B

DIM_A

NO OF POSN

PART NUMBER

9

23.24	17	36	3-103916-8
63.88	49	100	3-103916-7
51.18	39	80	3-103916-6
46.10	35	72	3-103916-5
38.48	29	60	3-103916-4
32.13	24	50	3-103916-3
28.32	21	44	3-103916-2
25.78	19	40	3-103916-1
21.97	16	34	3-103916-0
19.43	14	30	2-103916-9
16.89	12	26	2-103916-8
15.62	11	24	2-103916-7
10.54	7	16	2-103916-6
9.27	6	14	2-103916-5
8.00	5	12	2-103916-4
5.46	3	8	2-103916-3
13.08	9	20	2-103916-2
6.73	4	10	2-103916-1

1

23.24	17	36	1-103916-8
63.88	49	100	1-103916-7
51.18	39	80	1-103916-6
46.10	35	72	1-103916-5
38.48	29	60	1-103916-4
32.13	24	50	1-103916-3
28.32	21	44	1-103916-2
25.78	19	40	1-103916-1
21.97	16	34	1-103916-0
19.43	14	30	103916-9
16.89	12	26	103916-8
15.62	11	24	103916-7
10.54	7	16	103916-6
9.27	6	14	103916-5
8.00	5	12	103916-4
5.46	3	8	103916-3
13.08	9	20	103916-2
6.73	4	10	103916-1

FINISH

DIM_B

DIM_A

NO OF POSN

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

G. RAMESH

09NOV2017

CHK

J. OLSON

03NOV2017

APVD

J. OLSON

03NOV2017

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-

1 PLC ±0.3

2 PLC ±0.13

3 PLC ±-

4 PLC ±-

ANGLES ±0.5°

FINISH

SEE TABLE

MATERIAL

-

-

PRODUCT SPEC

108-1093

APPLICATION SPEC

114-25031

WEIGHT

-

CUSTOMER DRAWING

NAME

HEADER ASSEMBLY, VERTICAL, UNSHROUDED, AMPMODU SYSTEM 50 AMPMODU System 50

SIZE

A2

CAGE CODE

00779

DRAWING NO

103916

RESTRICTED TO

-

SCALE

5:1

SHEET

2

OF

2

REV

U

1471-9 (3/13)