


The 7000 Universal Range of Audio and Video Connectors employs many innovative features unique to the Deltron series. They are suitable for use in both commercial and industrial electronic applications, where reliability, simple operation and the elimination of RF and mechanical interference is necessary. Common uses include mixing desks, tape recorders, video recorders, DAT recorders and test instrumentation.

Dimensions



Deltron Part No	Silver Contacts		Gold Contacts	
	Nickel	Black	Nickel	Black
3-way	717-0300	719-0300	723-0300	725-0300
4-way	717-0400	719-0400	723-0400	725-0400
5way	717-0500	719-0500	723-0500	725-0500

Features

- completely interchangeable with all leading manufactures of XLRs.
- can be mounted from either the front or rear face
- HOUSING: a rugged diecasting offering full RF protection, with small industrial standard flange.
- INSERT: thermoplastic with high mechanical, thermal and electrical properties, excellent chemical resistance and dimensional stability.
- CONTACTS: precision machined in brass with generous solder buckets to accept a wide range of cable sizes.
- SHELL TO GROUND TERMINAL: silver plated straight through connection.
- CODING: a unique interchangeable system of coloured plastic buttons providing a quick and easy system of identification (when the connector is front mounted.)

Mechanical Properties

- Housing
 - Zinc high pressure diecast
 - Satin nickel or black chrome
 - Valox DR48 UL 94V-0
- Contact Base
 - Brass, 3 microns silver, anti-tarnish Finish, or 0.5 microns gold
- Contacts
 - Spring Steel, Nickel plate
 - 3 microns silver plate
- Earth Tag
 - Acetal (UL 94 HB)
- Ident Buttons.
 - Black, Blue, Orange, Red, Green
- Ident. Options
 - Yellow, Brown, Violet, Grey, White
- Operating Temp
 - 30°C to +80°C
- Insertion Force
 - 20N
- Withdrawal Force
 - 10N
- Min No. Insertions
 - 10000

Electrical Properties

- Number of Contacts
 - 3, 4 or 5
- Rated Current per Contact
 - 16, 10 or 7.5 AWG
- Maximum Wire Size
 - 14, 14 or 14 AWG
- (solid)
 - 2.5, 2.5 or 2.5mm
- Cap. Between Contacts
 - 4, 7 or 7pF
- Rated Voltage
 - 250 Volts a.c.
- Test Voltage
 - 1500 Volts a.c.
- Contact resistance
 - 3 milli-Ohms
- Insulation resistance
 - 1 giga-Ohms

CONVERTED FROM PS0632 ISS6 (23.09.02) IN JAN 2003

DrngNo 717-719-723-725 TITLE PROFESSIONAL QUALITY -CHASSIS PLUG ALL DIMENSIONS IN MM ANGLES IN DECIMAL DEGREES



GENERAL SPECIFICATION FOR MULTIPOLE CONNECTOR

CUSTOMER		FILTER REF			
Aprvd Date	29/01/03	Aprvd By	MC	Drwn by	BS
Scale:	NTS	Sheet	1 / 1		

