


# FMBA14



**SuperSOT™-6**  
Mark: .1N  
Dot denotes pin #1

## NPN Multi-Chip Darlington Transistor

This device is designed for applications requiring extremely high current gain at collector currents to 1.0 A. Sourced from Process 05.

### Absolute Maximum Ratings\*

$T_A = 25^\circ\text{C}$  unless otherwise noted

| Symbol         | Parameter  | Value       | Units            |
|----------------|--|-------------|------------------|
| $V_{CES}$      | Collector-Emitter Voltage                        | 30          | V                |
| $V_{CBO}$      | Collector-Base Voltage                           | 30          | V                |
| $V_{EBO}$      | Emitter-Base Voltage                             | 10          | V                |
| $I_C$          | Collector Current - Continuous                   | 1.2         | A                |
| $T_J, T_{stg}$ | Operating and Storage Junction Temperature Range | -55 to +150 | $^\circ\text{C}$ |

\*These ratings are limiting values above which the serviceability of any semiconductor device may be impaired.

#### NOTES:

- 1) These ratings are based on a maximum junction temperature of 150 degrees C.
- 2) These are steady state limits. The factory should be consulted on applications involving pulsed or low duty cycle operations.

### Thermal Characteristics

$T_A = 25^\circ\text{C}$  unless otherwise noted

| Symbol          | Characteristic  | Max    | Units                |
|-----------------|---|--------|----------------------|
|                 |   | FMBA14 |                      |
| $P_D$           | Total Device Dissipation<br>Derate above $25^\circ\text{C}$ | 700    | mW                   |
|                 |   | 5.6    | mW/ $^\circ\text{C}$ |
| $R_{\theta JA}$ | Thermal Resistance, Junction to Ambient                     | 180    | $^\circ\text{C/W}$   |

NPN Multi-Chip Darlington Transistor  
(continued)

Electrical Characteristics TA = 25°C unless otherwise noted

| Symbol | Parameter | Test Conditions | Min | Typ | Max | Units |
|--------|-----------|-----------------|-----|-----|-----|-------|
|--------|-----------|-----------------|-----|-----|-----|-------|

OFF CHARACTERISTICS

|               |                                     |                             |    |  |     |    |
|---------------|-------------------------------------|-----------------------------|----|--|-----|----|
| $V_{(BR)CES}$ | Collector-Emitter Breakdown Voltage | $I_C = 100\ \mu A, I_B = 0$ | 30 |  |     | V  |
| $I_{CBO}$     | Collector-Cutoff Current            | $V_{CB} = 30\ V, I_E = 0$   |    |  | 100 | nA |
| $I_{EBO}$     | Emitter-Cutoff Current              | $V_{EB} = 10\ V, I_C = 0$   |    |  | 100 | nA |

ON CHARACTERISTICS\*





|               |                                      |   |            |  |     |   |
|---------------|--------------------------------------|---|------------|--|-----|---|
| $h_{FE}$      | DC Current Gain                      | $I_C = 10\ mA, V_{CE} = 5.0\ V$<br>$I_C = 100\ mA, V_{CE} = 5.0\ V$ | 10K<br>20K |  |     |   |
| $V_{CE(sat)}$ | Collector-Emitter Saturation Voltage | $I_C = 100\ mA, I_B = 0.1\ mA$                                      |            |  | 1.5 | V |
| $V_{BE(on)}$  | Base-Emitter On Voltage              | $I_C = 100\ mA, V_{CE} = 5.0\ V$                                    |            |  | 2.0 | V |

SMALL SIGNAL CHARACTERISTICS

|          |                           |  |      |  |  |     |
|----------|---------------------------|--|------|--|--|-----|
| $h_{fe}$ | Small Signal Current Gain | $I_C = 10\ mA, V_{CE} = 5.0\ V,$<br>$f = 100\ MHz$ | 1.25 |  |  | MHz |
|----------|---------------------------|--|------|--|--|-----|

\*Pulse Test: Pulse Width  $\leq 300\ \mu s$ , Duty Cycle  $\leq 2.0\%$

Typical Characteristics




NPN Multi-Chip Darlington Transistor  
(continued)


FMBA14

Typical Characteristics (continued)


Collector-Cutoff Current  
vs Ambient Temperature




Collector-Emitter Breakdown  
Voltage with Resistance  
Between Emitter-Base




Input and Output Capacitance  
vs Reverse Voltage



Gain Bandwidth Product  
vs Collector Current




Power Dissipation vs  
Ambient Temperature



# SuperSOT™-6 Tape and Reel Data



## SSOT-6 Packaging Configuration: Figure 1.0




### Packaging Description:


SSOT-6 parts are shipped in tape. The carrier tape is made from a dissipative (carbon filled) polycarbonate resin. The cover tape is a multilayer film (Heat Activated Adhesive in nature) primarily composed of polyester film, adhesive layer, sealant, and anti-static sprayed agent. These reeled parts in standard option are shipped with 3,000 units per 7" or 177cm diameter reel. The reels are dark blue in color and is made of polystyrene plastic (anti-static coated). Other option comes in 10,000 units per 13" or 330cm diameter reel. This and some other options are described in the Packaging Information table.

These full reels are individually barcode labeled and placed inside a pizza box (illustrated in figure 1.0) made of recyclable corrugated brown paper with a Fairchild logo printing. One pizza box contains three reels maximum. And these pizza boxes are placed inside a barcode labeled shipping box which comes in different sizes depending on the number of parts shipped.


| SSOT-6 Packaging Information |                         |            |
|------------------------------|-------------------------|------------|
| Packaging Option             | Standard (no flow code) | D87Z       |
| Packaging type               | TNR                     | TNR        |
| Qty per Reel/Tube/Bag        | 3,000                   | 10,000     |
| Reel Size                    | 7" Dia                  | 13"        |
| Box Dimension (mm)           | 184x187x47              | 343x343x64 |
| Max qty per Box              | 9,000                   | 30,000     |
| Weight per unit (gm)         | 0.0158                  | 0.0158     |
| Weight per Reel (kg)         | 0.1440                  | 0.4700     |
| Note/Comments                |                         |            |



### SSOT-6 Unit Orientation




## SSOT-6 Tape Leader and Trailer Configuration: Figure 2.0



## SuperSOT™-6 Tape and Reel Data, continued




### SSOT-6 Embossed Carrier Tape

Configuration: Figure 3.0




| Dimensions are in millimeter |                 |                 |               |                 |                   |                 |             |                 |               |               |                 |                   |               |                 |
|------------------------------|-----------------|-----------------|---------------|-----------------|-------------------|-----------------|-------------|-----------------|---------------|---------------|-----------------|-------------------|---------------|-----------------|
| Pkg type                     | A0              | B0              | W             | D0              | D1                | E1              | E2          | F               | P1            | P0            | K0              | T                 | Wc            | Tc              |
| SSOT-6 (8mm)                 | 3.23<br>+/-0.10 | 3.18<br>+/-0.10 | 8.0<br>+/-0.3 | 1.55<br>+/-0.05 | 1.125<br>+/-0.125 | 1.75<br>+/-0.10 | 6.25<br>min | 3.50<br>+/-0.05 | 4.0<br>+/-0.1 | 4.0<br>+/-0.1 | 1.37<br>+/-0.10 | 0.255<br>+/-0.150 | 5.2<br>+/-0.3 | 0.06<br>+/-0.02 |

Notes: A0, B0, and K0 dimensions are determined with respect to the EIA/Jedec RS-481 rotational and lateral movement requirements (see sketches A, B, and C).



### SSOT-6 Reel Configuration: Figure 4.0





| Dimensions are in inches and millimeters |             |               |              |                                   |               |             |                                   |               |                             |
|--|-------------|---------------|--------------|-----------------------------------|---------------|-------------|-----------------------------------|---------------|-----------------------------|
| Tape Size                                | Reel Option | Dim A         | Dim B        | Dim C                             | Dim D         | Dim N       | Dim W1                            | Dim W2        | Dim W3 (LSL-USL)            |
| 8mm                                      | 7" Dia      | 7.00<br>177.8 | 0.059<br>1.5 | 512 +0.020/-0.008<br>13 +0.5/-0.2 | 0.795<br>20.2 | 2.165<br>55 | 0.331 +0.059/-0.000<br>8.4 +1.5/0 | 0.567<br>14.4 | 0.311 - 0.429<br>7.9 - 10.9 |
| 8mm                                      | 13" Dia     | 13.00<br>330  | 0.059<br>1.5 | 512 +0.020/-0.008<br>13 +0.5/-0.2 | 0.795<br>20.2 | 4.00<br>100 | 0.331 +0.059/-0.000<br>8.4 +1.5/0 | 0.567<br>14.4 | 0.311 - 0.429<br>7.9 - 10.9 |

# SuperSOT™-6 Package Dimensions





## SuperSOT™-6 (FS PKG Code 31, 33)



Scale 1:1 on letter size paper



Dimensions shown below are in:  
inches [millimeters]

Part Weight per unit (gram): 0.0158



LAND PATTERN RECOMMENDATION

CONTROLLING DIMENSION IS INCH  
VALUES IN [ ] ARE MILLIMETERS



SUPER SOT 6 LEADS

NOTES : UNLESS OTHERWISE SPECIFIED

1.0 STANDARD LEAD FINISH : 150 MICROINCHES 93.81 MICROMETERS)  
MINIMUM TIN / LEAD (SOLDER) ON COPPER.

2.0 NO JEDEC REGISTRATION AS OF JULY 1996

## TRADEMARKS

The following are registered and unregistered trademarks Fairchild Semiconductor owns or is authorized to use and is not intended to be an exhaustive list of all such trademarks.

|                      |                     |                     |            |
|----------------------|---------------------|---------------------|------------|
| ACEx™                | FASTr™              | PowerTrench®        | SyncFET™   |
| Bottomless™          | GlobalOptoisolator™ | QFET™               | TinyLogic™ |
| CoolFET™             | GTO™                | QS™                 | UHC™       |
| CROSSVOLT™           | HiSeC™              | QT Optoelectronics™ | VCX™       |
| DOME™                | ISOPLANAR™          | Quiet Series™       |            |
| E <sup>2</sup> CMOS™ | MICROWIRE™          | SILENT SWITCHER®    |            |
| EnSigna™             | OPTOLOGIC™          | SMART START™        |            |
| FACT™                | OPTOPLANAR™         | SuperSOT™-3         |            |
| FACT Quiet Series™   | PACMAN™             | SuperSOT™-6         |            |
| FAST®                | POP™                | SuperSOT™-8         |            |

## DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS.

## LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, or (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.
2. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

## PRODUCT STATUS DEFINITIONS

### Definition of Terms

| Datasheet Identification | Product Status         | Definition  |
|--------------------------|------------------------|---|
| Advance Information      | Formative or In Design | This datasheet contains the design specifications for product development. Specifications may change in any manner without notice.  |
| Preliminary              | First Production       | This datasheet contains preliminary data, and supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice in order to improve design. |
| No Identification Needed | Full Production        | This datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice in order to improve design.   |
| Obsolete                 | Not In Production      | This datasheet contains specifications on a product that has been discontinued by Fairchild semiconductor. The datasheet is printed for reference information only.   |