

REFERENCE SPECIFICATIONS

-NFC 93425 (in compliance with HE 507)

PHYSICAL CHARACTERISTICS

-INSULATOR MATERIAL: THERMOPLASTIC UL94V0

-CONTACT MATERIAL: PHOSPHOR BRONZE (signal contact)
GOLD OVER NICKEL

-ACCESSORIES: STAINLESS STEEL or BRASS
Cadmium plated, yellow passivation

-SHELLS: STEEL
Cadmium plated, yellow passivation

ELECTRICAL CHARACTERISTICS

-NOMINAL CURRENT: 7.5A

-CONTACT RESISTANCE: <= 7.3 m ohms signal

-CONTACT/CONTACT : >=1000 V

-CONTACT/GROUND : >=1200 V

-INSULATION RESISTANCE: >=5000 MOhms

ENVIRONMENTAL CHARACTERISTICS

- CLIMATIC CATEGORY: 55/125/21

TEMPERATURE RANGE -55°C TO +125°C

DAMP HEAT STEADY STATE 56 DAYS

SALT SPRAY 48 HOURS

MECHANICAL CHARACTERISTICS

- RETENTION AGAINST TORQUE: - Threaded insert: 0.7 N.m minimum
- Female screw : 0.5 N.m minimum

Series

DBML13W3S043N

Shell size: **E A B C D**
see sheet 3

M :characteristic
for the DM series

Front accessory definition
see sheet 2

Blank :without accessory

O :threaded insert M3

L :threaded insert UNC 4-40

V :female screw UNC 4-40

F :floating mounting

Layout of contacts

Contacts



S :Socket

Plating

Blank solder bucket 500 matings/unmatings


043 solder bucket 500 matings/unmatings for harsh environment

N :obligatory indication for HE 507 series



13W3 FOR EXAMPLE

www.fciconnect.com				surface ☒ tolerance std ISO 1302 ISO 406 ISO 1101 TOLERANCES UNLESS OTHERWISE SPECIFIED			projection 		mm 		
Dr M PESSON 2006/11/15				ANGULAR		0.X ±0.3		size A2		Scale 2:1	
Eng P LEGARE 2006/11/15				LINEAR		0.XX ±0.1					
Chr P LEGARE 2006/11/15				0° ±2°		0.XXX ±0.05		ECN		LS07-0309	
Appr P LEGARE 2006/11/15				Product family				- Spec ref			
				SUB FEMALE DMW				deg no C01-8637-1753		Rev C	
				mixed power+solder bucket							
				catalog no				CUSTOMER		sheet 1 of 7	






FRONT ACCESSORY	Blank without	F floating mounting	L insert M3 O insert UNC 4.40	V female screw UNC 4.40
-----------------	---------------	---------------------	----------------------------------	-------------------------

PART NUMBER	FRONT ACCESSORY
D*MxWxSN	without
D*MFxWxSN	Floating mounting
D*MLxWxSN	insert M3
D*MOxWxSN	insert UNC 4.40
D*MVxWxSN	female screw
D*MxWxS043N	without
D*MFxWxS043N	Floating mounting
D*MLxWxS043N	insert M3
D*MOxWxS03N	insert UNC 4.40
D*MVxWxS043N	female screw







shell size	LAYOUTS
#	xWx
E	5W1
A	11W1
A	7W2
B	21W1
B	17W2
B	13W3
B	9W4
C	25W3
C	21WA4
C	27W2
D	47W1
D	24W7
D	36W4

SCALE: 4


www.fciconnect.com		surface -	tolerance std	projection	mm
		ISO 1302	ISO 406 ISO 1101		
		TOLERANCES UNLESS OTHERWISE SPECIFIED			
Dr	M PESSON	2006/11/15	ANGULAR	0.X	±0.3
Eng	P LEGARE	2006/11/15	LINEAR	0.XX	±0.1
Chr	P LEGARE	2006/11/15	0° ±2°	0.XXX	±0.05
Appr	P LEGARE	2006/11/15	Product family		
				Spec ref	
SUB FEMALE DMW		mixed power+solder bucket		001-8637-1753	Rev. C
catalog no		CUSTOMER		sheet 2 of 7	




Floating signal contacts




SIDE VIEW FOR
LAYOUTS: E A B C




www.fciconnect.com			surface ☒ tolerance std 150 1302 150 406 150 1101		projection 		mm 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED					
Dr	M PESSON	2006/11/15	ANGULAR	0.X	±0.3	size	A2	Scale
Eng	P LEGARE	2006/11/15	LINEAR	0.XX	±0.1			
Chr	P LEGARE	2006/11/15	0° ±2°	0.XXX	±0.05	ECN	LS07-0309	
Appr	P LEGARE	2006/11/15	Product family			- Spec ref		
			title SUB FEMALE DMW mixed power+solder bucket			dag no C01-8637-1753		Rev C
catalog no			CUSTOMER			sheet 3 of 7		





www.fciconnect.com		surface - ISO 1302	tolerance std ISO 406 ISO 1101	projection TOLERANCES UNLESS OTHERWISE SPECIFIED	mm
Dr	M PESSON	2006/11/15	ANGULAR	0.X	±0.3
Eng	P LEGARE	2006/11/15	LINEAR	0.XX	±0.1
Chr	P LEGARE	2006/11/15	0° ±2°	0.XXX	±0.05
Appr	P LEGARE	2006/11/15	Product family	-	Spec ref
SUB FEMALE DMW		mixed power+solder bucket		catag no	CUSTOMER
Title		C01-8637-1753		Rev.	C



www.fciconnect.com		surface -	tolerance std	projection	mm
		ISO 1302	ISO 406	ISO 1101	
		TOLERANCES UNLESS OTHERWISE SPECIFIED			
Dr	M PESSON	2006/11/15	ANGULAR	0.X	±0.3
Eng	P LEGARE	2006/11/15	LINEAR	0.XX	±0.1
Chr	P LEGARE	2006/11/15	0° ±2°	0.XXX	±0.05
Appr	P LEGARE	2006/11/15	Product family	- Spec ref	
SUB FEMALE DMW		mixed power+solder bucket		catlog no	CUSTOMER
C01-8637-1753		Rev. C		sheet 6 of 7	

