






- 1. WIRE RANGE 28-32 AWG.
- 2. INSULATION RANGE 0.71-1.37 [.028-.054] DIA.
- 3. 0.00254 [.000100] MIN TIN-LEAD OVER 0.000762 [.000030] MIN NICKEL.
- 4. PREPLATED 0.00127 [.000050] MIN TIN-LEAD IN ZONES I & II, 0.000762 [.000030] MIN GOLD OVER 0.000762 [.000030] MIN NICKEL INLAY IN ZONE III.
- 5. PREPLATED 0.00127 [.000050] MIN TIN-LEAD IN ZONES I & II, 0.000381 [.000015] MIN GOLD OVER 0.000762 [.000030] MIN NICKEL INLAY IN ZONE III.
- 6. PREPLATED 0.00127 [.000050] MIN TIN-LEAD IN ZONES I & II, 0.00127 [.000050] MIN GOLD OVER 0.000762 [.000030] MIN NICKEL INLAY IN ZONE III.
- 7. PHOSPHOR BRONZE.
- 8. OBSOLETE.
- 9. ZONE I (OUTSIDE SURFACES).
- 10. ZONE II (INSIDE SURFACES).
- 11. ZONE III (INSIDE SURFACES).
- 12. MAXIMUM CUTOFF.



6	8	531225-9	8	531225-8
4	8	531225-7	8	531225-6
5	8	531225-5	8	531225-4
3	8	531225-3	8	531225-2
FINISH		LOOSE PIECE PART NO		STRIP PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. HAYMAKER 25JAN99	AMP AMP Incorporated Harrisburg, PA 17105-3608	
DIMENSIONS: MM [INCH]		CHK S. BOLASH 25JAN99		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD S. BOLASH 25JAN99	NAME	
0 PLC ±-		PRODUCT SPEC	CONTACT, RECEPTACLE, HIGH PRESSURE MINI-TANDEM SPRING	
1 PLC ±-		108-25031	SIZE	
2 PLC ±-		APPLICATION SPEC	CAGE CODE	
3 PLC ±0.13 [.005]		114-25021	DRAWING NO	
4 PLC ±-		WEIGHT	RESTRICTED TO	
ANGLES ±-		-	A2 00779 C- 531225	
FINISH		CUSTOMER DRAWING		SCALE 4:1
7		SHEET 1 OF 1		REV G