



Series 655000 TSOP-to-DIP 0.600 [15.24] Adapter

FEATURES


- Designed to allow user to cut 32-position adapter down to any size desired.
- Pins are mechanically fastened and soldered to board using Aries' patented process, creating a reliable electrical connection and rugged contact.

GENERAL SPECIFICATIONS

- ADAPTER BODY: FR-4 with 1-oz. Cu traces
- PADS: bare Cu protected with Entek® by Enthone or immersion white Sn to eliminate coplanarity concerns and solder bridges associated with hot air solder leveling
- PINS: Brass 360 1/2-hard per UNS C36000, ASTM B16/B16M
- PIN PLATING: 200μ [5.08μ] Sn/Pb 93/7 per ASTM B579-73 over 100μ [2.54μ] Ni per SAE AMS-QQ-N-290
- OPERATING TEMPERATURE: 221°F [105°C]

MOUNTING CONSIDERATIONS

- SUGGESTED PCB HOLE SIZE: 0.028 ± 0.003 [0.71 ± 0.08] dia.
- Will plug into standard IC sockets



CUSTOMIZATION: In addition to the standard products shown on this page, Aries specializes in custom design and production. Special materials, platings, sizes, and configurations can be furnished, depending on the quantity. **NOTE:** Aries reserves the right to change product general specifications without notice.

ORDERING INFORMATION


32-655000-10

32-655000-10-P for Panelized Version

ALL DIMENSIONS: INCHES [MILLIMETERS]

ALL TOLERANCES: ± 0.005 [0.13] UNLESS OTHERWISE SPECIFIED

CONSULT FACTORY FOR OTHER SIZES AND CONFIGURATIONS



ARIES
ELECTRONICS, INC.

Bristol, PA 19007-6810 USA
TEL (215) 781-9956 • FAX (215) 781-9845
WWW.ARIESELEC.COM • INFO@ARIESELEC.COM

PRINTOUTS OF THIS DOCUMENT MAY BE OUT OF DATE AND SHOULD BE CONSIDERED UNCONTROLLED

18041
Rev. AA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Aries:

[32-655000-10](#) [32-655000-10-P](#)

Aries Electronics:

[48-655000-10](#)