


8			7		
THIS DRAWING IS UNPUBLISHED.			RELEASED FOR PUBLICATION		
(C) COPYRIGHT — BY TYCO ELECTRONICS CORPORATION.			ALL RIGHTS RESERVED.		
PART NUMBER	REV	FIRST USED	POWER UNIT	FEED TYPE	
1852701-1	A	122500-1	LEADMAKER	POST FEED	
1852701-2	A	565435-5	BENCH MODEL K	PRE FEED	
1852701-3	A	354500-1	BENCH MODEL G	PRE FEED	



TERMINAL NAME: Ø.093 SOCKET			
AMP TERM PN	MFR TERM PN		
		PIN	
940318-1	02-09-2116		
940318-2	02-09-6122		
940318-3	02-09-6125		
940318-4	02-09-1151		
940318-5	02-09-8103		
		SOCKET	
940319-1	02-09-1117		
940319-2	02-09-5143		
940319-3	02-09-5130		
940319-4	02-09-1122		
940319-5	02-09-1203		
940319-6	02-09-1208		
		WIRE STRIP LENGTH	
		.156-.188	
		TERM APPL SPEC	
		NONE	
		FEED	
		.498	
		APPL INSTRUCTION	
		408-8040	
		SET UP GAGE	
		458637-1	
		LAYOUT	
		L1676Q	

LOC	DIST	REVIEWS			
A	66	F	LTR	DESCRIPTION	DATE
		A	ORIGINAL		

REF	REF	REF	REF	22594-8	NUT, HEX(1/2-20)	70
REF	REF	REF	REF	240628-1	PLATE, ADJUSTMENT	69
REF	REF	REF	REF	240626-1	SHAFT, PIVOT	68
REF	REF	REF	REF	240633-1	BUSHING	67
REF	REF	REF	REF	455680-1	LEVER, INTERMEDIATE	66
REF	REF	REF	REF	240629-1	BLOCK, PIVOT	65
REF	REF	REF	REF	240632-2	SCREW, ADJ FEED ROD	64
REF	REF	REF	REF	240659-3	PIN, CAM ROLLER	63
REF	REF	REF	REF	240658-1	ROLLER, CAM	62
REF	REF	REF	REF	454398-2	ROD, FEED	61
REF	REF	REF	REF	454178-1	GUIDE, FEED ROD	60
1	1	1	REF	454220-1	CAP, RAM	59
REF	REF	REF	REF	454485-1	HOUSING	58

1	1	1	REF	3-694433-2	PAWL, FEED	56
REF	REF	REF	REF	240624-1	PIN, FEED FINGER	55
REF	REF	REF	REF	691499-1	SPRING, FEED FINGER	54
REF	REF	REF	REF	690541-1	HOLDER, FEED FINGER	53
REF	REF	REF	REF	455679-1	LEVER, TERMINAL FEED ARM	52
1	1	1	REF	811242-2	BUMPER, HOLDDOWN	51
1	1	1	REF	690753-1	SPACER, TONKER	50
1	REF	REF	REF	690602-6	CAM, PRE-FEED 1 5/8 ST	49
REF	1	REF	REF	690602-5	CAM, PRE-FEED 1 1/8 ST	48
REF	REF	1	REF	690501-4	CAM, POST-FEED 1 5/8 ST	47
1	1	1	REF	459456-1	APPLICATOR, BASIC (SUBASSY)	46
1	1	1	REF	690191-1	PLUG, NYLON	45
1	1	1	REF	455673-8	RAM	44
1	1	1	REF	690125-1	WASHER, LAMINATED	43
1	1	1	REF	690124-1	WASHER, RAM	42
1	1	1	REF	690686-2	BOLT, CRIMPER(5/16x1.10)	41

1	1	1	REF	23241-6	BALL, STEEL	40
1	1	1	REF	690170-1	SPRING, COMPRESSION	39
1	1	1	REF	690142-1	DISC, INSULATION	38
1	1	1	REF	354777-1	WIRE DISC, PLASTIC	37
1	1	1	REF	22480-5	WASHER, SPRING	36
1	1	1	REF	690212-1	POST, RAM	35

REF	REF	REF	REF	455675-1	PLATE, BASE	33
REF	REF	REF	REF			32
REF	REF	REF	REF			31
REF	REF	REF	REF	455689-1	BLOCK, STRIP GUIDE ADJ	30
1	1	1	REF	1-318756-4	PLATE, STRIP GUIDE	29
2	2	2	REF			28
1	1	1	REF	8-22281-7	SPRING, DRAG	27
1	1	1	REF	690546-1	LEVER, DRAG RELEASE	26
1	1	1	REF	2-690754-1	DRAG, TERMINAL	25
1	1	1	REF	1320860-2	GUIDE, STRIP (REAR)	24
1	1	1	REF	1-690712-8	GUIDE, STRIP (FRONT)	23

REF	REF	REF	REF	4-22284-9	SPRING, FEED RETURN	21
1	1	1	REF			20
1	1	1	REF	1-458230-5	STRIPPER	19
1	1	1	REF			18
1	1	1	REF			17
1	1	1	REF			16
1	1	1	REF			15
1	1	1	REF			14
1	1	1	REF			13
1	1	1	REF			12
1	1	1	REF			11
1	1	1	REF			10

1	1	1	REF	2-853714-0	PLATE, REAR SHEAR	9
1	1	1	REF	1633054-3	ANVIL	8
1	1	1	REF			7
1	1	1	REF	238009-4	SPACER, BLOCK CRIMPER	6
1	1	1	REF	455888-6	SPACER, CRIMPER	5
1	1	1	REF	455888-2	SPACER, CRIMPER	4
1	1	1	REF	5-1424909-4	CRIMPER, INSULATION	3
1	1	1	REF	1-853720-4	BLADE, SLUG	2
1	1	1	REF	3-456405-9	CRIMPER, WIRE	1
-3	-2	-1	U/M	PART NO	DESCRIPTION	ITEM NO
QTY REQD PER ASSY				PARTS LIST		

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWG. 23SEPT02 CIR. 23SEPT02		 Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		SIDE FEED HDM APPLICATOR	
		0 PLC ± .005		PRODUCT SPEC		—	
		1 PLC ± .005				—	
		2 PLC ± .005				—	
		3 PLC ± .020				—	
4 PLC ± .005		4 PLC ± .005		APPLICATION SPEC		—	
MATERIAL		FINISH		WEIGHT		—	
—		—		A1 00779 C 1852701		—	
CUSTOMER DRAWING				SCALE		SHEET 1 OF 1	
						REV A	

