

Detailed information for: S203-K16



This page contains technical data sheet, documents library and links to offering related to this product. If you require any other information, please contact us using form located at the bottom of the page.

[Print...](#)[Print to Pdf...](#)[Data Sheet](#)[Documentation](#)

S203-K16

General Information

Extended Product Type: S203-K16

Type:

Product ID: 2CDS253001R0467

EAN: 4016779496155

Catalog Description: Miniature Circuit Breaker - S200 - 3P - K - 16 ampere

Long Description: System pro M compact S200 miniature circuit breakers are current limiting. They have two different tripping mechanisms, the delayed thermal tripping mechanism for overload protection and the electromechanic tripping mechanism for short circuit protection. They are available in different characteristics (B,C,D,K,Z), configurations (1P,1P+N,2P,3P,3P+N,4P), breaking capacities (up to 6 kA at 230/400 V AC) and rated currents (up to 63A). All MCBS of the product range S200 comply with IEC/EN 60898-1, IEC/EN 60947-2, UL1077 and CSA 22.2 No. 235, allowing the use for residential, commercial and industrial applications. Bottom-fitting auxiliary contact can be mounted on S200 to save 50% space.



Categories

Products » Low Voltage Products and Systems » Modular DIN Rail Products » Miniature Circuit Breakers MCBS

+ Accessories

Ordering

Minimum Order Quantity: 1 piece

Customs Tariff Number: 85362010

Popular Downloads

Data Sheet, Technical Information: [9AKK107046A0423](#)

Instructions and Manuals: [2CSC400002D0208](#)

Dimensions

Product Net Width:	52.5 mm
Product Net Depth / Length:	69 mm
Product Net Height:	88 mm
Product Net Weight:	0.375 kg
Technical	
Standards:	IEC/EN 60947-2 UL 1077
Number of Poles:	3
Tripping Characteristic:	K
Rated Current (I_n):	16 A
Rated Operational Voltage:	acc. to IEC 60947-2 440 V AC
Power Loss:	6 W at Rated Operating Conditions per Pole 2 W
Rated Insulation Voltage (U_i):	acc. to IEC/EN 60664-1 440 V
Operational Voltage:	Maximum (Incl. Tolerance) 125 V DC Maximum (Incl. Tolerance) 440 V AC Minimum 12 V AC / 12 V DC
Rated Frequency (f):	50 Hz 60 Hz
Rated Ultimate Short-Circuit Breaking Capacity (I_{cu}):	(230 V AC) 20 kA (440 V AC) 10 kA
Rated Service Short-Circuit Breaking Capacity (I_{cs}):	(230 V AC) 15 kA
Energy Limiting Class:	3
Overvoltage Category:	III
Pollution Degree:	3
Rated Impulse Withstand Voltage (U_{imp}):	4 kV (6.2 kV @ sea level) kV (5.0 kV @ 2000 m) kV
Dielectric Test Voltage:	50 / 60 Hz, 1 min: 2 kV
Housing Material:	Insulation Group II, RAL 7035
Actuator Type:	Insulation group II, black, sealable
Contact Position Indication:	Red ON / Green OFF
Degree of Protection:	IP20
Remarks:	IP40 in enclosure with cover
Electrical Endurance:	20000 AC cycle
Mechanical Endurance (N_{endu}):	20000 cycle
Terminal Type:	Screw Terminals
Screw Terminal Type:	Failsafe Bi-directional Cylinder-lift Terminal
Connecting Capacity:	Busbar 10 / 10 mm ² Flexible with Ferrule 0.75 ... 25 mm ² Flexible 0.75 ... 25 mm ² Rigid 0.75 ... 35 mm ² Stranded 0.75 ... 35 mm ²
Tightening Torque:	2.8 N·m
Recommended Screw Driver:	Pozidriv 2
Mounting on DIN Rail:	TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715

Mounting Position:

Any

Environmental**Ambient Air Temperature:**Operation -25 ... +55 °C
Storage -40 ... +70 °C**Resistance to Shock acc. to IEC 60068-2-27:** 25g / 2 shocks / 13 ms**Resistance to Vibrations acc. to IEC 60068-2-6:** 5g, 20 cycles at 5 ... 150 ... 5 Hz with load 0.8 In**Environmental Conditions:**28 cycles
with 55 °C / 90-96 %
and 25 °C / 95-100 %**RoHS Status:**

Following EU Directive 2002/95/EC August 18, 2005 and amendment

Technical UL/CSA**Maximum Operating Voltage UL/CSA:**110 V DC
480Y / 277 V AC**Connecting Capacity UL/CSA:**Busbar 18-8 AWG
Conductor 18-4 AWG**Tightening Torque UL/CSA:**

25 in-lb

Interrupting Rating acc. to UL1077:(110 V DC) 10 kA
(277 V AC) 6 kA
(480Y / 277 V AC) 6 kA**Certificates and Declarations (Document Number)****Declaration of Conformity - CE:** [2CDK403001D0605](#)**Environmental Information:** [2CDK400030D0201](#)**Instructions and Manuals:** [2CSC400002D0208](#)**RoHS Information:** [2CDK400003K0203](#)**Container Information****Package Level 1 Units:** 1 piece**Package Level 1 Width:** 92 mm**Package Level 1 Depth / Length:** 58 mm**Package Level 1 Height:** 80 mm**Package Level 1 Gross Weight:** 0.4 kg**Package Level 1 EAN:** 4016779609500**Package Level 2 Units:** 36 piece**Package Level 2 Width:** 275 mm**Package Level 2 Depth / Length:** 395 mm**Package Level 2 Height:** 210 mm**Package Level 2 Gross Weight:** 13.36 kg**Package Level 2 EAN:** 4016779973519**Classifications****Object Classification Code:**

F

ETIM 4:

EC000042 - Miniature circuit breaker (MCB)

ETIM 5:

EC000042 - Miniature circuit breaker (MCB)

ETIM 6:

EC000042 - Miniature circuit breaker (MCB)

ETIM 7:

EC000042 - Miniature circuit breaker (MCB)

eClass:

7.0 27141901

UNSPSC:

39121614

Contact information

What would you like to do?

I need more information

ABB Sales

Submit your inquiry

Your local ABB Sales Team

Name

Customer Support

Country / region

United States of America

Name

Company

E-Mail

Phone

Zip code

Your message

→ Privacy policy

Cancel

Send message

▲ Close