





Technical drawing of a 3D printed part, showing a cross-section with internal features. The drawing includes dimensions and tolerances:

- Top left dimension: 1.91 [+.075]
- Top right dimension: 1.91 [+.075]
- Bottom left dimension: 1.91 [+.075]
- Bottom right dimension: 1.27 [+.050] TYP
- Far right dimension: 0.953 [+.0375]
- Far right dimension: 8.00 [+.315]

④ ACTUAL HOLE SIZE USED WILL DEPEND ON TRACE ROUTING REQUIREMENTS BETWEEN HOLES AND CONNECTOR PLACEMENT TECHNIQUE.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 01-03-05 A. FERNANDEZ-DOCKS CHK 01-03-05 S. SHUEY APP'D M. WALMSLEY 01-03-05		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± 0.13 [0.005] 3 PLC ± — 4 PLC ± — ANGLES ± —		NAME RECEPTACLE ASSEMBLY, SHIELDED,VERTICAL, AMPLITUDE .050 Series	
		PRODUCT SPEC — APPLICATION SPEC —		SIZE CAGE CODE DRAWING NO A1 00779 C=5749721	
MATERIAL 		FINISH 		RESTRICTED TO WEIGHT — CUSTOMER DRAWING	
				SCALE 4:1 SHEET 1 of 1 REV B	

4805 (3/11)