

POWER

SIL10E Series

Data Sheet

Total Power: 49.9 Watts
Input Voltage: 3.0 - 5.5 Vdc
of Outputs: Single



SPECIAL FEATURES

- 10 A current rating
- Input voltage range: 3.0 - 5.5 Vdc
- Output voltage range: 0.8 - 3.63 V
- Ultra-high efficiency: 96% @ 5 Vin and 3.3 Vout
- Extremely low internal power dissipation
- Minimal thermal design concerns
- Designed in reliability: MTBF of >7 million hours per Telcordia SR-322
- Ideal solution where board space is at a premium or tighter card pitch is required
- Industry standard footprint and pin out
- Available RoHS compliant
- Two year warranty

SAFETY

- UL, cUL CAN/CSA 22.2 No. 60950-1-03/UL 60950-1, File No. E186249
- TÜV Product Service (EN60950) Certificate No. B 08 05 51485 378
- CB report and certificate to IEC60950, Certificate No. DE3-51686M1

Electrical Specifications

Input

Input voltage range	3.0 - 5.5 Vdc	
Input current	No load (max.)	70 mA
Input current (max.)		8 A max. @ Io max. and Vout = 3.3 V
Input reflected ripple		65 mA rms
Remote ON/OFF		See Note 2
Start-up time		20 ms

Output

Voltage adjustability (See Note 1)	Fixed output versions 5 Vin with wide trim 3.3 Vin with wide trim	±10% 0.8 - 3.63 Vdc 0.8 - 2.75 Vdc
Setpoint accuracy		±0.4%.
Line regulation		±0.2%
Load regulation		±1.0%
Minimum load		0 A
Overshoot/undershoot		None
Ripple and noise 5 Hz to 20 MHz		50 mV pk-pk 25 mV rms max.
Temperature co-efficient		±0.01% / °C
Transient response		50 mV max. deviation 50 µs recovery to within ±1.0%
Remote sense		10% Vo compensation

Note: All specifications are typical at nominal input, full load at 25 °C unless otherwise stated.

General Specifications

Efficiency		See table
Insulation voltage		Non-isolated
Switching frequency	Fixed	300 kHz typical
Approvals and standards		EN60950 UL/cUL60950
Material flammability		UL94V-0
Dimensions	L x W x H	50.8 x 7.8 x 12.7 mm 2.0 x 0.31 x 0.5 inches
Pin length	Vertical	0.135 ± 0.002 in (3.43 ± 0.5 mm)
Weight		5 g (0.18 oz)
MTBF	Telcordia SR-332 MIL-HDBK-217F	7,042,000 hours 680,000 hours

Environmental Specifications

Thermal performance	Operating ambient temperature	-40 °C to +100 °C
See Note 3	Non-operating temperature	-40 °C to +125 °C
Protection		
Short-circuit	Continuous	
Thermal	Automatic recovery	

EMC Characteristics

Electrostatic discharge	EN61000-4-2, IEC801-2
Conducted immunity	EN61000-4-6
Radiated immunity	EN61000-4-3

Ordering Information

Model Number ^(3, 4)	Output Power (Max.)	Input Voltage	Output Voltage	Output Current (Min.)	Output Current (Max.)	Efficiency (Typical)	Regulation	
							Line	Load
SIL10E-05W3V3-VJ	36.3 W	4.5 - 5.5 Vdc	0.8 - 3.63 Vdc	0 A	10 A	95%	±0.2%	±1.0%

Part Number System with Options

Product Family	Rated Output Current	Performance	Input Voltage	Type of Output	Output Voltage	Mounting/Packaging Options
SIL SIL = Single In Line	10 10 = 10 Amps	E E = Enhanced Performance	05 05 = 3.0 - 5.5 V 12 = 10 - 12 V	W W = Wide	3V3 2.5 V, 3.3 V, etc.	VJ V = Vertical H = Horizontal J = Pb-free RoHS 6/6 compliant

Output Voltage Adjustment

The ultra-wide output voltage trim range offers major advantages to users who select the SIL10E-05W3V3J. It is no longer necessary to purchase a variety of modules in order to cover different output voltages. The output voltage can be trimmed in a range of 0.8 Vdc to 3.63 Vdc. When the SIL10E-05W3V3J converter leaves the factory the output has been adjusted to the default voltage of 3.3 V.

- When $V_{in} \geq 4.5$ V, then V_{out} can be adjusted from 0.8 - 3.63 Vdc
- When $V_{in} < 4.5$ V, then V_{out} can be adjusted from 0.8 - 2.75 Vdc


Notes:

- When $V_{in} \geq 4.5$ V, then V_{out} can be adjusted from 0.8 V to 3.6 V. When $V_{in} < 4.5$ V, then V_{out} can be adjusted from 0.8 V to 2.75 V.
- The SIL10E features a 'Negative Logic' Remote ON/OFF operation. If not using the Remote ON/OFF pin, leave the pin open (the converter will be on). The Remote ON/OFF pin is referenced to ground. The following conditions apply for the SIL10E:

Configuration	Converter Operation
Remote pin open circuit	Unit is ON
Remote pin pulled low	Unit is ON
Remote pin pulled high [$V_{on/off} > 1.2$ V]	Unit is OFF
- Full derating curves available in both the Longform (Technical Reference) and Application Note 136.
- For certain applications that use low ESR capacitors on the output of the convertor and to insure maximum converter stability, please add the suffix '02' to the model, e.g. SIL10E-05S2V5-V02J.
- NOTICE: Some models do not support all options. Please contact your local Artesyn Embedded Technologies representative or use the on-line model number search tool at <http://www.Artesyn.com/power> to find a suitable alternative.

Mechanical Drawings


Input Pin Connections	
J1	
Pin	Function
1	+Vout
2	+Vout
3	Remote Sense (+)
4	+Vout
5	Ground



Horizontal Mount Version

Dimensions in Inches (mm)
Tolerances (unless otherwise specified)
2 Place 0.15
3 Place 0.006

Input Pin Connections	
J2	
Pin	Function
1	Ground
2	+Vin
3	+Vin
4	No Pin
5	Trim
6	Remote ON/OFF



Vertical Mount Version

Dimensions in Inches (mm)
Tolerances (unless otherwise specified)
2 Place 0.15
3 Place 0.006

WORLDWIDE OFFICES

Americas

2900 S.Diablo Way
Tempe, AZ 85282
USA
+1 888 412 7832

Europe (UK)

Waterfront Business Park
Merry Hill, Dudley
West Midlands, DY1 1LX
United Kingdom
+44 (0) 1384 842 211

Asia (HK)

14/F, Lu Plaza
2 Wing Yip Street
Kwun Tong, Kowloon
Hong Kong
+852 2176 3333

ARTESYN
EMBEDDED TECHNOLOGIES™

www.artesyn.com

While every precaution has been taken to ensure accuracy and completeness in this literature, Artesyn Embedded Technologies assumes no responsibility, and disclaims all liability for damages resulting from use of this information or for any errors or omissions. Artesyn Embedded Technologies, Artesyn and the Artesyn Embedded Technologies logo are trademarks and service marks of Artesyn Embedded Technologies, Inc. All other names and logos referred to are trade names, trademarks, or registered trademarks of their respective owners. © 2015 Artesyn Embedded Technologies, Inc.

For more information: www.artesyn.com/power
For support: productsupport.ep@artesyn.com