


SD6020

Low profile shielded drum core power inductors



Product features

- Low profile surface mount shielded drum core inductors
- 6.0 mm x 6.0 mm x 2.0 mm surface mount package
- Ferrite core material
- Inductance range from 1.99 μ H to 100 μ H
- Current range from 0.36 A to 4.2 A
- Frequency range up to 1 MHz

Applications

- Notebook, laptop computers
- Digital cameras
- LED Drivers
- TFT LCD Bias supplies
- Wireless handsets,
- Handheld instruments
- Gaming consoles
- GPS devices
- Battery backup/power
- DC-DC Converters,
- Buck-boost regulators

Environmental data

- Storage temperature range (component):
-40 °C to +125 °C
- Operating temperature range: -40 °C to +125 °C
(ambient plus self-temperature rise)
- Solder reflow temperature:
J-STD-020 (latest revision) compliant



Part Number ⁶	OCL ¹ $\mu\text{H} \pm 30\%$	I_{rms}^2 (A)	I_{sat}^3 (A)	Typ. DCR $\text{m}\Omega$ @ +20 °C	Max DCR $\text{m}\Omega$ @ +20 °C	K-factor ⁴
SD6020-2R2-R	1.99	4.2	2.2	30.0	36.0	40.0
SD6020-4R1-R	3.9	2.22	1.95	47.5	57.0	28.5
SD6020-5R4-R	5.5	1.80	1.60	63.3	76.0	24.0
SD6020-6R2-R	6.5	1.63	1.40	80.0	96.0	22.2
SD6020-8R9-R	8.5	1.47	1.25	96.7	116.0	19.3
SD6020-100-R	9.7	1.39	1.20	103.3	124.0	18.1
SD6020-120-R	11	1.31	1.10	115.0	138.0	17.1
SD6020-150-R	13	1.07	0.97	163.3	196.0	15.4
SD6020-180-R	16	1.10	0.85	175.0	210.0	13.9
SD6020-220-R	20	0.94	0.80	241.7	290.0	12.7
SD6020-270-R	27	0.82	0.75	275.0	330.0	10.9
SD6020-330-R	29	0.76	0.65	320.8	385.0	10.5
SD6020-390-R	37	0.63	0.57	416.7	500.0	9.2
SD6020-470-R	45	0.61	0.54	495.8	595.0	8.2
SD6020-560-R	55	0.57	0.50	515.0	618.0	7.8
SD6020-680-R	68	0.50	0.43	700.0	840.0	6.7
SD6020-820-R	80	0.48	0.41	815.0	978.0	6.3
SD6020-101-R	94	0.42	0.36	1000.0	1200.0	5.8

5 Part Number Definition: SD6020-xxx-R
SD6020 = Product code and size; -xxx = Inductance value in μH ;
R = decimal point; If no R is present, third character equals
number of zeros. -R suffix = RoHS compliant


[illegible]

Do not route traces or vias underneath the inductor.


Parts packaged on 13" Diameter reel, 2,600 parts per reel.




Core loss vs Bp-p



Temperature rise vs total loss



Inductance characteristics



Solder Reflow Profile




Table 1 - Standard SnPb Solder (T_p)

Package Thickness	Volume mm^3 <350	Volume mm^3 ≥ 350
<2.5mm	235°C	220°C
$\geq 2.5mm$	220°C	220°C

Table 2 - Lead (Pb) Free Solder (T_p)

Package Thickness	Volume mm^3 <350	Volume mm^3 350 - 2000	Volume mm^3 >2000
<1.6mm	260°C	260°C	260°C
1.6 – 2.5mm	260°C	250°C	245°C
>2.5mm	250°C	245°C	245°C

Reference JDEC J-STD-020

Profile Feature	Standard SnPb Solder	Lead (Pb) Free Solder
Preheat and Soak		
• Temperature min. (T_{smin})	100°C	150°C
• Temperature max. (T_{smax})	150°C	200°C
• Time (T_{smin} to T_{smax}) (t_s)	60-120 Seconds	60-120 Seconds
Average ramp up rate T_{smax} to T_p	3°C/ Second Max.	3°C/ Second Max.
Liquidous temperature (T_L)	183°C	217°C
Time at liquidous (t_L)	60-150 Seconds	60-150 Seconds
Peak package body temperature (T_p)*	Table 1	Table 2
Time (t_p)** within 5 °C of the specified classification temperature (T_c)	20 Seconds**	30 Seconds**
Average ramp-down rate (T_p to T_{smax})	6°C/ Second Max.	6°C/ Second Max.
Time 25°C to Peak Temperature	6 Minutes Max.	8 Minutes Max.

* Tolerance for peak profile temperature (T_p) is defined as a supplier minimum and a user maximum.

** Tolerance for time at peak profile temperature (t_p) is defined as a supplier minimum and a user maximum.

Life Support Policy: Eaton does not authorize the use of any of its products for use in life support devices or systems without the express written approval of an officer of the Company. Life support systems are devices which support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin.

Eaton
Electronics Division
1000 Eaton Boulevard
Cleveland, OH 44122
United States
www.eaton.com/electronics

© 2017 Eaton
All Rights Reserved
Printed in USA
Publication No. 4144 BU-SB111169
August 2017