

# Designer Series Light Panels from inspired LED




The Designer Series is ideally suited for under the cabinet task lighting applications, kitchen lighting, jewelry lighting, decorative lighting and reading lighting. Light Panels components are sold separately and can be mixed and matched to create a system.

## Features

- ✕ Low Cost Modular Design
- ✕ Both Warm and Cool Color Light Options
- ✕ Long Life 100,000HRs
- ✕ Easy Installation
- ✕ Highly Efficient PS
- ✕ Low Energy Consumption
- ✕ UV or IR free

## Interconnection



## Specifications

- ✕ Power Supply Options – 110 VAC in / 12 VDC out, 1, 2 amp wall plug.
- ✕ 10" Light Panel- 1.5 Watts 10" (L) x 7/8" (W) x 3/4" Screw or Adhesive Mounting.  
Warm White Color Temp. 3200K nm 55 lm or Cool White Color Temp. 6500K nm 90 lm.
- ✕ 18" Light Panel- 3 Watts 18" (L) x 7/8" (W) x 3/4" Screw or Adhesive Mounting. 12VDC  
Warm White Color Temp. 3200K nm 110 lm or Cool White Color Temp. 6500K nm 180 lm.
- ✕ In Line Switch – 2 1/2" (L) x 3/4" (W) x 1/2" (H) Screw or Adhesive Mounting.
- ✕ 4 Position Dimmer – 2 1/2" (L) x 3/4" (W) x 1/2" (H) Screw or Adhesive Mounting.
- ✕ Interconnect Cable – 4", 1', 2', 3', 4', 6' & 12' lengths available.

inspired LED

Patent Pending

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Inspired LED:](#)

[4870](#)