






REV	ECO	DESCRIPTION	DRFT	CHKD
1		DRAWING MODIFY	JAMY 4/19/06	
2		DRAWING MODIFY	Yican 08/01/06	



## NOTES:

ELECTRICAL:

1. VOLTAGE RATING : 125 VAC RMS.
2. CURRENT RATING : 1.5 AMP.
3. CONTACT RESISTANCE : 35 MILLIOHMS MAX.
4. INSULATION RESISTANCE: 1000 MEGOHMS MIN @ 500 VDC.
5. DIELECTRIC STRENGTH : 1000 VAC RMS 60Hz, 1MIN.

MECHANICAL:

1. HOUSING MATERIAL : NYLON+G.F.30% UL94V-0.COLOR YELLOW
2. CONTACT MATERIAL : PHOSPHOR BRONZE Ø 0.46mm.
3. PLATING : GOLD PLATING OVER NICKEL.
4. OPERATING LIFE : 750 CYCLES MIN.
5. PCB RETENTION PRE-SOLDER : 1 LB MIN.
6. PCB RETENTION POST-SOLDER: 10 LBS MIN.

ENVIRONMENTAL:

1. STORAGE : -40°C TO +85°C.
2. OPERATION: -40°C TO +85°C.
3. WAVE SOLDERING TEMPERATURE: 255°C TO 265°C(5~10 SECONDS).

**4. RoHS COMPLIANT**

MATES WITH MODULAR PLUG CONFORMING TO  
FCC PART 68, SUBPART F.

ROHS PART NUMBER: E5908-00CL8X-L

2- 6u" 5-50u"  
3-15u" 4-30u"

DETACHED LISTS	MM (INCH)	DFTO JAMY	DATE 10/17/05
		CHKD ANKUE	DATE 2006/8/3
		MFO	DATE
		APPV LUSHENG	DATE 2006/8/3
		MATERIAL :	
	ANGLES ± 0.5	QT'Y :	
		FINISH :	
		SCALE : 1.5:1	



**RoHS Compliant**

FULL RISE ELECTRONIC CO., LTD

TITLE

20.57 PCB JACK 8P

DRAWING NO. GE593266-LA

SIZE A3

/PART NO. SEE NOTE

REV 2

DO NOT SCALE DRAWING

SHEET X OF Y

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pulse:

[E5908-00CL82-L](#)