





P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REVISED PER E.O. PI9555	11JUL2007	-	RDR
	C	REVISED PER E.O. P20396	25JUN2010	-	RDR
	D	REVISED PER PCN-21-121539	04MAR2022	DRK	CB
	DI	REVISED PER PCN-25-234384	31JAN2025	RK	CB



SECTION A-A
CONDUCTOR WINGS



SECTION B-B
INSULATION WINGS

- 3 MATERIAL: .012 [0.30] THICK COPPER ALLOY
2. WIRE RANGE: 18 AWG TO 14 AWG [0.75-2.0 mm²]
INSULATION RANGE: $\varnothing .075 - .140$ [$\varnothing 1.91 - 3.56$]
- 1 PALLADIUM-NICKEL PLATED REGION

NOTES: UNLESS OTHERWISE SPECIFIED



TE INTERNAL PN	DEUTSCH PN	REV	PLATING
1060-16-0988	1060-16-0988	F	Selective Pd-Ni, Au/Ni/Cu overall

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J APOSTOL 03DEC2009	TE Connectivity		
DIMENSIONS: INCHES [mm]		CHK D MEYER 25JUN2010			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD R REED 25JUN2010			
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ±.025 [0.64] 4 PLC ± ANGLES ±		PRODUCT SPEC 108-151000			
MATERIAL 3		APPLICATION SPEC 114-151000	NAME PIN, STAMPED CONTACT SIZE 16 14-18 AWG, .075-.140 INS		
FINISH SEE TABLE		WEIGHT 0.33g	SIZE A3	CAGE CODE 4AFU8	DRAWING NO C-1060-16-09XX
		CUSTOMER DRAWING	SCALE 6:1	SHEET 1 OF 1	REV DI