

# Fuseholders

## MAXI™ Fuse In-Line Fuseholder

The In-Line Fuseholder provides an efficient, simple installation method for MAXI™ Fuse applications.

### Specifications

**Terminal:** Copper Alloy

**Body:** Black Thermoplastic (UL94HB)

**Cover:** Translucent Thermoplastic

**Ambient Temp.:** -10°C to +80°C

Maximum number of fuseblocks tied together is two for all ratings, up to and including 50A.

| Part Number | Description                                        |
|-------------|----------------------------------------------------|
| 152001      | Fuseholder-Rated at 60A                            |
| 152900      | Cover                                              |
| 913-653     | Ring tongue terminal for 2.5-6mm² (12-10AWG) wire* |
| 913-654     | Ring tongue terminal for 5-10mm² (10-8 AWG) wire*  |
| 913-550     | M5 x 8 Screw per DIN 7985-4.8                      |

\*It is recommended that cross linked polyethelene (GXL) insulated wire be used, as described in SAE J1128 (Type, FLY in DIN 76722) or equivalent.

## MAXI™ Fuse In-Line Fuseholder With Protective Cap

Supplied with two 6" leads -  
6 gauge wire for up to 60 amp  
MAXI™ Fuse applications,  
this In-Line Fuseholder also provides  
a protective cover for harsh under-the-hood  
environments. Mounting hole also permits  
easy bulkhead installation.

**Part Number:** MAH 1

## ATO® Blade Fuse Splashproof In-Line Fuseholder

The Splashproof Fuseholder provides a protective  
cover to permit the use of ATO® Fuses in harsh environments.

### Specifications

**Body:** Black Alcryn Thermoplastic

**Cover:** Black Alcryn Thermoplastic

**Ambient Temp.:** -10°C to +80°C

| Part Number | Description                                                        |
|-------------|--------------------------------------------------------------------|
| FHAC001     | #16AWG (1.0mm² ) stranded black wire with terminals rated for 20A  |
| FHAC002     | #12AWG (3.0mm² ) stranded orange wire with terminals rated for 30A |

