



LOC		DIST		REVISIONS					
HM		00		P	LTR	DESCRIPTION	DATE	DWN	APVD
				B		REV: EC 0B40-0259-01	23OCT01	TLP	CD
				C		ECO-06-016706	13JUL2006	JM	BM




- 1 MATERIAL: JACK HOUSING - POLYPHENYLENE OXIDE, 94V-0 RATED.
TERMINAL BLOCK - POLYPHENYLENE OXIDE, 94V-0 RATED.
STUFFER CAP - POLYCARBONATE, CLEAR, 94V-0 RATED.
DOOR - POLYCARBONATE, CLEAR, 94V-0 RATED.
JACK CONTACTS - PHOSPHOROUS BRONZE, PLATED WITH
1.27um [0.000050] MINIMUM THICK GOLD IN LOCALIZED
AREA AND 3.81um [0.00150] MINIMUM THICK MATTE TIN IN
SOLDER AREA OVER 1.27um [0.000050] MINIMUM THICK
NICKEL UNDERPLATE.
- 2 TOOLLESS WILL TERMINATE 22-24 AWG SOLID CONDUCTORS AND 24 AWG
STRANDED CONDUCTORS, 1.14 [0.045] MAXIMUM INSULATION DIAMETER.
- 3 CAVITY CONFORMS TO FCC RULES AND REGULATIONS)
PART 68 SUBPART F REQUIREMENTS.
- 4 MOUNTING PANEL THICKNESS 1.473 - 1.600 [0.058 - .063].
- 5 THESE TWO SUGGESTED CUTOUT OPENINGS ARE USED
IN TANDEM WITH DUAL FRONT AND BACK CUTOUTS.
- 6 ONE MODULAR JACK ASSEMBLY PER POLYBAG.
- 7 ASSEMBLY SHIPPED WITH STUFFER CAP NOT LATCHED
AT REAR OF HOUSING ASSEMBLY AS SHOWN.
- 8 DIMENSION SHOWN WITH STUFFER CAP IN LATCHED POSITION.



OPEN POSITION



SEE DETAIL A



DETAIL A
SCALE 10:1


PART NUMBER

COLOR CODE	IDC TERMINAL	MODULAR JACK	
WHITE/BLUE			5
BLUE			4
WHITE/ORANGE			3
ORANGE			6
WHITE/GREEN			1
GREEN			2
WHITE/BROWN			7
BROWN			8


ELECTRICAL SCHEMATIC
T568A

COLOR CODE	IDC TERMINAL	MODULAR JACK	
WHITE/BLUE			5
BLUE			4
WHITE/ORANGE			1
ORANGE			2
WHITE/GREEN			3
GREEN			6
WHITE/BROWN			7
BROWN			8

ELECTRICAL SCHEMATIC
T568B



SINGLE PANEL CUTOUT



SUGGESTED FLUSH MOUNT
PANEL APPLICATION CUTOUT

PACKAGE	HOUSING COLOR	PART NUMBER
	ELECTRIC IVORY	1-1339189-1
	VIOLET	1-1339189-0
	GREEN	1339189-9
	YELLOW	1339189-8
	RED	1339189-7
	BLUE	1339189-6
	ORANGE	1339189-5
	NEMA GRAY	1339189-4
	WHITE	1339189-3
	BLACK	1339189-2
	LIGHT ALMOND	1339189-1

THIS DRAWING IS UNPUBLISHED. IT IS THE PROPERTY OF TYCO ELECTRONICS CORPORATION. IT IS TO BE USED ONLY FOR THE PURPOSES SPECIFIED. IT IS NOT TO BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, INCLUDING PHOTOCOPYING, RECORDING, OR BY ANY INFORMATION STORAGE AND RETRIEVAL SYSTEM. WITHOUT PERMISSION IN WRITING FROM TYCO ELECTRONICS CORPORATION.		DWN P. PEPE	09JUN99	tyco Electronics		AMP Incorporated Harrisburg, PA 17103-3608
DIMENSIONS: mm [INCHES]		CHK P. PEPE	09JUN99	NAME		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD P. PEPE	09JUN99	PRODUCT SPEC		
0 PLC ±.01		APPLICATION SPEC		SIZE		
1 PLC ±.013		WEIGHT		CUSTOME DRAWING		
2 PLC ±.025		REVISION		SCALE		
3 PLC ±.053		SHEET		FORM		
4 PLC ±.075		DRAWING NO.		REV		
ANGLES		DATE		BY		
FINISH		SHEET		FORM		