



Home / Products / Cylinders / Stainless Steel Cylinders / Stainless Steel Cylinder Configurator / FDR-12-1

Knowledge Base

- [New! All Stainless Steel Cylinders](#)
- [New Clippard 9/16" Bore Stainless Steel Cylinders Press Release](#)
- [Bore Size Calculator](#)
- [Picture Perfect](#)
- [Pneumatic Solutions for Pushing Cheese](#)
- [Portable Gas Analyzers](#)
- [more...](#)



More Views



Get CAD files:

FDR-12-1

Mount	Cylinder Type
Block	Double Acting
Rod Type	Stroke
Standard	1
Cushion Type	Magnetic Piston
None	No
Rod Wipers	Seal Material
No	Nitrile
Rod Thread	Spring
1/4-28	Normal Spring
Rear Port	Rotated Ports
Std Rear Port	Standard Ports

(In Stock)

Qty:

Details

3/4" Bore S/S Cylinder, Front Mount, Rotating Rod

See Catalog: [Page 25](#)

Additional Information

Bore	3/4"
Clevis Bracket	CB-1795
Cushion Type	None
Cylinder Type	Double Acting
Length	4.593" (tip-to-tip)
Length, Cylinder	3.968"
Length, Rod (exposed)	0.625"
Length, Rod Thread	0.562"
Magnetic Piston	No
Material, Bushing	Sintered Bronze
Material, Rod	303 Stainless Steel
Material, Tube	304 Stainless Steel
Materials, End Caps	Clear Anodized Aluminum
Mount	Block
Port Thread	1/8" NPT
Pressure, Max	250 psi
Rear Port	Std Rear Port
Rod Clevis	RC-1281
Rod End	RE-1285
Rod Extension	Available from your local distributor .
Rod Thread	1/4-28
Rod Type	Standard
Rod Wipers	No
Rotated Ports	Standard Ports
Seal Material	Nitrile
Spring	None
Stroke	1"
Temperature, Max	230 °F (110 °C)
Temperature, Min	-20 °F (-29 °C)



