



HF body tube

Product illustrations are exemplary illustrations and can deviate from supplied products.

Part no.: 30809-667

Features:

- With high shielding against high-frequency radiation
- Frame-type plug-in units to accept boards in HP dimensions
- Module body with cooling fins
- Front and rear with four threads for bolting front and rear panels
- Plug-in unit can be mounted in a subrack or fitted laterally to a mounting plate with the slide nut

Add to basket



Standard pack quantity 5

**Technical Information:**

Height	Width	Description
3 U	7 HP	Depth = 167 mm

Downloads:

Download CAD data in DWG format ([Log in required](#))

Download CAD data in DXF format ([Log in required](#))

To gain access to the additional information you must log in.
If you do not yet have a user name, you may register here.

Delivery comprises:

Qty	Description
1	HF body tube, Al extrusion, black anodised, cut edges clean

Accessories:

Part no.	Description	
21100-289	Slide nut M 3	Add to basket
20838-001	Front panel with handle	Add to basket
21100-105	Mounting kit for one HF frame type plug-in unit	Add to basket
30809-635	Rear panel	Add to basket
21100-112	Slide nut M 2.5	Add to basket
21101-937	Board fastening in HF plug-in units Complete assembly kit	Add to basket
20838-093	Front panel with handle	Add to basket
30809-641	Rear panel	Add to basket

Technical Data:

B = internal width dimension

Note:

- Please order front panel, rear panel, brackets for PCBs and fixing materials separately