




NOTES:-

- MICRO SWITCH BLUE GLASS FILLED POLYESTER HOUSING & COVER. BLACK GLASS FILLED POLYAMIDE HEAD.
- ENCLOSURE DOUBLE INSULATED TO IEC 539 CLASS II.
- MINIMUM OPERATING VELOCITY (V_{min}) = 2.0 MM/S
MAXIMUM OPERATING VELOCITY (V_{max}) = 200 MM/S
MAXIMUM OPERATING FREQUENCY (F_{max}) = 250 OPS/MIN
(THESE LIMITS APPLY TO CAM OPERATION AS SHOWN IN THE ABOVE DIAGRAMS ONLY)
- FREE POSITION (FP), OPERATING POINT (OP), OVERTRAVEL (OT) AND PRETRAVEL (PT) ALL TO EN50047.

△ MAXIMUM TIGHTENING TORQUE FOR FIXING SCREW = 0.5Nm (4.4in.LB)

△ 3.50(.138) FOR PG13.5, M20x1.5 AND PF 1/2 THREADS, 7.20(.283) FOR 1/2-14 NPT THREADS.

7. CABLED PRODUCTS TEMP RANGE -25°C TO 85°C -3°F TO 185°F

IEC 947-5-1 ELECTRICAL RATING										ALL CHANGES CAN BE MADE IN THIS DRAWING WITHOUT JOINT NEWHOUSE/FREEPORT APPROVAL	
SILVER CONTACTS						GOLD PLATED CONTACTS		ENVIRONMENTAL		APPROVALS	
AC		AC (FOR 2NC)		DC		I _{th} = 10A 1V 10μA MIN. 50V 100mA MAX.		IP66 NEMA 1, 12, 13		△ UL	
A600 U _e	AC15 I _e	A500 U _e	AC15 I _e	O300 U _e	DC13 I _e			TEMP RANGE : -40°C TO 85°C -40°F TO 185°F			
VOLTS AMPS		VOLTS AMPS		VOLTS AMPS				STORAGE : -40°C TO 85°C -40°F TO 185°F			
120 240 380 480 500 600	6 3 1.9 1.5 1.4 1.2	120 240 380 480 500	6 3 1.9 1.5 1.4	125 250	0.55 0.27			SHOCK : 50G PER IEC 68-2-27 VIBRATION : 10G PER IEC 68-2-6			
THE COPYRIGHT OF THIS DRAWING IS THE PROPERTY OF HONEYWELL LTD. THE DRAWING IS SUPPLIED IN CONFIDENCE AND IS NOT TO BE REPRODUCED OR USED FOR ANY PURPOSE OTHER THAN THAT FOR WHICH IT IS SUPPLIED.						THIRD ANGLE PROJECTION		SCALE 1:1		DIMENSIONS ARE IN MM/INCHES.	
										MODIFY ON CAD SYSTEM ONLY	