



FEATURES:

- Newly designed Minipincer® Test Lead Patch Cord with Pincer contacts complies with IEC 1010-2-31, which is the latest international safety standard for test accessories.
- Pincer width is a slim .36" (9.14 mm) for easier access to test terminals.
- Pincer clamp is gold plated Beryllium Copper to ensure signal integrity & attaches onto component leads up to .060" (1.5 mm) O.D.
- Pincer patch cord can connect directly to Pomona's sheathed type flexible tests leads for added patch cord length.
- For added safety, the grabber and banana plug body insulation material is fire retardant Nylon 6, UL94V-0 rated.
- Banana jack is molded directly to the wire for a long lasting connection.
- High strand count silicone insulated wire offers excellent flexibility and high temperature resistance.

MATERIALS:

Grabber: Body: Nylon 6 – Fire Retardant – UL94 V-O Rated, Color per part number

Pincer: Beryllium Copper, Gold Plated, Compression Spring: Music Wire

Wire: 18 AWG, 65 x 36 Tinned Copper, Insulation – Silicone, .144" (3.66 mm) O.D., Color per Part Number

Banana Jack: Body - Brass, Nickel Plated

Insulation - Nylon 6, Fire Retardant UL94 V-0 Rated, Color per part number

RATINGS:

IEC 1010 2-031, Category II, P2 Compliant

Operating Voltage: 300 VRMS/DC Max.

Current: 5 Amperes Max.

ORDERING INFORMATION: Model 6261-12-*

Standard Wire Length: 12" (30.48 cm). Additional lengths can be quoted upon request.

* = Color Code, -0 Black and -2 Red

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Sales: 800-490-2361 Fax: 888-403-3360

Technical Assistance: 800-241-2060

PomonaACCESS 90489 (800) 444-6785 or (425) 446-6010

More drawings available at www.pomonaelectronics.com

Page 1 of 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

6261-12-0