

Cirrus 25




Cirrus 25	25 / 1				25 / 2			
Nominal Power Output at 10°C, 12 V or 230 V*	5 W		10 W		20 W		40 W	
Rated fan current (amps) at 12 V	0.04		0.04		0.04		0.04	
Recommended fuse at 12 V/24 V	4		4		4		4	
Time delay (Amps) at 115 / 230 V	n/a		n/a		n/a		2	
Fan volumetric flow at zero static pressure (m³/hr)	5.1		5.1		5.1		5.1	
Fan lifetime at 40°C, L 10 hours	120,000		120,000		120,000		120,000	
Fan operating temperature C°	-10 to +70		-10 to +70		-10 to +70		-10 to +70	
Input Voltage (V) fan DC heater	12	24	12	24	12	24	12	24
	12	24	12	24	12	24	12	24
	n/a		n/a		n/a		n/a	
Dimensions (mm) cross section length of profile and fan	26 x 27		26 x 27		26 x 27		26 x 27	
	50		50		72		72	
	0.06		0.06		0.09		0.09	
Weight (kg)	0.06		0.06		0.09		0.09	
Protection Type	IP 20		IP 20		IP 20		IP 20	
Cable length (mm)	600		600		600		600	
Outlet Finger Guard (High Voltage supply)	n/a		n/a		n/a		Y	
Outlet Finger Guard (Low Voltage supply)	Option		Option		Option		Option	

When specifying 12V fan, select either ac or dc operation. For 24V fan operation ac or dc can be applied.* Other power outputs available on request.

Ordering Example:

Type	Size	Power	Fan input	AC / DC	Heater Voltage	Finger guard outlet	DIN clip
	1 / 2		12 / 24			1 / 0	1 / 0
C 25	2	30 W	12 V	DC	24 V	0	1

Order Code Example: C 25 / 2 – 30 W – 12 V – DC – 24 V – 0 – 1



- Features:**
- High power to size ratio
 - Lightweight
 - Easy to fit
 - pre-wired
 - Independent fan circuit to aid climate cooling
- Options:**
- Finger guard at outlet
 - Smartcon®- Cable to allow AC fan supply and/or 24 V fan supply
 - Fixings - 35mm DIN Rail clip (EN50022)

DBK David+Baader GmbH

Components

Rheinstrasse 72 - 74
D - 76870 Kandell

Phone: + 49 (0) 72 75 7 03 - 231
Fax: + 49 (0) 72 75 7 03 - 249

info@dbk-group.de
www.dbk-components.com