

RODZAJ POLACZENIA/INTERNAL CIRCUIT
PATRZ SCHEMATY POLACZEN/WIRING CONFIGURATION
NAPIECIE ORAZ KOLOR DIODY/VOLTAGE AND LED COLOUR:

1= 12V
2= 24V
3= 48V
4= 115V
5= 230V

A= 12V
B= 24V
C= 48V
D= 115V
E= 230V


CZERWONA DIODA
RED LED

ZIELONA DIODA
GREEN LED



ŻOLTA DIODA
YELLOW LED

MOLEX PN	MPM PN	MOLEX PN	MPM PN
1210010189	A06A11	1210010216	A06C4D
1210010190	A06A12	1210010217	A06C4E
1210010192	A06A14	1210010219	A06C4H
1210010193	A06A15	1210010220	A06C4L
1210010194	A06A1B	1210010221	A06C4M
1210010197	A06A1H	1210010222	A06G21
1210010199	A06A1L	1210010223	A06G22
1210010200	A06A1M	1210010225	A06G24
1210010202	A06C32	1210010226	A06G25
1210010205	A06C35	1210010228	A06G2B
1210010206	A06C3B	1210010229	A06G2D
1210010207	A06C3H	1210010230	A06G2E
1210010209	A06C41	1210010231	A06G2H
1210010210	A06C42	1210010232	A06G2K
1210010211	A06C43	1210010233	A06G2L
1210010212	A06C44	1210010234	A06G2M
1210010213	A06C45	1210010236	A06S02
1210010420	A06C4A	1210010240	A06S0H
1210010214	A06C4B	1210010198	A06A1K
1210010215	A06C4C	1210010241	A06S0L

SCHEMATY POLACZEN
/WIRING CONFIGURATION



TAMPONADRUK SCHEMATU (BIAŁY)
CIRCUIT PRINTOUT (WHITE)



ORIGINAL RELEASE EC NO: WEU2009-0419 DRWN: MWOL SZCZAK 2009/05/20 CHKD: MDABROWSKA 2009/05/20 APPR: GOGRODNIK 2009/05/20	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION STYLE MM ONLY	SCALE ---	DESIGN UNITS METRIC	FIRST ANGLE PROJECTION
	DESCRIPTION	mm INCH	DRAWN BY DATE	TITLE	MPM A06 ADAPTORS	
	4 PLACES	± --- ± ---	MLEVYTSKYY 2009/05/05	CHECKED BY DATE	MOLEX INCORPORATED	
	3 PLACES	± --- ± ---	MDABROWSKA 2009/05/05	APPROVED BY DATE	DOCUMENT NO. A06XXX	
	2 PLACES	± --- ± ---	MWOL SZCZAK 2009/05/05	MATERIAL NO.	SHEET NO. 1 OF 1	
1 PLACE	± --- ± ---	ANGULAR ± ---°	SEE DRAWING	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	SIZE A3					