


Multilayer Chip Baluns For DVB-H/ISDB-T


Conformity to RoHS Directive

HHM Series HHM1591A2


SHAPES AND DIMENSIONS



CIRCUIT DIAGRAM



RECOMMENDED PC BOARD PATTERNS



ELECTRICAL CHARACTERISTICS

Unbalanced impedance	50Ω
Balanced impedance	100Ω
Frequency range	350 to 950MHz
Unbalanced port return loss	4.5dB min.
Phase imbalance at balanced port	180±20deg.
Amplitude imbalance at balanced port	0±2.0dB
Insertion loss	2.8dB max.
Temperature range	Operating -40 to +85°C
	Storage -40 to +85°C
Packaging style and quantities	2000pieces/reel


• Conformity to RoHS Directive: This means that, in conformity with EU Directive 2002/95/EC, lead, cadmium, mercury, hexavalent chromium, and specific bromine-based flame retardants, PBB and PBDE, have not been used, except for exempted applications.

• All specifications are subject to change without notice.


FREQUENCY CHARACTERISTICS

Unbalance 50Ω/Balance 100Ω


RETURN LOSS



AMPLITUDE BALANCE



INSERTION LOSS



PHASE BALANCE

