

Radial Lead Type

Series: EE Type : A

Country of Origin

- Features High ripple current (at high frequency):
40% higher than ED Series
Endurance: 105 °C 8000,10000h
Miniaturization: 1 rank smaller size(at the same ripple current)
RoHS directive compliant

Japan
Malaysia
China



■ Main applications

Electronic ballast, Power supply input circuit


■ Specifications

Category temp. range	-25 to +105°C							
Rated W.V. Range	160 to 450 V .DC							
Nominal Cap. Range	10 to 330 μ F							
Capacitance Tolerance	±20 % (120Hz/+20°C)							
DC Leakage Current	I ≤ 0.06 CV + 10(μ A) After 2 minutes application of rated working voltage at +20°C							
tan δ	Please see the attached standard products list							
Characteristics at low temperature	W.V.(V)	160	200	250	350	400	450	(Impedance ratio at 120Hz)
	Z(-25°C)/Z(20°C)	3	3	3	6	6	6	
Endurance	After following life test with DC voltage and +105±2°C ripple current value applied (The sum of DC and ripple peak voltage shall not exceed the rated working voltage), for regulation times, the capacitors shall meet the limits specified below. Post test requirements at +20°C.							
	Regulation times of life test: φ 10=8000h, φ 12.5 to φ18=10000h							
	Capacitance change	±20% of initial measured value						
	tan δ	≤ 200 of initial specified value						
	DC leakage current	≤ initial specified value						
Shelf Life	After storage for 1000 hours at +105±2 °C with no voltage applied and then being stabilized at +20 °C, capacitors shall meet the limits specified in Endurance (With voltage treatment)							

■ Ripple current Frequency Coefficient

Frequency (Hz)	50 ≤	120 ≤	300 ≤	1k ≤	10k ≤	100k ≤
Cap.(μF)						
10μF ≤	0.25	0.35	0.50	0.65	0.90	1.00
100μF ≤	0.30	0.40	0.55	0.70	0.90	1.00

■ Dimensions in mm (not to scale)



	(mm)			
Body Dia. φD	10	12.5	16	18
Lead Dia. φd	0.6	0.6	0.8	0.8
Lead space P	5.0	5.0	7.5	7.5

■ Case size / Ripple current table

Cap. (μ F)	160V			200V		
	Case size ϕ D×L (mm)	Ripple current (mA)r.m.s.(105 °C)		Case size ϕ D×L (mm)	Ripple current (mA)r.m.s.(105 °C)	
		120Hz	100kHz		120Hz	100kHz
22	10 × 20	245	700	10 × 20	300	850
33	10 × 20	280	810	10 × 20	320	920
47	10 × 20	370	1065	12.5 × 20	385	1100
68	12.5 × 20	470	1350	12.5 × 25	465	1330
				16 × 20S	465	1330
82	12.5 × 25	520	1480	16 × 20S	510	1460
100	12.5 × 25	660	1660	16 × 25	690	1730
	16 × 20S	680	1700	18 × 20S	670	1665
150	16 × 25	755	1890	16 × 25	740	1860
	18 × 20S	730	1820			
220	16 × 31.5	910	2280	18 × 31.5	1175	2600
	18 × 25S	780	1950			
330	18 × 31.5	1040	2600	18 × 40	1250	3120

Cap. (μ F)	250V			350V		
	Case size ϕ D×L (mm)	Ripple current (mA)r.m.s.(105 °C)		Case size ϕ D×L (mm)	Ripple current (mA)r.m.s.(105 °C)	
		120Hz	100kHz		120Hz	100kHz
15				10 × 20	170	480
22	10 × 20	275	785	12.5 × 20	230	660
33				12.5 × 25	275	790
	12.5 × 20	350	995	16 × 20S	315	900
47	12.5 × 25	450	1290	16 × 25	375	1070
	16 × 20S	490	1400	18 × 20S	375	1070
68	16 × 20S	490	1400	16 × 31.5	535	1530
				18 × 25S	465	1330
82	16 × 25	590	1680	18 × 25S	535	1530
	18 × 20S	590	1680			
100	16 × 31.5	840	2100	18 × 31.5	640	1600
	18 × 25S	840	2100			
150	18 × 31.5	1010	2520			
220	18 × 40	1175	2940			

Cap. (μ F)	400V			450V		
	Case size ϕ D×L (mm)	Ripple current (mA)r.m.s.(105 °C)		Case size ϕ D×L (mm)	Ripple current (mA)r.m.s.(105 °C)	
		120Hz	100kHz		120Hz	100kHz
10	10 × 20	150	430	10 × 20U	115	330
				12.5 × 20	170	490
15	12.5 × 20	205	590	12.5 × 25	270	780
22	12.5 × 25	265	760	16 × 20S	330	945
	16 × 20S	300	860			
33	16 × 20S	355	1020	16 × 25	350	1000
				18 × 20S	350	1000
47	16 × 25	410	1180	16 × 31.5	420	1200
	18 × 20S	410	1180	18 × 25S	420	1200
56				18 × 31.5	480	1380
68	18 × 25	515	1470	18 × 40	630	1800
82	18 × 31.5	575	1645			
100	18 × 40	825	2060			

■ Standard Products

W.V. (V)	Cap. (±20%) (μF)	Case size		Specification			Lead Length			Part No.	Min.Packaging Q'ty	
		Dia. (mm)	Length (mm)	Ripple current (100kHz) (+105°C) (mA)	tan δ (120Hz) (+20°C)	Endu- rance (hours)	Lead Dia. (mm)	Lead Space			Straight Leads (pcs)	Taping (pcs)
								Straight (mm)	Taping ※B (mm)			
160	22	10	20	700	0.15	8000	0.6	5.0	5.0	EEUEE2C220 ()	200	500
	33	10	20	810	0.15	8000	0.6	5.0	5.0	EEUEE2C330 ()	200	500
	47	10	20	1065	0.15	8000	0.6	5.0	5.0	EEUEE2C470 ()	200	500
	68	12.5	20	1350	0.15	10000	0.6	5.0	5.0	EEUEE2C680 ()	200	500
	82	12.5	25	1480	0.15	10000	0.6	5.0	5.0	EEUEE2C820 ()	200	500
	100	12.5	25	1660	0.15	10000	0.6	5.0	5.0	EEUEE2C101 ()	200	500
		16	20	1700	0.15	10000	0.8	7.5	7.5	EEUEE2C101S ()	100	250
	150	16	25	1890	0.15	10000	0.8	7.5	7.5	EEUEE2C151 ()	100	250
		18	20	1820	0.15	10000	0.8	7.5	7.5	EEUEE2C151S ()	100	250
	220	16	31.5	2280	0.15	10000	0.8	7.5		EEUEE2C221	100	
		18	25	1950	0.15	10000	0.8	7.5	7.5	EEUEE2C221S()	100	250
330	18	31.5	2600	0.15	10000	0.8	7.5		EEUEE2C331	50		
200	22	10	20	850	0.15	8000	0.6	5.0	5.0	EEUEE2D220	200	500
	33	10	20	920	0.15	8000	0.6	5.0	5.0	EEUEE2D330 ()	200	500
	47	12.5	20	1100	0.15	10000	0.6	5.0	5.0	EEUEE2D470 ()	200	500
	68	12.5	25	1330	0.15	10000	0.6	5.0	5.0	EEUEE2D680 ()	200	500
		16	20	1330	0.15	10000	0.8	7.5	7.5	EEUEE2D680S ()	100	250
	82	16	20	1460	0.15	10000	0.8	7.5	7.5	EEUEE2D820S()	100	250
	100	16	25	1730	0.15	10000	0.8	7.5	7.5	EEUEE2D101 ()	100	250
		18	20	1665	0.15	10000	0.8	7.5	7.5	EEUEE2D101S()	100	250
	150	16	25	1860	0.15	10000	0.8	7.5	7.5	EEUEE2D151 ()	100	250
	220	18	31.5	2600	0.15	10000	0.8	7.5		EEUEE2D221	100	
	330	18	40	3120	0.15	10000	0.8	7.5		EEUEE2D331	50	
250	22	10	20	785	0.15	8000	0.6	5.0	5.0	EEUEE2E220 ()	200	500
	33	12.5	20	995	0.15	10000	0.6	5.0	5.0	EEUEE2E330 ()	200	500
	47	12.5	25	1290	0.15	10000	0.6	5.0	5.0	EEUEE2E470 ()	200	500
		16	20	1400	0.15	10000	0.8	7.5	7.5	EEUEE2E470S()	100	250
	68	16	20	1400	0.15	10000	0.8	7.5	7.5	EEUEE2E680S()	100	250
	82	16	25	1680	0.15	10000	0.8	7.5	7.5	EEUEE2E820 ()	100	250
		18	20	1680	0.15	10000	0.8	7.5	7.5	EEUEE2E820S ()	100	250
	100	16	31.5	2100	0.15	10000	0.8	7.5		EEUEE2E101	100	
		18	25	2100	0.15	10000	0.8	7.5	7.5	EEUEE2E101S ()	100	250
	150	18	31.5	2520	0.15	10000	0.8	7.5		EEUEE2E151	50	
	220	18	40	2940	0.15	10000	0.8	7.5		EEUEE2E221	50	
350	15	10	20	480	0.20	8000	0.6	5.0	5.0	EEUEE2V150 ()	200	500
	22	12.5	20	660	0.20	10000	0.6	5.0	5.0	EEUEE2V220 ()	200	500
	33	12.5	25	790	0.20	10000	0.6	5.0	5.0	EEUEE2V330 ()	200	500
		16	20	900	0.20	10000	0.8	7.5	7.5	EEUEE2V330S ()	100	250
	47	16	25	1070	0.20	10000	0.8	7.5	7.5	EEUEE2V470 ()	100	250
		18	20	1070	0.20	10000	0.8	7.5	7.5	EEUEE2V470S ()	100	250
	68	16	31.5	1530	0.20	10000	0.8	7.5		EEUEE2V680	100	
		18	25	1330	0.20	10000	0.8	7.5	7.5	EEUEE2V680S ()	100	250
	82	18	25	1530	0.20	10000	0.8	7.5	7.5	EEUEE2V820S ()	100	250

When requesting taped product, please put the letter "B" between the "()". Lead wire pitch B=5mm, 7.5mm.
The taping dimensions are explained on p.196 of our Catalog. Please use it as a reference guide.

Design, and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and / or use. Should a safety concern arise regarding this product, please be sure to contact us immediately. Mar.2006

■ Standard Products

W.V. (V)	Cap. (±20%) (μF)	Case size		Specification			Lead Length			Part No.	Min.Packaging Q'ty	
		Dia.	Length	Ripple current (100kHz) (+105°C) (mA)	tan δ (120Hz) (+20°C)	Endu- rance (hours)	Lead Dia. (mm)	Lead Space			Straight Leads (pcs)	Taping (pcs)
								Straight (mm)	Taping *B (mm)			
350	100	18	31.5	1600	0.20	10000	0.8	7.5		EEUEE2V101	50	
400	10	10	20	430	0.24	8000	0.6	5.0	5.0	EEUEE2G100 ()	200	500
	15	12.5	20	590	0.24	10000	0.6	5.0	5.0	EEUEE2G150 ()	200	500
	22	12.5	25	760	0.24	10000	0.6	5.0	5.0	EEUEE2G220 ()	200	500
		16	20	860	0.24	10000	0.8	7.5	7.5	EEUEE2G220S()	100	250
	33	16	20	1020	0.24	10000	0.8	7.5	7.5	EEUEE2G330S()	100	250
	47	16	25	1180	0.24	10000	0.8	7.5	7.5	EEUEE2G470 ()	100	250
		18	20	1180	0.24	10000	0.8	7.5	7.5	EEUEE2G470S()	100	250
	68	18	25	1470	0.24	10000	0.8	7.5	7.5	EEUEE2G680 ()	100	250
	82	18	31.5	1645	0.24	10000	0.8	7.5		EEUEE2G820	50	
100	18	40	2060	0.24	10000	0.8	7.5		EEUEE2G101	50		
450	10	10	20	330	0.24	8000	0.6	5.0	5.0	EEUEE2W100U()	200	500
		12.5	20	490	0.24	10000	0.6	5.0	5.0	EEUEE2W100()	200	500
	15	12.5	25	780	0.24	10000	0.6	5.0	5.0	EEUEE2W150()	200	500
	22	16	20	945	0.24	10000	0.8	7.5	7.5	EEUEE2W220S()	100	250
	33	16	25	1000	0.24	10000	0.8	7.5	7.5	EEUEE2W330()	100	250
		18	20	1000	0.24	10000	0.8	7.5	7.5	EEUEE2W330S()	100	250
	47	16	31.5	1200	0.24	10000	0.8	7.5		EEUEE2W470	100	
		18	25	1200	0.24	10000	0.8	7.5	7.5	EEUEE2W470S()	100	250
	56	18	31.5	1380	0.24	10000	0.8	7.5		EEUEE2W560	50	
68	18	40	1800	0.24	10000	0.8	7.5		EEUEE2W680	50		

When requesting taped product, please put the letter "B" between the "()". Lead wire pitch B=5mm, 7.5mm.
The taping dimensions are explained on p.196 of our Catalog. Please use it as a reference guide.