






1	2	3	4	5
---	---	---	---	---



PCB LAYOUT - COMPONENT VIEW

MATERIAL:
HOUSING MATERIAL: PBT
FLAMABILITY RATING: UL94-V0
COLOR: RED
CONTACT MATERIAL: PHOSPHOR BRONZE
CONTACT TYPE: STAMPED
CONTACT PLATING: MATT TIN OVER NICKEL
QUALITY CLASS: 25 MATING CYCLES
PITCH: 2.54 MM PER ROW
1.27 MM RIBBON CABLE

ENVIRONNEMENTAL:
OPERATING TEMPERATURE: -40°C UP TO 105°C
COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL:
CURRENT RATING: 1.0 A PER PIN (CABLE)
WORKING VOLTAGE: 100VAC
INSULATION RESISTANCE: >1000MOHM
DIELECTRIC WITHSTANDING VOLT.: 500VAC/MN
CONTACT RESISTANCE: 10mOHM MAX


STANDARD
UL CERTIFIED: E323964 / MOD. NUMBER 69020710xx7x

SOLDERING: WAVE PROCESS ONLY

DIMENSION:
DIM.A= 1.27 x No. of Spaces
DIM.B= DIM.A + 3.3
DIM.C= DIM.A + 2.1
DIM.D= DIM.A + 4.7

AVAILABLE
xx : 4 TO 26 CIRCUITS

PACKAGING:
x = 2 TUBE
x = 7 TAPE & REEL

RoHS Compliant				PROJECTION: 	GENERAL TOLERANCE .X = +/- 0.2 .XX = +/- 0.15		
G							
F							
E	07-MAR-11	CLOSE HEIGHT	GG				
D	07-APR-10	PINNING	JP				
C	09-MAR-10	STANDARD	JP	APPROVAL: RJ	UNIT: MM	DESCRIPTION: MM TRANSITION CONNECTOR	SIZE
B	27-NOV-07	MODIFICATIONS	CH				
A	03-NOV-06	PDF	JP				
REV	DATE	FILE	BY				
					SCALE:	WERI PART NO: 690 207 10 xx 7 x	A4
					SHEET: 1/1		
					DRAW: EAGER		