

Single-Phase Metered PDU, 3.2-3.8kW 16/20A 200-240V, 0U Vertical Rackmount, 6 C19 and 32 C13 outlets, C20 inlet with NEMA L6-20P input cable

MODEL NUMBER: PDUMV20HV



Description

Tripp Lite single phase Metered PDU / Power Distribution Units offer real-time local reporting of load level in amps via built-in digital display. Enables visual monitoring of PDU load levels to prevent overloads as additional equipment is added. Offers reliable rackmount multi-outlet power distribution from any protected UPS, generator or mains input power source. High quality design includes rugged all-metal housing and secure rackmount installation with included mounting accessories.

Features

- 16/20A single phase 200-240V Metered Power Distribution Unit / PDU (Agency derated to 16A continuous)
- Two-digit lighted meter reports combined total output current in amps
- 10ft / 3m detachable input cable with NEMA L6-20P plug
- C20 inlet accepts a variety of 16A international cordsets
- 0U 63.75in / 162cm vertical rackmount format installs using no rack spaces
- 38 total outlets (6 C19, 32 C13)
- Installable cord retention brackets keep vital networking equipment plugged in
- Toolless installation supported in button-mount compatible equipment racks
- Bolt-down installation brackets support installation in other racks and additional surfaces

Specifications

General Info	
Product Group	PDUS
OVERVIEW	

Highlights

- Metered single phase 16/20A 200-240V 0U 63.75in / 162cm vertical rackmount PDU
- Two-digit meter reports output current in amps
- 10ft / 3m detachable input cable with NEMA L6-20P plug
- C20 inlet accepts a variety of 16A international cordsets
- 38 output receptacles (6 C19, 32 C13) with cord retention brackets
- Toolless button mount and bolt-down bracket installation hardware included

Applications

- Ideal means of powering networking equipment in datacenters, computer rooms and network closets

Package Includes

- PDUMV20HV 63.75 inch basic PDU with owner's manual
- Set of 2 bolt-on plug retention brackets and installation hardware
- Set of mounting brackets and installation hardware

PDU Type	Metered
OUTPUT	
Output Capacity Details	3.3kW (208V input), 3.5kW (220V input), 3.7kW (230V input), 3.8kW (240V input), 3.2kW (200V input); 20A maximum (agency de-rated to 16A continuous)
Frequency Compatibility	50 / 60 Hz
Output Nominal Voltage	200-240V nominal, single phase
Overload Protection	Outlets are arranged in a single unbreakered load bank
Outlet Quantity / Type	38 total (6 C19, 32 C13)
Outlet Type	IEC-C13, IEC-C19
INPUT	
PDU Input Voltage	200; 208; 220; 230; 240
Maximum Input Amps	20
Maximum Input Amps Details	Agency de-rated to 16A continuous
Input Connection Type	L6-20P detachable cordset, C20 inlet available
PDU Plug Type	NEMA L6-20P; IEC-320 C20
Input Cord Length (ft.)	10
Input Cord Length (m)	3.05
Input Phase	Single-Phase
LEDS ALARMS & SWITCHES	
Switches	n/a
Front Panel LEDs	Includes built-in 2-character LED meter to display whole PDU power consumption
PHYSICAL	
Shipping Dimensions (hwd / in.)	64.5 x 3.5 x 4.75
Shipping Dimensions (hwd / cm)	163.8 x 8.9 x 12.1
Shipping Weight (lbs.)	6
Shipping Weight (kg)	2.8
Unit Dimensions (hwd / in.)	63.75 x 2.25 x 3.75
Unit Dimensions (hwd / cm)	162 x 5.7 x 9.5
Unit Weight (lbs.)	5.2
Unit Weight (kg)	2.4
Material of Construction	Aluminum
Style	Vertical Rackmount, Wallmount, Raceway, Workbench
Form Factors Supported	Ou vertical installation in equipment racks, plus under-counter and wallmount



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

PDU Form Factor	Vertical (0U)
ENVIRONMENTAL	
Relative Humidity	0-95% non-condensing
CERTIFICATIONS	
Certifications	Tested to UL60950-1 (USA, Canada), NOM (Mexico), CE (IEC 60950)
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.